

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P523730

Luminaire Tested: **SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523730
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5651.1 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523730

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523730

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	33	27
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	66	55	47	41	60	50	44	38	42	36	32	33	30	27	25	23	21	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	17	15	12
9	49	37	29	25	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7756	7756	7756
5°	7812	7765	7737
10°	7799	7744	7709
15°	7747	7705	7663
20°	7696	7652	7594
25°	7604	7552	7477
30°	7464	7424	7331
35°	7268	7219	7127
40°	7036	6992	6912
45°	6844	6795	6729
50°	6598	6555	6492
55°	6257	6174	6127
60°	5696	5532	5506
65°	5017	4809	4792
70°	4332	4154	4154
75°	3729	3675	3625
80°	3289	3326	3246
85°	2572	2805	2805



TEST NUMBER: P523730

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.5	1.4
10°-20°	227.0	4.0
20°-30°	339.9	6.0
30°-40°	398.7	7.1
40°-50°	400.0	7.1
50°-60°	341.2	6.0
60°-70°	222.5	3.9
70°-80°	111.6	2.0
80°-90°	30.9	0.5
90°-100°	256.7	4.5
100°-110°	730.5	12.9
110°-120°	699.9	12.4
120°-130°	553.9	9.8
130°-140°	444.6	7.9
140°-150°	348.1	6.2
150°-160°	254.7	4.5
160°-170°	157.8	2.8
170°-180°	53.5	0.9
0°-30°	646.4	11.4
0°-40°	1045.1	18.5
0°-60°	1786.3	31.6
0°-90°	2151.4	38.1
90°-120°	1687.1	29.9
90°-150°	3033.8	53.7
90°-180°	3500.0	61.9
0°-180°	5651.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	844	836	838	835	835	80
15°	811	803	807	804	802	229
25°	747	738	742	735	734	343
35°	645	639	641	634	633	403
45°	524	521	521	516	516	404
55°	389	388	384	382	381	346
65°	230	226	220	219	220	229
75°	105	105	103	102	102	113
85°	24	26	26	26	26	29
90°	0	0	0	0	0	2
95°	28	111	497	172	106	32
105°	114	172	744	1315	1250	120
115°	211	255	564	1196	1404	208
125°	298	330	539	894	1069	267
135°	364	395	532	755	854	281
145°	430	452	537	654	712	268
155°	491	502	550	591	615	227
165°	542	544	556	568	576	152
175°	568	565	562	559	555	54
180°	563	563	563	563	563	



TEST NUMBER: P523730

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	840.6	840.6	840.6	840.6	840.6
2.5°	845.9	838.9	840.6	839.3	835.8
5°	843.5	835.6	838.4	835.4	835.4
7.5°	837.8	829.1	831.9	828.9	828.8
10°	832.5	823.8	826.6	823.6	822.9
12.5°	824.8	816.2	819.5	816.0	815.8
15°	811.1	803.2	806.7	803.7	802.3
17.5°	795.6	787.0	791.2	787.1	786.5
20°	783.8	775.2	779.4	773.5	773.5
22.5°	769.7	761.0	765.9	758.2	758.2
25°	747.0	738.4	741.8	735.2	734.5
27.5°	720.0	711.5	715.2	707.7	707.5
30°	700.6	692.7	696.9	688.8	688.1
32.5°	679.4	672.0	675.1	667.0	666.3
35°	645.3	638.9	640.9	633.5	632.8
37.5°	609.5	602.9	605.3	598.9	598.6
40°	584.2	579.9	580.5	575.3	573.9
42.5°	560.6	555.7	556.3	551.2	550.9
45°	524.5	520.9	520.8	515.7	515.7
47.5°	486.2	483.5	482.7	478.4	478.3
50°	459.7	457.5	456.7	453.0	452.3
52.5°	432.0	431.0	428.5	425.4	425.2
55°	389.0	387.5	383.8	381.6	380.9
57.5°	342.3	339.4	335.2	332.0	332.5
60°	308.7	305.8	299.8	298.4	298.4
62.5°	276.3	272.8	266.8	264.8	265.9
65°	229.8	225.5	220.3	218.8	219.5
67.5°	187.7	183.8	178.1	178.1	177.5
70°	160.6	158.4	154.0	154.0	154.0
72.5°	136.4	135.4	132.2	132.1	131.6
75°	104.6	104.6	103.1	102.4	101.7
77.5°	78.4	78.7	77.9	77.2	75.9
80°	61.9	63.3	62.6	61.9	61.1
82.5°	46.6	48.0	47.9	46.6	46.4
85°	24.3	26.5	26.5	26.5	26.5
87.5°	6.5	8.8	9.4	9.4	10.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.6	45.4	105.4	30.7	23.1
95°	27.8	110.6	497.0	172.0	106.0
97.5°	51.2	129.5	765.4	547.7	375.3
100°	67.5	140.8	823.7	834.3	642.7
102.5°	85.5	152.9	810.8	1068.0	900.6
105°	113.5	172.2	744.4	1314.9	1250.0
107.5°	142.0	194.6	666.9	1384.6	1442.4
110°	161.7	211.0	622.3	1357.9	1487.8

TEST NUMBER: P523730

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	180.6	227.3	592.3	1294.9	1480.1
115°	211.0	255.0	564.5	1195.8	1404.3
117.5°	237.8	279.1	548.0	1087.5	1308.3
120°	259.2	293.8	546.3	1025.6	1237.2
122.5°	276.4	310.9	542.0	971.3	1167.7
125°	297.8	330.2	538.8	894.1	1069.0
127.5°	321.1	351.5	537.1	848.0	992.1
130°	333.1	363.5	534.5	815.8	941.5
132.5°	346.0	375.5	534.5	790.8	906.4
135°	364.2	394.6	532.4	755.2	853.7
137.5°	381.3	410.9	532.1	725.2	810.2
140°	394.2	424.5	531.3	700.2	781.9
142.5°	408.7	434.1	533.9	680.3	753.6
145°	429.5	451.5	536.6	653.7	712.3
147.5°	447.3	468.7	541.4	626.7	677.4
150°	462.7	477.4	543.1	617.8	653.4
152.5°	474.7	490.2	544.8	605.7	638.8
155°	490.6	502.1	549.5	590.7	614.8
157.5°	510.3	517.2	550.6	583.9	601.1
160°	520.6	525.8	554.8	578.7	593.4
162.5°	526.6	532.6	555.7	574.4	585.7
165°	542.0	544.1	555.9	567.9	576.3
167.5°	552.5	550.6	560.8	566.3	569.6
170°	555.9	554.9	559.1	560.3	564.5
172.5°	563.6	560.1	561.7	558.6	561.9
175°	567.7	564.6	562.3	559.0	554.8
177.5°	569.4	564.4	561.7	558.3	559.1
180°	563.4	563.4	563.4	563.4	563.4

(END OF REPORT)