

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523742

Luminaire Tested: **SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523742
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6658.6 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523742

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523742

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20									
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																									
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48							
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41							
2	89	82	76	71	82	75	70	66	64	60	56	53	50	48	43	41	39	34							
3	81	72	65	59	74	66	60	55	56	52	48	47	43	40	38	36	33	29							
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25							
5	68	57	49	43	63	53	45	40	45	39	35	37	33	30	31	28	25	22							
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19							
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17							
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15							
9	50	38	31	26	46	35	29	24	31	25	21	26	22	19	21	18	16	14							
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13							

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11505	11505	11505
5°	11590	11518	11479
10°	11570	11489	11437
15°	11494	11431	11368
20°	11418	11353	11268
25°	11281	11204	11092
30°	11073	11015	10875
35°	10783	10709	10574
40°	10438	10372	10254
45°	10154	10082	9982
50°	9789	9726	9633
55°	9283	9159	9088
60°	8449	8208	8167
65°	7444	7134	7110
70°	6428	6161	6161
75°	5532	5454	5376
80°	4877	4936	4819
85°	3822	4160	4160



TEST NUMBER: P523742

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.9	1.8
10°-20°	336.7	5.1
20°-30°	504.3	7.6
30°-40°	591.5	8.9
40°-50°	593.4	8.9
50°-60°	506.2	7.6
60°-70°	330.1	5.0
70°-80°	165.6	2.5
80°-90°	45.8	0.7
90°-100°	254.3	3.8
100°-110°	723.6	10.9
110°-120°	693.3	10.4
120°-130°	548.7	8.2
130°-140°	440.5	6.6
140°-150°	344.8	5.2
150°-160°	252.3	3.8
160°-170°	156.3	2.3
170°-180°	53.0	0.8
0°-30°	958.9	14.4
0°-40°	1550.5	23.3
0°-60°	2650.1	39.8
0°-90°	3191.7	47.9
90°-120°	1671.3	25.1
90°-150°	3005.3	45.1
90°-180°	3467.0	52.1
0°-180°	6658.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1247	1247	1247	1247	1247	
5°	1251	1240	1244	1239	1239	119
15°	1203	1192	1197	1192	1190	339
25°	1108	1095	1101	1091	1090	510
35°	957	948	951	940	939	598
45°	778	773	773	765	765	599
55°	577	575	569	566	565	513
65°	341	335	327	325	326	340
75°	155	155	153	152	151	168
85°	36	39	39	39	39	42
90°	0	0	0	0	0	2
95°	28	110	492	170	105	32
105°	112	171	737	1303	1238	119
115°	209	253	559	1185	1391	206
125°	295	327	534	886	1059	264
135°	361	391	527	748	846	278
145°	426	447	532	648	706	266
155°	486	497	544	585	609	225
165°	537	539	551	563	571	151
175°	562	559	557	554	550	53
180°	558	558	558	558	558	

TEST NUMBER: P523742

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.0	1247.0	1247.0	1247.0	1247.0
2.5°	1254.9	1244.6	1247.0	1245.2	1240.0
5°	1251.4	1239.6	1243.7	1239.4	1239.4
7.5°	1242.9	1230.0	1234.1	1229.8	1229.5
10°	1235.0	1222.2	1226.3	1221.9	1220.8
12.5°	1223.6	1210.8	1215.8	1210.5	1210.3
15°	1203.3	1191.6	1196.8	1192.3	1190.2
17.5°	1180.4	1167.5	1173.8	1167.7	1166.8
20°	1162.9	1150.0	1156.3	1147.6	1147.6
22.5°	1141.9	1129.1	1136.2	1124.8	1124.8
25°	1108.2	1095.4	1100.6	1090.7	1089.6
27.5°	1068.2	1055.6	1061.0	1049.9	1049.6
30°	1039.4	1027.6	1033.9	1021.9	1020.8
32.5°	1007.9	997.0	1001.6	989.5	988.4
35°	957.4	947.8	950.8	939.9	938.8
37.5°	904.3	894.5	897.9	888.5	888.1
40°	866.7	860.3	861.2	853.5	851.4
42.5°	831.7	824.4	825.4	817.7	817.3
45°	778.2	772.8	772.7	765.0	765.0
47.5°	721.3	717.3	716.1	709.7	709.5
50°	682.0	678.8	677.6	672.1	671.1
52.5°	640.9	639.4	635.6	631.0	630.8
55°	577.1	574.9	569.4	566.1	565.0
57.5°	507.8	503.5	497.3	492.5	493.3
60°	457.9	453.7	444.8	442.6	442.6
62.5°	409.8	404.7	395.9	392.8	394.5
65°	341.0	334.6	326.8	324.6	325.7
67.5°	278.5	272.7	264.3	264.2	263.4
70°	238.3	235.1	228.4	228.4	228.4
72.5°	202.4	200.9	196.1	196.1	195.2
75°	155.2	155.2	153.0	151.9	150.8
77.5°	116.3	116.7	115.6	114.5	112.6
80°	91.8	93.9	92.9	91.8	90.7
82.5°	69.1	71.2	71.0	69.1	68.9
85°	36.1	39.3	39.3	39.3	39.3
87.5°	9.6	13.0	14.0	14.0	14.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.5	45.0	104.4	30.4	22.9
95°	27.6	109.5	492.3	170.4	105.0
97.5°	50.7	128.3	758.2	542.6	371.8
100°	66.8	139.5	816.0	826.5	636.6
102.5°	84.7	151.5	803.2	1057.9	892.1
105°	112.5	170.6	737.4	1302.6	1238.3
107.5°	140.7	192.8	660.6	1371.6	1428.8
110°	160.2	209.0	616.5	1345.2	1473.8

TEST NUMBER: P523742

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	178.9	225.2	586.8	1282.8	1466.2
115°	209.0	252.6	559.2	1184.6	1391.1
117.5°	235.6	276.4	542.8	1077.3	1296.0
120°	256.8	291.0	541.1	1016.0	1225.5
122.5°	273.8	308.0	536.9	962.1	1156.8
125°	295.0	327.1	533.7	885.7	1058.9
127.5°	318.1	348.2	532.0	840.0	982.8
130°	330.0	360.1	529.5	808.2	932.7
132.5°	342.7	372.0	529.5	783.3	897.9
135°	360.8	390.9	527.4	748.1	845.7
137.5°	377.7	407.0	527.1	718.4	802.6
140°	390.5	420.6	526.3	693.7	774.6
142.5°	404.9	430.0	528.8	673.9	746.6
145°	425.5	447.3	531.6	647.5	705.6
147.5°	443.1	464.3	536.3	620.8	671.0
150°	458.4	472.9	538.0	612.0	647.3
152.5°	470.3	485.6	539.7	600.0	632.8
155°	486.0	497.4	544.3	585.2	609.1
157.5°	505.5	512.3	545.4	578.5	595.5
160°	515.7	520.9	549.6	573.3	587.8
162.5°	521.6	527.6	550.5	569.0	580.2
165°	536.9	539.0	550.7	562.6	570.9
167.5°	547.3	545.4	555.6	561.0	564.3
170°	550.7	549.7	553.9	555.0	559.2
172.5°	558.3	554.8	556.4	553.3	556.6
175°	562.4	559.3	557.1	553.8	549.6
177.5°	564.1	559.1	556.4	553.0	553.9
180°	558.1	558.1	558.1	558.1	558.1

(END OF REPORT)