

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523937

Luminaire Tested: **SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523937
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9153.8 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 71.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523937

CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523937

CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	63	59	53	49	47	38	36	34	25	24	23	17
3	76	67	60	55	68	60	54	50	46	42	39	34	31	29	22	21	19	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	39	57	47	41	36	37	32	29	27	24	21	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	42	35	30	48	38	32	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	19	23	18	15	17	14	12	11	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7683	7683	7683
5°	7739	7692	7665
10°	7725	7671	7637
15°	7675	7633	7591
20°	7624	7581	7524
25°	7533	7481	7407
30°	7394	7355	7261
35°	7201	7151	7061
40°	6970	6926	6847
45°	6780	6731	6665
50°	6537	6495	6432
55°	6198	6116	6069
60°	5643	5480	5455
65°	4971	4764	4748
70°	4292	4114	4114
75°	3693	3643	3590
80°	3257	3294	3220
85°	2551	2784	2784



TEST NUMBER: P523937

CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	0.9
10°-20°	224.8	2.5
20°-30°	336.8	3.7
30°-40°	395.0	4.3
40°-50°	396.2	4.3
50°-60°	338.0	3.7
60°-70°	220.4	2.4
70°-80°	110.6	1.2
80°-90°	30.6	0.3
90°-100°	515.2	5.6
100°-110°	1465.8	16.0
110°-120°	1404.4	15.3
120°-130°	1111.5	12.1
130°-140°	892.2	9.7
140°-150°	698.5	7.6
150°-160°	511.1	5.6
160°-170°	316.6	3.5
170°-180°	107.4	1.2
0°-30°	640.3	7.0
0°-40°	1035.3	11.3
0°-60°	1769.5	19.3
0°-90°	2131.1	23.3
90°-120°	3385.4	37.0
90°-150°	6087.6	66.5
90°-180°	7023.0	76.7
0°-180°	9153.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	836	828	830	828	828	79
15°	804	796	799	796	795	227
25°	740	731	735	728	728	340
35°	639	633	635	628	627	399
45°	520	516	516	511	511	400
55°	385	384	380	378	377	342
65°	228	223	218	217	218	227
75°	104	104	102	101	101	112
85°	24	26	26	26	26	28
90°	0	0	0	0	0	3
95°	56	222	997	345	213	64
105°	228	346	1494	2639	2508	241
115°	423	512	1133	2400	2818	417
125°	598	663	1081	1794	2145	535
135°	731	792	1068	1516	1713	564
145°	862	906	1077	1312	1429	538
155°	984	1008	1103	1185	1234	455
165°	1088	1092	1116	1140	1156	306
175°	1139	1133	1128	1122	1113	108
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P523937

CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	832.7	832.7	832.7	832.7	832.7
2.5°	837.9	831.1	832.7	831.4	828.0
5°	835.6	827.7	830.5	827.6	827.6
7.5°	829.9	821.3	824.1	821.1	821.0
10°	824.6	816.1	818.8	815.9	815.2
12.5°	817.0	808.5	811.8	808.3	808.1
15°	803.5	795.6	799.1	796.1	794.7
17.5°	788.1	779.6	783.8	779.7	779.1
20°	776.5	767.9	772.1	766.3	766.3
22.5°	762.5	753.9	758.7	751.1	751.1
25°	740.0	731.4	734.9	728.3	727.6
27.5°	713.3	704.9	708.5	701.0	700.9
30°	694.0	686.2	690.4	682.3	681.6
32.5°	673.0	665.7	668.8	660.7	660.0
35°	639.3	632.9	634.9	627.6	626.9
37.5°	603.8	597.2	599.6	593.3	593.0
40°	578.7	574.4	575.1	569.9	568.5
42.5°	555.4	550.5	551.1	546.0	545.7
45°	519.6	516.0	515.9	510.8	510.8
47.5°	481.6	478.9	478.1	473.9	473.8
50°	455.4	453.2	452.5	448.8	448.1
52.5°	427.9	426.9	424.4	421.4	421.2
55°	385.3	383.9	380.2	378.0	377.3
57.5°	339.1	336.2	332.0	328.8	329.4
60°	305.8	302.9	297.0	295.6	295.6
62.5°	273.7	270.2	264.3	262.3	263.4
65°	227.7	223.4	218.2	216.8	217.5
67.5°	185.9	182.1	176.5	176.4	175.9
70°	159.1	156.9	152.5	152.5	152.5
72.5°	135.2	134.2	130.9	130.9	130.3
75°	103.6	103.6	102.2	101.4	100.7
77.5°	77.6	77.9	77.2	76.5	75.2
80°	61.3	62.7	62.0	61.3	60.6
82.5°	46.1	47.5	47.4	46.1	46.0
85°	24.1	26.2	26.3	26.3	26.3
87.5°	6.4	8.7	9.3	9.4	9.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.2	91.2	211.5	61.6	46.4
95°	55.9	221.9	997.3	345.2	212.8
97.5°	102.7	259.9	1535.9	1099.1	753.1
100°	135.4	282.5	1652.8	1674.2	1289.6
102.5°	171.5	306.9	1627.1	2143.0	1807.2
105°	227.8	345.5	1493.8	2638.6	2508.3
107.5°	285.0	390.5	1338.2	2778.3	2894.3
110°	324.6	423.3	1248.8	2724.8	2985.4

TEST NUMBER: P523937

CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	362.4	456.1	1188.6	2598.4	2970.0
115°	423.4	511.7	1132.7	2399.6	2817.8
117.5°	477.2	560.0	1099.6	2182.2	2625.2
120°	520.1	589.5	1096.2	2058.0	2482.5
122.5°	554.5	623.9	1087.6	1949.0	2343.2
125°	597.5	662.7	1081.1	1794.1	2145.0
127.5°	644.4	705.3	1077.7	1701.5	1990.7
130°	668.4	729.4	1072.5	1637.1	1889.3
132.5°	694.2	753.5	1072.5	1586.8	1818.8
135°	730.8	791.7	1068.2	1515.5	1713.0
137.5°	765.2	824.4	1067.8	1455.1	1625.8
140°	791.0	851.9	1066.1	1405.1	1569.0
142.5°	820.2	871.0	1071.2	1365.2	1512.3
145°	861.9	906.0	1076.8	1311.6	1429.3
147.5°	897.6	940.4	1086.3	1257.5	1359.2
150°	928.5	957.9	1089.7	1239.6	1311.1
152.5°	952.6	983.7	1093.2	1215.5	1281.9
155°	984.4	1007.5	1102.6	1185.4	1233.7
157.5°	1023.9	1037.8	1104.8	1171.7	1206.2
160°	1044.6	1055.1	1113.4	1161.3	1190.7
162.5°	1056.6	1068.8	1115.1	1152.6	1175.3
165°	1087.6	1091.8	1115.5	1139.5	1156.3
167.5°	1108.6	1104.8	1125.4	1136.3	1143.0
170°	1115.5	1113.4	1122.0	1124.3	1132.7
172.5°	1131.0	1123.8	1127.1	1120.8	1127.5
175°	1139.2	1132.8	1128.4	1121.8	1113.4
177.5°	1142.6	1132.5	1127.1	1120.3	1122.0
180°	1130.6	1130.6	1130.6	1130.6	1130.6

(END OF REPORT)