

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523754

Luminaire Tested: **SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523754  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (5000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7555.0 lumens  
Efficiency: N/A  
Efficacy: 114.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523754  
CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (5000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523754

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (5000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	29	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14912	14912	14912
5°	15021	14929	14878
10°	14996	14890	14824
15°	14897	14816	14734
20°	14798	14715	14604
25°	14623	14522	14377
30°	14351	14277	14096
35°	13976	13881	13705
40°	13529	13443	13291
45°	13160	13067	12938
50°	12687	12607	12485
55°	12030	11871	11781
60°	10952	10638	10586
65°	9649	9245	9215
70°	8330	7987	7987
75°	7169	7069	6969
80°	6323	6397	6248
85°	4944	5399	5399



TEST NUMBER: P523754

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (5000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.8	2.0
10°-20°	436.4	5.8
20°-30°	653.7	8.7
30°-40°	766.7	10.1
40°-50°	769.1	10.2
50°-60°	656.1	8.7
60°-70°	427.9	5.7
70°-80°	214.7	2.8
80°-90°	59.4	0.8
90°-100°	250.8	3.3
100°-110°	713.5	9.4
110°-120°	683.6	9.0
120°-130°	541.0	7.2
130°-140°	434.3	5.7
140°-150°	340.0	4.5
150°-160°	248.8	3.3
160°-170°	154.1	2.0
170°-180°	52.3	0.7
0°-30°	1242.9	16.5
0°-40°	2009.6	26.6
0°-60°	3434.8	45.5
0°-90°	4136.8	54.8
90°-120°	1647.8	21.8
90°-150°	2963.1	39.2
90°-180°	3418.0	45.2
0°-180°	7555.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1616	1616	1616	1616	1616	
5°	1622	1607	1612	1606	1606	154
15°	1560	1544	1551	1545	1543	440
25°	1436	1420	1426	1414	1412	660
35°	1241	1228	1232	1218	1217	775
45°	1009	1002	1002	992	992	777
55°	748	745	738	734	732	665
65°	442	434	424	421	422	441
75°	201	201	198	197	196	218
85°	47	51	51	51	51	55
90°	0	0	0	0	0	3
95°	27	108	485	168	104	31
105°	111	168	727	1284	1221	117
115°	206	249	551	1168	1372	203
125°	291	322	526	873	1044	260
135°	356	385	520	738	834	274
145°	420	441	524	638	696	262
155°	479	490	537	577	600	221
165°	529	531	543	555	563	149
175°	554	551	549	546	542	53
180°	550	550	550	550	550	

TEST NUMBER: P523754

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1616.3	1616.3	1616.3	1616.3	1616.3
2.5°	1626.5	1613.2	1616.3	1613.9	1607.2
5°	1621.9	1606.7	1612.0	1606.4	1606.4
7.5°	1610.9	1594.3	1599.6	1593.9	1593.6
10°	1600.7	1584.1	1589.4	1583.7	1582.3
12.5°	1586.0	1569.3	1575.8	1569.0	1568.7
15°	1559.6	1544.4	1551.1	1545.4	1542.6
17.5°	1529.9	1513.2	1521.4	1513.4	1512.3
20°	1507.2	1490.6	1498.7	1487.4	1487.4
22.5°	1480.0	1463.4	1472.6	1457.9	1457.9
25°	1436.4	1419.8	1426.5	1413.7	1412.3
27.5°	1384.5	1368.2	1375.2	1360.7	1360.5
30°	1347.1	1331.9	1340.1	1324.4	1323.1
32.5°	1306.3	1292.2	1298.1	1282.5	1281.1
35°	1240.9	1228.4	1232.4	1218.2	1216.8
37.5°	1172.1	1159.3	1163.8	1151.6	1151.1
40°	1123.3	1115.0	1116.2	1106.3	1103.5
42.5°	1078.0	1068.6	1069.8	1059.8	1059.3
45°	1008.6	1001.7	1001.5	991.6	991.6
47.5°	934.9	929.7	928.1	919.9	919.6
50°	883.9	879.8	878.3	871.1	869.8
52.5°	830.7	828.7	823.9	817.9	817.6
55°	747.9	745.2	738.0	733.7	732.4
57.5°	658.1	652.6	644.5	638.3	639.4
60°	593.5	588.0	576.5	573.7	573.7
62.5°	531.2	524.6	513.1	509.2	511.4
65°	442.0	433.7	423.5	420.7	422.1
67.5°	360.9	353.5	342.5	342.5	341.4
70°	308.8	304.7	296.1	296.1	296.1
72.5°	262.3	260.4	254.1	254.1	253.0
75°	201.1	201.1	198.3	196.9	195.5
77.5°	150.7	151.3	149.9	148.4	145.9
80°	119.0	121.8	120.4	119.0	117.6
82.5°	89.5	92.3	92.1	89.5	89.2
85°	46.7	50.9	51.0	51.0	51.0
87.5°	12.5	16.9	18.1	18.2	19.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.4	44.4	102.9	30.0	22.6
95°	27.2	108.0	485.4	168.0	103.6
97.5°	50.0	126.5	747.6	535.0	366.6
100°	65.9	137.5	804.5	814.9	627.7
102.5°	83.5	149.4	792.0	1043.1	879.6
105°	110.9	168.2	727.1	1284.3	1220.9
107.5°	138.7	190.1	651.3	1352.3	1408.8
110°	158.0	206.0	607.8	1326.3	1453.1

TEST NUMBER: P523754

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	222.0	578.5	1264.7	1445.6
115°	206.1	249.1	551.3	1168.0	1371.5
117.5°	232.2	272.6	535.2	1062.2	1277.8
120°	253.2	286.9	533.5	1001.7	1208.3
122.5°	269.9	303.7	529.4	948.6	1140.5
125°	290.8	322.5	526.2	873.2	1044.1
127.5°	313.6	343.3	524.5	828.2	969.0
130°	325.4	355.0	522.0	796.8	919.6
132.5°	337.9	366.8	522.0	772.3	885.3
135°	355.7	385.4	519.9	737.6	833.8
137.5°	372.4	401.3	519.7	708.3	791.3
140°	385.0	414.7	518.9	683.9	763.7
142.5°	399.2	424.0	521.4	664.5	736.1
145°	419.5	441.0	524.1	638.4	695.7
147.5°	436.9	457.7	528.7	612.1	661.6
150°	451.9	466.3	530.4	603.4	638.2
152.5°	463.7	478.8	532.1	591.6	623.9
155°	479.1	490.4	536.7	577.0	600.5
157.5°	498.4	505.1	537.7	570.3	587.1
160°	508.4	513.6	541.9	565.3	579.6
162.5°	514.3	520.2	542.8	561.0	572.0
165°	529.4	531.4	543.0	554.7	562.8
167.5°	539.6	537.8	547.8	553.1	556.4
170°	543.0	541.9	546.1	547.2	551.3
172.5°	550.5	547.0	548.6	545.5	548.8
175°	554.5	551.4	549.2	546.0	541.9
177.5°	556.1	551.2	548.6	545.3	546.1
180°	550.3	550.3	550.3	550.3	550.3

(END OF REPORT)