

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523970

Luminaire Tested: **SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523970
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11121.8 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523970
CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523970

CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	33	29	32	28	25	25	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17266	17266	17266
5°	17393	17286	17225
10°	17364	17240	17163
15°	17248	17155	17060
20°	17134	17038	16908
25°	16930	16813	16646
30°	16617	16530	16320
35°	16183	16071	15869
40°	15664	15566	15389
45°	15237	15130	14980
50°	14689	14596	14454
55°	13930	13745	13640
60°	12680	12317	12258
65°	11171	10706	10671
70°	9644	9247	9247
75°	8302	8185	8067
80°	7322	7407	7231
85°	5727	6246	6246



TEST NUMBER: P523970

CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.0	1.6
10°-20°	505.3	4.5
20°-30°	756.8	6.8
30°-40°	887.7	8.0
40°-50°	890.5	8.0
50°-60°	759.7	6.8
60°-70°	495.4	4.5
70°-80°	248.5	2.2
80°-90°	68.8	0.6
90°-100°	464.5	4.2
100°-110°	1321.7	11.9
110°-120°	1266.3	11.4
120°-130°	1002.2	9.0
130°-140°	804.5	7.2
140°-150°	629.8	5.7
150°-160°	460.8	4.1
160°-170°	285.4	2.6
170°-180°	96.9	0.9
0°-30°	1439.1	12.9
0°-40°	2326.8	20.9
0°-60°	3977.0	35.8
0°-90°	4789.7	43.1
90°-120°	3052.5	27.4
90°-150°	5489.0	49.4
90°-180°	6332.0	56.9
0°-180°	11121.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1871	1871	1871	1871	1871	
5°	1878	1860	1866	1860	1860	178
15°	1806	1788	1796	1789	1786	509
25°	1663	1644	1652	1637	1635	765
35°	1437	1422	1427	1410	1409	897
45°	1168	1160	1160	1148	1148	899
55°	866	863	854	850	848	770
65°	512	502	490	487	489	511
75°	233	233	230	228	226	253
85°	54	59	59	59	59	64
90°	0	0	0	0	0	4
95°	50	200	899	311	192	58
105°	205	312	1347	2379	2262	217
115°	382	461	1021	2164	2541	376
125°	539	598	975	1618	1934	482
135°	659	714	963	1366	1545	508
145°	777	817	971	1183	1289	485
155°	888	908	994	1069	1112	410
165°	981	984	1006	1028	1043	276
175°	1027	1022	1018	1012	1004	97
180°	1019	1019	1019	1019	1019	



TEST NUMBER: P523970

CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1871.4	1871.4	1871.4	1871.4	1871.4
2.5°	1883.2	1867.8	1871.4	1868.6	1860.9
5°	1878.0	1860.3	1866.5	1859.9	1859.9
7.5°	1865.2	1845.9	1852.0	1845.5	1845.2
10°	1853.4	1834.1	1840.2	1833.6	1832.0
12.5°	1836.3	1817.1	1824.5	1816.6	1816.3
15°	1805.8	1788.2	1796.0	1789.3	1786.1
17.5°	1771.3	1752.1	1761.5	1752.3	1751.0
20°	1745.1	1725.9	1735.3	1722.1	1722.1
22.5°	1713.6	1694.4	1705.1	1688.0	1688.0
25°	1663.1	1643.9	1651.6	1636.8	1635.2
27.5°	1603.1	1584.1	1592.2	1575.5	1575.2
30°	1559.8	1542.1	1551.6	1533.5	1531.9
32.5°	1512.5	1496.2	1503.0	1484.9	1483.3
35°	1436.8	1422.3	1426.9	1410.5	1408.9
37.5°	1357.0	1342.3	1347.5	1333.4	1332.8
40°	1300.6	1291.0	1292.4	1280.9	1277.7
42.5°	1248.1	1237.2	1238.6	1227.1	1226.5
45°	1167.8	1159.8	1159.6	1148.1	1148.1
47.5°	1082.5	1076.4	1074.6	1065.1	1064.8
50°	1023.4	1018.6	1016.9	1008.6	1007.0
52.5°	961.8	959.5	953.9	947.0	946.7
55°	866.0	862.8	854.5	849.6	848.0
57.5°	762.0	755.6	746.3	739.1	740.4
60°	687.2	680.8	667.5	664.3	664.3
62.5°	615.1	607.4	594.1	589.5	592.1
65°	511.7	502.1	490.4	487.2	488.8
67.5°	417.9	409.2	396.6	396.6	395.3
70°	357.5	352.7	342.8	342.8	342.8
72.5°	303.8	301.5	294.2	294.2	292.9
75°	232.9	232.9	229.6	227.9	226.3
77.5°	174.5	175.2	173.5	171.8	168.9
80°	137.8	141.0	139.4	137.7	136.1
82.5°	103.7	106.9	106.6	103.6	103.3
85°	54.1	58.9	59.0	59.0	59.0
87.5°	14.4	19.6	21.0	21.0	22.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.5	82.2	190.7	55.5	41.9
95°	50.4	200.1	899.2	311.2	191.9
97.5°	92.6	234.4	1384.9	991.0	679.1
100°	122.1	254.7	1490.3	1509.6	1162.8
102.5°	154.7	276.7	1467.1	1932.3	1629.5
105°	205.4	311.5	1346.9	2379.1	2261.7
107.5°	257.0	352.1	1206.6	2505.1	2609.7
110°	292.6	381.7	1126.0	2456.9	2691.9

TEST NUMBER: P523970

CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	326.7	411.3	1071.7	2342.9	2677.9
115°	381.8	461.4	1021.3	2163.6	2540.7
117.5°	430.2	504.9	991.5	1967.6	2367.1
120°	469.0	531.5	988.4	1855.6	2238.4
122.5°	500.0	562.5	980.6	1757.3	2112.8
125°	538.8	597.5	974.8	1617.7	1934.1
127.5°	581.0	636.0	971.7	1534.2	1795.0
130°	602.7	657.7	967.1	1476.1	1703.5
132.5°	626.0	679.4	967.1	1430.7	1639.9
135°	658.9	713.9	963.2	1366.5	1544.6
137.5°	689.9	743.4	962.8	1312.0	1465.9
140°	713.2	768.1	961.3	1266.9	1414.7
142.5°	739.5	785.4	965.9	1230.9	1363.6
145°	777.1	816.9	970.9	1182.7	1288.8
147.5°	809.3	848.0	979.5	1133.9	1225.6
150°	837.2	863.7	982.6	1117.8	1182.2
152.5°	858.9	887.0	985.7	1095.9	1155.8
155°	887.6	908.5	994.2	1068.8	1112.4
157.5°	923.3	935.8	996.1	1056.5	1087.6
160°	941.9	951.3	1003.9	1047.1	1073.7
162.5°	952.7	963.7	1005.4	1039.2	1059.7
165°	980.6	984.4	1005.8	1027.5	1042.6
167.5°	999.6	996.2	1014.7	1024.6	1030.6
170°	1005.8	1003.9	1011.6	1013.7	1021.3
172.5°	1019.8	1013.3	1016.3	1010.6	1016.7
175°	1027.1	1021.5	1017.5	1011.5	1003.9
177.5°	1030.2	1021.1	1016.3	1010.1	1011.6
180°	1019.4	1019.4	1019.4	1019.4	1019.4

(END OF REPORT)