

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523972

Luminaire Tested: **SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523972
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11624.8 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 107
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523972

CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523972

CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	33	29	32	28	25	25	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18046	18046	18046
5°	18179	18068	18004
10°	18149	18019	17940
15°	18028	17930	17832
20°	17909	17807	17673
25°	17696	17574	17400
30°	17368	17277	17058
35°	16914	16798	16586
40°	16373	16270	16083
45°	15926	15814	15657
50°	15354	15256	15108
55°	14560	14367	14256
60°	13254	12874	12812
65°	11677	11191	11153
70°	10081	9665	9665
75°	8677	8555	8434
80°	7651	7741	7561
85°	5992	6531	6531



TEST NUMBER: P523972

CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.0	1.6
10°-20°	528.1	4.5
20°-30°	791.1	6.8
30°-40°	927.9	8.0
40°-50°	930.8	8.0
50°-60°	794.0	6.8
60°-70°	517.8	4.5
70°-80°	259.8	2.2
80°-90°	71.9	0.6
90°-100°	485.5	4.2
100°-110°	1381.5	11.9
110°-120°	1323.6	11.4
120°-130°	1047.6	9.0
130°-140°	840.8	7.2
140°-150°	658.3	5.7
150°-160°	481.7	4.1
160°-170°	298.3	2.6
170°-180°	101.2	0.9
0°-30°	1504.1	12.9
0°-40°	2432.0	20.9
0°-60°	4156.8	35.8
0°-90°	5006.3	43.1
90°-120°	3190.6	27.4
90°-150°	5737.2	49.4
90°-180°	6618.0	56.9
0°-180°	11624.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1956	1956	1956	1956	1956	
5°	1963	1944	1951	1944	1944	186
15°	1887	1869	1877	1870	1867	532
25°	1738	1718	1726	1711	1709	799
35°	1502	1487	1491	1474	1473	938
45°	1221	1212	1212	1200	1200	940
55°	905	902	893	888	886	804
65°	535	525	513	509	511	534
75°	243	243	240	238	237	264
85°	57	62	62	62	62	66
90°	0	0	0	0	0	4
95°	53	209	940	325	200	60
105°	215	326	1408	2487	2364	227
115°	399	482	1068	2262	2656	393
125°	563	624	1019	1691	2022	504
135°	689	746	1007	1428	1614	531
145°	812	854	1015	1236	1347	507
155°	928	950	1039	1117	1163	429
165°	1025	1029	1051	1074	1090	288
175°	1074	1068	1064	1057	1049	102
180°	1066	1066	1066	1066	1066	

TEST NUMBER: P523972

CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1956.0	1956.0	1956.0	1956.0	1956.0
2.5°	1968.4	1952.3	1956.0	1953.1	1945.0
5°	1962.9	1944.4	1950.9	1944.0	1944.0
7.5°	1949.5	1929.4	1935.8	1928.9	1928.6
10°	1937.2	1917.0	1923.4	1916.6	1914.9
12.5°	1919.3	1899.2	1907.0	1898.8	1898.4
15°	1887.4	1869.0	1877.2	1870.2	1866.9
17.5°	1851.4	1831.3	1841.2	1831.5	1830.2
20°	1824.0	1803.9	1813.7	1800.0	1800.0
22.5°	1791.1	1771.0	1782.2	1764.4	1764.4
25°	1738.3	1718.2	1726.3	1710.8	1709.2
27.5°	1675.6	1655.8	1664.2	1646.8	1646.4
30°	1630.3	1611.9	1621.7	1602.8	1601.2
32.5°	1580.9	1563.8	1571.0	1552.1	1550.4
35°	1501.7	1486.6	1491.4	1474.3	1472.6
37.5°	1418.4	1403.0	1408.5	1393.7	1393.0
40°	1359.4	1349.4	1350.9	1338.8	1335.4
42.5°	1304.6	1293.2	1294.6	1282.6	1282.0
45°	1220.6	1212.2	1212.0	1200.0	1200.0
47.5°	1131.4	1125.1	1123.2	1113.3	1112.9
50°	1069.7	1064.7	1062.9	1054.3	1052.6
52.5°	1005.3	1002.9	997.0	989.8	989.5
55°	905.2	901.8	893.2	888.0	886.3
57.5°	796.5	789.8	780.0	772.5	773.8
60°	718.3	711.6	697.7	694.3	694.3
62.5°	642.9	634.8	620.9	616.2	618.9
65°	534.9	524.8	512.6	509.2	510.9
67.5°	436.8	427.8	414.5	414.5	413.1
70°	373.7	368.7	358.3	358.3	358.3
72.5°	317.5	315.1	307.5	307.5	306.2
75°	243.4	243.4	240.0	238.2	236.6
77.5°	182.4	183.1	181.4	179.6	176.6
80°	144.0	147.4	145.7	144.0	142.3
82.5°	108.3	111.7	111.4	108.3	108.0
85°	56.6	61.6	61.7	61.7	61.7
87.5°	15.1	20.4	21.9	22.0	23.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.2	85.9	199.3	58.0	43.8
95°	52.7	209.1	939.9	325.3	200.5
97.5°	96.8	245.0	1447.5	1035.8	709.8
100°	127.6	266.3	1557.7	1577.8	1215.4
102.5°	161.6	289.2	1533.4	2019.7	1703.2
105°	214.7	325.6	1407.8	2486.7	2363.9
107.5°	268.6	368.0	1261.2	2618.4	2727.7
110°	305.9	399.0	1176.9	2568.0	2813.6

TEST NUMBER: P523972

CATALOG NUMBER: SQ4-PP3-150U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	341.5	429.9	1120.2	2448.9	2799.0
115°	399.1	482.2	1067.5	2261.5	2655.6
117.5°	449.7	527.7	1036.3	2056.6	2474.1
120°	490.2	555.6	1033.1	1939.5	2339.6
122.5°	522.6	588.0	1025.0	1836.8	2208.4
125°	563.1	624.5	1018.9	1690.8	2021.6
127.5°	607.3	664.7	1015.7	1603.6	1876.1
130°	630.0	687.4	1010.8	1542.9	1780.5
132.5°	654.3	710.1	1010.8	1495.4	1714.1
135°	688.7	746.2	1006.7	1428.3	1614.4
137.5°	721.1	777.0	1006.3	1371.4	1532.2
140°	745.4	802.9	1004.7	1324.2	1478.7
142.5°	773.0	820.9	1009.6	1286.6	1425.2
145°	812.3	853.9	1014.8	1236.1	1347.0
147.5°	845.9	886.3	1023.8	1185.2	1281.0
150°	875.1	902.8	1027.0	1168.3	1235.6
152.5°	897.8	927.1	1030.2	1145.5	1208.1
155°	927.7	949.5	1039.2	1117.2	1162.7
157.5°	965.0	978.1	1041.2	1104.3	1136.8
160°	984.5	994.4	1049.3	1094.5	1122.2
162.5°	995.8	1007.3	1050.9	1086.2	1107.6
165°	1025.0	1028.9	1051.3	1073.9	1089.8
167.5°	1044.8	1041.3	1060.6	1070.9	1077.2
170°	1051.3	1049.3	1057.4	1059.6	1067.5
172.5°	1065.9	1059.2	1062.2	1056.3	1062.6
175°	1073.6	1067.6	1063.5	1057.2	1049.3
177.5°	1076.8	1067.3	1062.2	1055.8	1057.4
180°	1065.5	1065.5	1065.5	1065.5	1065.5

(END OF REPORT)