

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523768

Luminaire Tested: **SQ4-PP3-075U-125D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523768
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-125D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8779.0 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 79.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523768

CATALOG NUMBER: SQ4-PP3-075U-125D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523768

CATALOG NUMBER: SQ4-PP3-075U-125D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61	
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56	56	56	56	52	
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	50	48	48	48	48	43	
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	41	41	41	37	
4	77	66	58	52	71	62	55	49	54	49	44	48	43	40	41	38	35	35	35	35	32	
5	70	59	51	44	66	55	48	42	49	43	38	43	38	35	37	34	31	31	31	31	28	
6	65	53	45	39	61	50	42	37	44	38	34	39	34	30	34	30	27	27	27	27	24	
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	24	24	24	22	
8	56	43	36	30	52	41	34	29	37	31	26	32	28	24	28	24	22	22	22	22	19	
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	20	20	20	17	
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	24	20	18	18	18	18	16	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19149	19149	19149
5°	19290	19171	19104
10°	19257	19120	19035
15°	19129	19025	18921
20°	19002	18895	18752
25°	18777	18647	18461
30°	18429	18333	18099
35°	17947	17824	17599
40°	17373	17264	17066
45°	16898	16779	16614
50°	16293	16188	16031
55°	15448	15244	15127
60°	14064	13660	13594
65°	12389	11874	11835
70°	10696	10256	10256
75°	9208	9079	8947
80°	8119	8214	8023
85°	6352	6934	6934



TEST NUMBER: P523768

CATALOG NUMBER: SQ4-PP3-075U-125D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.3	2.2
10°-20°	560.4	6.4
20°-30°	839.4	9.6
30°-40°	984.5	11.2
40°-50°	987.6	11.2
50°-60°	842.5	9.6
60°-70°	549.5	6.3
70°-80°	275.7	3.1
80°-90°	76.3	0.9
90°-100°	254.3	2.9
100°-110°	723.6	8.2
110°-120°	693.3	7.9
120°-130°	548.7	6.3
130°-140°	440.5	5.0
140°-150°	344.8	3.9
150°-160°	252.3	2.9
160°-170°	156.3	1.8
170°-180°	53.0	0.6
0°-30°	1596.0	18.2
0°-40°	2580.5	29.4
0°-60°	4410.6	50.2
0°-90°	5312.1	60.5
90°-120°	1671.3	19.0
90°-150°	3005.3	34.2
90°-180°	3467.0	39.5
0°-180°	8779.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2076	2076	2076	2076	2076	
5°	2083	2063	2070	2063	2063	198
15°	2003	1983	1992	1984	1981	565
25°	1844	1823	1832	1815	1814	848
35°	1593	1577	1582	1564	1562	995
45°	1295	1286	1286	1273	1273	997
55°	960	957	948	942	940	854
65°	568	557	544	540	542	566
75°	258	258	255	253	251	280
85°	60	65	66	66	66	71
90°	0	0	0	0	0	3
95°	28	110	492	170	105	32
105°	112	171	737	1303	1238	119
115°	209	253	559	1185	1391	206
125°	295	327	534	886	1059	264
135°	361	391	527	748	846	278
145°	426	447	532	648	706	266
155°	486	497	544	585	609	225
165°	537	539	551	563	571	151
175°	562	559	557	554	550	53
180°	558	558	558	558	558	

TEST NUMBER: P523768

CATALOG NUMBER: SQ4-PP3-075U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2075.5	2075.5	2075.5	2075.5	2075.5
2.5°	2088.6	2071.5	2075.5	2072.4	2063.8
5°	2082.8	2063.2	2070.0	2062.7	2062.7
7.5°	2068.6	2047.2	2054.0	2046.7	2046.4
10°	2055.5	2034.1	2040.9	2033.6	2031.8
12.5°	2036.5	2015.2	2023.5	2014.7	2014.4
15°	2002.7	1983.2	1991.8	1984.4	1980.9
17.5°	1964.5	1943.2	1953.6	1943.4	1942.0
20°	1935.4	1914.1	1924.5	1909.9	1909.9
22.5°	1900.5	1879.1	1891.0	1872.1	1872.1
25°	1844.5	1823.1	1831.7	1815.3	1813.5
27.5°	1777.9	1756.9	1765.9	1747.3	1747.0
30°	1729.9	1710.3	1720.8	1700.7	1698.9
32.5°	1677.5	1659.3	1666.9	1646.9	1645.1
35°	1593.4	1577.4	1582.5	1564.3	1562.5
37.5°	1505.0	1488.7	1494.5	1478.8	1478.1
40°	1442.5	1431.8	1433.4	1420.6	1417.0
42.5°	1384.3	1372.2	1373.7	1361.0	1360.2
45°	1295.1	1286.2	1286.0	1273.3	1273.3
47.5°	1200.5	1193.8	1191.8	1181.2	1180.9
50°	1135.1	1129.7	1127.8	1118.6	1116.9
52.5°	1066.7	1064.2	1057.9	1050.3	1049.9
55°	960.4	956.9	947.7	942.2	940.4
57.5°	845.1	838.0	827.6	819.7	821.1
60°	762.2	755.0	740.3	736.7	736.7
62.5°	682.1	673.6	658.8	653.8	656.7
65°	567.5	556.9	543.9	540.3	542.1
67.5°	463.5	453.9	439.8	439.8	438.4
70°	396.5	391.2	380.2	380.2	380.2
72.5°	336.9	334.4	326.3	326.3	324.9
75°	258.3	258.3	254.7	252.8	251.0
77.5°	193.5	194.3	192.4	190.6	187.4
80°	152.8	156.4	154.6	152.8	151.0
82.5°	115.0	118.5	118.2	115.0	114.6
85°	60.0	65.4	65.5	65.5	65.5
87.5°	16.0	21.7	23.3	23.3	24.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.5	45.0	104.4	30.4	22.9
95°	27.6	109.5	492.3	170.4	105.0
97.5°	50.7	128.3	758.2	542.6	371.8
100°	66.8	139.5	816.0	826.5	636.6
102.5°	84.7	151.5	803.2	1057.9	892.1
105°	112.5	170.6	737.4	1302.6	1238.3
107.5°	140.7	192.8	660.6	1371.6	1428.8
110°	160.2	209.0	616.5	1345.2	1473.8

TEST NUMBER: P523768

CATALOG NUMBER: SQ4-PP3-075U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	178.9	225.2	586.8	1282.8	1466.2
115°	209.0	252.6	559.2	1184.6	1391.1
117.5°	235.6	276.4	542.8	1077.3	1296.0
120°	256.8	291.0	541.1	1016.0	1225.5
122.5°	273.8	308.0	536.9	962.1	1156.8
125°	295.0	327.1	533.7	885.7	1058.9
127.5°	318.1	348.2	532.0	840.0	982.8
130°	330.0	360.1	529.5	808.2	932.7
132.5°	342.7	372.0	529.5	783.3	897.9
135°	360.8	390.9	527.4	748.1	845.7
137.5°	377.7	407.0	527.1	718.4	802.6
140°	390.5	420.6	526.3	693.7	774.6
142.5°	404.9	430.0	528.8	673.9	746.6
145°	425.5	447.3	531.6	647.5	705.6
147.5°	443.1	464.3	536.3	620.8	671.0
150°	458.4	472.9	538.0	612.0	647.3
152.5°	470.3	485.6	539.7	600.0	632.8
155°	486.0	497.4	544.3	585.2	609.1
157.5°	505.5	512.3	545.4	578.5	595.5
160°	515.7	520.9	549.6	573.3	587.8
162.5°	521.6	527.6	550.5	569.0	580.2
165°	536.9	539.0	550.7	562.6	570.9
167.5°	547.3	545.4	555.6	561.0	564.3
170°	550.7	549.7	553.9	555.0	559.2
172.5°	558.3	554.8	556.4	553.3	556.6
175°	562.4	559.3	557.1	553.8	549.6
177.5°	564.1	559.1	556.4	553.0	553.9
180°	558.1	558.1	558.1	558.1	558.1

(END OF REPORT)