

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523782

Luminaire Tested: **SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523782
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2151.4 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 20.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523782

CATALOG NUMBER: SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523782

CATALOG NUMBER: SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7756	7756	7756
5°	7812	7765	7737
10°	7799	7744	7709
15°	7747	7705	7663
20°	7696	7652	7594
25°	7604	7552	7477
30°	7464	7424	7331
35°	7268	7219	7127
40°	7036	6992	6912
45°	6844	6795	6729
50°	6598	6555	6492
55°	6257	6174	6127
60°	5696	5532	5506
65°	5017	4809	4792
70°	4332	4154	4154
75°	3729	3675	3625
80°	3289	3326	3246
85°	2572	2805	2805



TEST NUMBER: P523782

CATALOG NUMBER: SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.5	3.7
10°-20°	227.0	10.5
20°-30°	339.9	15.8
30°-40°	398.7	18.5
40°-50°	400.0	18.6
50°-60°	341.2	15.9
60°-70°	222.5	10.3
70°-80°	111.6	5.2
80°-90°	30.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.4	30.0
0°-40°	1045.1	48.6
0°-60°	1786.3	83.0
0°-90°	2151.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2151.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	844	836	838	835	835	80
15°	811	803	807	804	802	229
25°	747	738	742	735	734	343
35°	645	639	641	634	633	403
45°	524	521	521	516	516	404
55°	389	388	384	382	381	346
65°	230	226	220	219	220	229
75°	105	105	103	102	102	113
85°	24	26	26	26	26	29
90°	0	0	0	0	0	



TEST NUMBER: P523782

CATALOG NUMBER: SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	840.6	840.6	840.6	840.6	840.6
2.5°	845.9	838.9	840.6	839.3	835.8
5°	843.5	835.6	838.4	835.4	835.4
7.5°	837.8	829.1	831.9	828.9	828.8
10°	832.5	823.8	826.6	823.6	822.9
12.5°	824.8	816.2	819.5	816.0	815.8
15°	811.1	803.2	806.7	803.7	802.3
17.5°	795.6	787.0	791.2	787.1	786.5
20°	783.8	775.2	779.4	773.5	773.5
22.5°	769.7	761.0	765.9	758.2	758.2
25°	747.0	738.4	741.8	735.2	734.5
27.5°	720.0	711.5	715.2	707.7	707.5
30°	700.6	692.7	696.9	688.8	688.1
32.5°	679.4	672.0	675.1	667.0	666.3
35°	645.3	638.9	640.9	633.5	632.8
37.5°	609.5	602.9	605.3	598.9	598.6
40°	584.2	579.9	580.5	575.3	573.9
42.5°	560.6	555.7	556.3	551.2	550.9
45°	524.5	520.9	520.8	515.7	515.7
47.5°	486.2	483.5	482.7	478.4	478.3
50°	459.7	457.5	456.7	453.0	452.3
52.5°	432.0	431.0	428.5	425.4	425.2
55°	389.0	387.5	383.8	381.6	380.9
57.5°	342.3	339.4	335.2	332.0	332.5
60°	308.7	305.8	299.8	298.4	298.4
62.5°	276.3	272.8	266.8	264.8	265.9
65°	229.8	225.5	220.3	218.8	219.5
67.5°	187.7	183.8	178.1	178.1	177.5
70°	160.6	158.4	154.0	154.0	154.0
72.5°	136.4	135.4	132.2	132.1	131.6
75°	104.6	104.6	103.1	102.4	101.7
77.5°	78.4	78.7	77.9	77.2	75.9
80°	61.9	63.3	62.6	61.9	61.1
82.5°	46.6	48.0	47.9	46.6	46.4
85°	24.3	26.5	26.5	26.5	26.5
87.5°	6.5	8.8	9.4	9.4	10.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)