

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561784

Luminaire Tested: **SQ4-PR1-025U-050D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561784  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-025U-050D-92765-1D-UNV-STD-W-4 (6500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4213.2 lumens  
Efficiency: N/A  
Efficacy: 122.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 34.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561784

CATALOG NUMBER: SQ4-PR1-025U-050D-92765-1D-UNV-STD-W-4 (6500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561784

CATALOG NUMBER: SQ4-PR1-025U-050D-92765-1D-UNV-STD-W-4 (6500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49	43				43
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37				37
3	82	73	66	60	75	67	61	56	58	53	49	49	45	42	40	38	36	31				31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27				27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	33	29	27	24				24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21				21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	19				19
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	25	22	19	17				17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15				15
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7893	7893	7893
5°	7964	7903	7862
10°	7939	7884	7842
15°	7904	7854	7812
20°	7864	7813	7755
25°	7809	7756	7667
30°	7725	7669	7560
35°	7610	7544	7436
40°	7437	7358	7224
45°	7135	7009	6864
50°	6600	6440	6314
55°	5760	5630	5511
60°	4855	4812	4718
65°	4198	4216	4183
70°	3858	3876	3876
75°	3704	3704	3729
80°	3485	3523	3485
85°	2805	3123	3123



TEST NUMBER: P561784

CATALOG NUMBER: SQ4-PR1-025U-050D-92765-1D-UNV-STD-W-4 (6500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.9	1.9
10°-20°	231.5	5.5
20°-30°	349.1	8.3
30°-40°	416.0	9.9
40°-50°	410.1	9.7
50°-60°	313.4	7.4
60°-70°	194.0	4.6
70°-80°	110.2	2.6
80°-90°	33.5	0.8
90°-100°	152.2	3.6
100°-110°	433.0	10.3
110°-120°	414.9	9.8
120°-130°	328.4	7.8
130°-140°	263.6	6.3
140°-150°	206.3	4.9
150°-160°	151.0	3.6
160°-170°	93.5	2.2
170°-180°	31.7	0.8
0°-30°	661.5	15.7
0°-40°	1077.5	25.6
0°-60°	1801.0	42.7
0°-90°	2138.7	50.8
90°-120°	1000.1	23.7
90°-150°	1798.3	42.7
90°-180°	2075.0	49.3
0°-180°	4213.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	856	856	856	856	856	
5°	860	850	853	850	849	82
15°	828	819	822	819	818	234
25°	767	758	762	754	753	353
35°	676	668	670	661	660	422
45°	547	540	537	528	526	419
55°	358	352	350	344	343	321
65°	192	191	193	192	192	195
75°	104	104	104	105	105	110
85°	26	28	30	30	30	31
90°	0	0	0	0	0	2
95°	16	66	295	102	63	19
105°	67	102	441	779	741	71
115°	125	151	335	709	832	123
125°	176	196	319	530	634	158
135°	216	234	316	448	506	167
145°	255	268	318	388	422	159
155°	291	298	326	350	364	134
165°	321	322	330	337	342	90
175°	336	335	333	331	329	32
180°	334	334	334	334	334	



TEST NUMBER: P561784

CATALOG NUMBER: SQ4-PR1-025U-050D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	855.5	855.5	855.5	855.5	855.5
2.5°	860.8	853.3	855.5	853.6	849.6
5°	859.9	850.5	853.3	850.3	848.9
7.5°	853.3	844.1	846.8	843.8	843.0
10°	847.4	838.7	841.5	838.5	837.1
12.5°	840.9	831.7	835.0	831.4	830.0
15°	827.5	818.8	822.3	819.4	817.9
17.5°	812.8	803.5	807.0	803.6	801.7
20°	801.0	792.3	795.8	790.6	789.9
22.5°	788.0	779.4	782.8	775.9	775.8
25°	767.1	757.7	761.9	753.8	753.1
27.5°	742.2	733.5	737.0	728.7	727.9
30°	725.1	716.4	719.9	711.0	709.6
32.5°	705.6	697.5	700.5	691.6	690.7
35°	675.7	667.8	669.8	660.9	660.2
37.5°	641.7	634.5	635.6	625.9	625.2
40°	617.5	610.3	610.9	600.5	599.8
42.5°	591.0	583.8	583.2	572.8	572.1
45°	546.8	539.5	537.2	527.6	526.1
47.5°	496.3	489.1	484.7	476.9	475.9
50°	459.8	452.6	448.7	442.1	439.9
52.5°	420.3	413.1	409.8	403.8	401.6
55°	358.1	352.4	350.0	344.1	342.6
57.5°	299.0	295.1	294.4	288.7	288.1
60°	263.1	260.9	260.8	255.7	255.7
62.5°	232.4	230.8	232.0	228.6	228.0
65°	192.3	190.9	193.1	191.6	191.6
67.5°	160.6	160.6	162.0	161.4	161.4
70°	143.0	143.0	143.7	143.7	143.7
72.5°	127.0	126.5	128.4	128.3	127.8
75°	103.9	103.9	103.9	104.6	104.6
77.5°	80.9	81.1	81.6	81.5	80.9
80°	65.6	66.3	66.3	65.6	65.6
82.5°	50.3	51.0	51.0	50.8	50.3
85°	26.5	28.0	29.5	29.5	29.5
87.5°	7.7	10.0	11.8	11.8	11.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.1	26.9	62.5	18.2	13.7
95°	16.5	65.6	294.6	102.0	62.9
97.5°	30.3	76.8	453.7	324.7	222.5
100°	40.0	83.5	488.3	494.6	381.0
102.5°	50.7	90.6	480.6	633.0	533.8
105°	67.3	102.1	441.3	779.4	740.9
107.5°	84.2	115.4	395.3	820.7	855.0
110°	95.9	125.1	368.9	804.9	881.9

TEST NUMBER: P561784

CATALOG NUMBER: SQ4-PR1-025U-050D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	107.0	134.7	351.1	767.6	877.3
115°	125.1	151.2	334.6	708.8	832.4
117.5°	141.0	165.4	324.8	644.6	775.5
120°	153.7	174.1	323.8	607.9	733.3
122.5°	163.8	184.3	321.3	575.7	692.2
125°	176.5	195.8	319.4	530.0	633.6
127.5°	190.3	208.4	318.3	502.6	588.1
130°	197.5	215.5	316.8	483.6	558.1
132.5°	205.1	222.6	316.8	468.7	537.3
135°	215.9	233.9	315.6	447.7	506.0
137.5°	226.0	243.5	315.4	429.8	480.3
140°	233.7	251.7	314.9	415.1	463.5
142.5°	242.3	257.3	316.4	403.3	446.7
145°	254.6	267.6	318.1	387.5	422.2
147.5°	265.1	277.8	320.9	371.5	401.5
150°	274.3	283.0	321.9	366.2	387.3
152.5°	281.4	290.6	322.9	359.0	378.7
155°	290.8	297.6	325.7	350.2	364.4
157.5°	302.5	306.6	326.3	346.1	356.3
160°	308.6	311.7	328.9	343.1	351.7
162.5°	312.1	315.7	329.4	340.5	347.2
165°	321.3	322.5	329.5	336.6	341.6
167.5°	327.5	326.4	332.4	335.7	337.6
170°	329.5	328.9	331.4	332.1	334.6
172.5°	334.1	332.0	333.0	331.1	333.1
175°	336.5	334.6	333.3	331.4	328.9
177.5°	337.5	334.5	333.0	330.9	331.4
180°	334.0	334.0	334.0	334.0	334.0

(END OF REPORT)