

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561803

Luminaire Tested: **SQ4-PR1-025U-100D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561803
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-100D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5613.7 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 56.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561803
CATALOG NUMBER: SQ4-PR1-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561803

CATALOG NUMBER: SQ4-PR1-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	79	77	73	71	69	64	63	61	57
2	93	86	80	75	88	81	76	71	72	68	65	64	61	58	57	54	52	49
3	85	76	68	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	67	59	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	37	33	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13880	13880	13880
5°	14004	13897	13825
10°	13960	13864	13790
15°	13899	13813	13738
20°	13829	13740	13639
25°	13732	13639	13481
30°	13583	13487	13293
35°	13383	13266	13076
40°	13077	12938	12703
45°	12545	12325	12072
50°	11606	11326	11104
55°	10129	9901	9691
60°	8536	8464	8296
65°	7383	7412	7355
70°	6782	6817	6817
75°	6513	6513	6559
80°	6126	6195	6126
85°	4933	5483	5483



TEST NUMBER: P561803

CATALOG NUMBER: SQ4-PR1-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.3	2.5
10°-20°	407.0	7.3
20°-30°	613.9	10.9
30°-40°	731.5	13.0
40°-50°	721.2	12.8
50°-60°	551.2	9.8
60°-70°	341.1	6.1
70°-80°	193.7	3.5
80°-90°	58.9	1.0
90°-100°	135.9	2.4
100°-110°	386.8	6.9
110°-120°	370.6	6.6
120°-130°	293.3	5.2
130°-140°	235.4	4.2
140°-150°	184.3	3.3
150°-160°	134.8	2.4
160°-170°	83.5	1.5
170°-180°	28.3	0.5
0°-30°	1163.2	20.7
0°-40°	1894.7	33.8
0°-60°	3167.0	56.4
0°-90°	3760.8	67.0
90°-120°	893.2	15.9
90°-150°	1606.2	28.6
90°-180°	1853.0	33.0
0°-180°	5613.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1504	1504	1504	1504	1504	
5°	1512	1496	1500	1495	1493	143
15°	1455	1440	1446	1441	1438	411
25°	1349	1332	1340	1326	1324	621
35°	1188	1174	1178	1162	1161	742
45°	962	949	945	928	925	737
55°	630	620	616	605	602	564
65°	338	336	340	337	337	343
75°	183	183	183	184	184	193
85°	47	49	52	52	52	54
90°	0	0	0	0	0	2
95°	15	59	263	91	56	17
105°	60	91	394	696	662	64
115°	112	135	299	633	744	110
125°	158	175	285	473	566	141
135°	193	209	282	400	452	149
145°	227	239	284	346	377	142
155°	260	266	291	313	326	120
165°	287	288	294	301	305	81
175°	301	299	298	296	294	28
180°	298	298	298	298	298	

TEST NUMBER: P561803

CATALOG NUMBER: SQ4-PR1-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1504.4	1504.4	1504.4	1504.4	1504.4
2.5°	1513.7	1500.5	1504.4	1501.1	1494.0
5°	1512.1	1495.7	1500.5	1495.2	1492.7
7.5°	1500.5	1484.3	1489.1	1483.9	1482.3
10°	1490.1	1474.9	1479.8	1474.5	1472.0
12.5°	1478.7	1462.5	1468.4	1462.1	1459.5
15°	1455.1	1439.9	1446.1	1440.8	1438.3
17.5°	1429.2	1413.0	1419.1	1413.1	1409.8
20°	1408.5	1393.3	1399.4	1390.3	1389.1
22.5°	1385.7	1370.5	1376.6	1364.4	1364.2
25°	1348.9	1332.4	1339.8	1325.5	1324.3
27.5°	1305.1	1289.9	1296.0	1281.5	1279.9
30°	1275.0	1259.8	1266.0	1250.3	1247.8
32.5°	1240.8	1226.6	1231.7	1216.2	1214.6
35°	1188.2	1174.3	1177.8	1162.3	1161.0
37.5°	1128.3	1115.7	1117.7	1100.6	1099.3
40°	1085.8	1073.2	1074.2	1056.0	1054.7
42.5°	1039.2	1026.5	1025.5	1007.3	1006.0
45°	961.5	948.8	944.6	927.7	925.2
47.5°	872.8	860.2	852.3	838.6	836.8
50°	808.6	795.9	789.1	777.4	773.6
52.5°	739.1	726.4	720.7	710.0	706.2
55°	629.7	619.6	615.5	605.1	602.5
57.5°	525.8	519.0	517.8	507.7	506.6
60°	462.6	458.8	458.7	449.6	449.6
62.5°	408.7	405.9	407.9	401.9	400.9
65°	338.2	335.7	339.5	336.9	336.9
67.5°	282.5	282.5	284.8	283.8	283.8
70°	251.4	251.4	252.7	252.7	252.7
72.5°	223.4	222.4	225.7	225.7	224.7
75°	182.7	182.7	182.7	184.0	184.0
77.5°	142.3	142.5	143.6	143.3	142.3
80°	115.3	116.6	116.6	115.3	115.3
82.5°	88.4	89.6	89.7	89.4	88.4
85°	46.6	49.2	51.8	51.8	51.8
87.5°	13.5	17.5	20.7	20.7	19.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.5	24.1	55.8	16.2	12.2
95°	14.7	58.6	263.1	91.1	56.1
97.5°	27.1	68.6	405.3	290.0	198.7
100°	35.7	74.5	436.1	441.7	340.3
102.5°	45.3	81.0	429.3	565.4	476.8
105°	60.1	91.2	394.1	696.2	661.8
107.5°	75.2	103.0	353.1	733.1	763.7
110°	85.6	111.7	329.5	719.0	787.7

TEST NUMBER: P561803

CATALOG NUMBER: SQ4-PR1-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	95.6	120.3	313.6	685.6	783.6
115°	111.7	135.0	298.9	633.1	743.5
117.5°	125.9	147.7	290.1	575.8	692.7
120°	137.2	155.5	289.2	543.0	655.0
122.5°	146.3	164.6	287.0	514.2	618.3
125°	157.7	174.8	285.3	473.4	566.0
127.5°	170.0	186.1	284.3	449.0	525.3
130°	176.4	192.5	283.0	431.9	498.5
132.5°	183.2	198.8	283.0	418.7	479.9
135°	192.8	208.9	281.9	399.9	452.0
137.5°	201.9	217.5	281.7	383.9	429.0
140°	208.7	224.8	281.3	370.7	414.0
142.5°	216.4	229.8	282.6	360.2	399.0
145°	227.4	239.1	284.1	346.1	377.1
147.5°	236.8	248.1	286.6	331.8	358.6
150°	245.0	252.8	287.5	327.1	345.9
152.5°	251.3	259.6	288.4	320.7	338.2
155°	259.7	265.8	290.9	312.8	325.5
157.5°	270.2	273.8	291.5	309.2	318.3
160°	275.6	278.4	293.8	306.4	314.2
162.5°	278.8	282.0	294.2	304.1	310.1
165°	287.0	288.1	294.3	300.7	305.1
167.5°	292.5	291.5	296.9	299.8	301.6
170°	294.3	293.8	296.0	296.6	298.9
172.5°	298.4	296.5	297.4	295.7	297.5
175°	300.6	298.9	297.7	296.0	293.8
177.5°	301.5	298.8	297.4	295.6	296.0
180°	298.3	298.3	298.3	298.3	298.3

(END OF REPORT)