

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523793

Luminaire Tested: **SQ4-PP3-0U-075D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523793
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-075D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3146.9 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 31.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523793

CATALOG NUMBER: SQ4-PP3-0U-075D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523793

CATALOG NUMBER: SQ4-PP3-0U-075D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11344	11344	11344
5°	11427	11357	11317
10°	11408	11327	11277
15°	11332	11270	11209
20°	11257	11194	11109
25°	11124	11046	10936
30°	10918	10860	10723
35°	10632	10559	10425
40°	10292	10227	10110
45°	10010	9940	9842
50°	9651	9590	9496
55°	9153	9030	8961
60°	8331	8093	8053
65°	7340	7034	7010
70°	6337	6075	6075
75°	5454	5379	5301
80°	4808	4867	4750
85°	3769	4107	4107



TEST NUMBER: P523793

CATALOG NUMBER: SQ4-PP3-0U-075D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	3.7
10°-20°	332.0	10.5
20°-30°	497.2	15.8
30°-40°	583.2	18.5
40°-50°	585.1	18.6
50°-60°	499.1	15.9
60°-70°	325.5	10.3
70°-80°	163.3	5.2
80°-90°	45.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	945.5	30.0
0°-40°	1528.7	48.6
0°-60°	2612.9	83.0
0°-90°	3146.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3146.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1234	1222	1226	1222	1222	117
15°	1186	1175	1180	1176	1174	335
25°	1093	1080	1085	1075	1074	502
35°	944	934	938	927	926	590
45°	767	762	762	754	754	591
55°	569	567	561	558	557	506
65°	336	330	322	320	321	336
75°	153	153	151	150	149	166
85°	36	39	39	39	39	43
90°	0	0	0	0	0	



TEST NUMBER: P523793

CATALOG NUMBER: SQ4-PP3-0U-075D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.5	1229.5	1229.5	1229.5	1229.5
2.5°	1237.3	1227.2	1229.5	1227.7	1222.6
5°	1233.8	1222.2	1226.3	1222.0	1222.0
7.5°	1225.4	1212.8	1216.8	1212.5	1212.3
10°	1217.7	1205.0	1209.0	1204.7	1203.7
12.5°	1206.5	1193.8	1198.7	1193.5	1193.3
15°	1186.4	1174.8	1179.9	1175.6	1173.5
17.5°	1163.8	1151.1	1157.3	1151.3	1150.4
20°	1146.5	1133.9	1140.1	1131.5	1131.5
22.5°	1125.8	1113.2	1120.2	1109.0	1109.0
25°	1092.7	1080.0	1085.1	1075.4	1074.3
27.5°	1053.2	1040.8	1046.1	1035.1	1034.9
30°	1024.8	1013.2	1019.4	1007.5	1006.5
32.5°	993.7	983.0	987.5	975.6	974.6
35°	944.0	934.5	937.5	926.7	925.6
37.5°	891.6	881.9	885.3	876.1	875.6
40°	854.5	848.2	849.1	841.5	839.4
42.5°	820.0	812.9	813.8	806.2	805.8
45°	767.2	762.0	761.8	754.3	754.3
47.5°	711.2	707.2	706.0	699.8	699.6
50°	672.4	669.2	668.1	662.7	661.6
52.5°	631.9	630.4	626.7	622.2	622.0
55°	569.0	566.9	561.4	558.2	557.1
57.5°	500.6	496.4	490.3	485.6	486.4
60°	451.5	447.3	438.6	436.4	436.4
62.5°	404.1	399.0	390.3	387.3	389.0
65°	336.2	329.9	322.2	320.1	321.1
67.5°	274.6	268.9	260.6	260.5	259.7
70°	234.9	231.8	225.2	225.2	225.2
72.5°	199.6	198.1	193.3	193.3	192.5
75°	153.0	153.0	150.9	149.8	148.7
77.5°	114.7	115.1	114.0	112.9	111.0
80°	90.5	92.6	91.6	90.5	89.4
82.5°	68.1	70.2	70.0	68.1	67.9
85°	35.6	38.7	38.8	38.8	38.8
87.5°	9.5	12.9	13.8	13.8	14.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)