

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523804

Luminaire Tested: **SQ4-PP3-0U-100D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523804
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-100D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4026.5 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 42.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523804

CATALOG NUMBER: SQ4-PP3-0U-100D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523804

CATALOG NUMBER: SQ4-PP3-OU-100D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14515	14515	14515
5°	14621	14532	14481
10°	14596	14493	14428
15°	14500	14421	14342
20°	14403	14323	14214
25°	14233	14135	13994
30°	13969	13895	13720
35°	13604	13511	13340
40°	13169	13086	12936
45°	12809	12719	12594
50°	12350	12271	12152
55°	11710	11556	11466
60°	10660	10355	10304
65°	9392	9001	8970
70°	8109	7774	7774
75°	6980	6880	6784
80°	6153	6227	6078
85°	4817	5251	5251



TEST NUMBER: P523804

CATALOG NUMBER: SQ4-PP3-OU-100D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.8	3.7
10°-20°	424.8	10.5
20°-30°	636.2	15.8
30°-40°	746.3	18.5
40°-50°	748.6	18.6
50°-60°	638.6	15.9
60°-70°	416.5	10.3
70°-80°	209.0	5.2
80°-90°	57.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1209.8	30.0
0°-40°	1956.0	48.6
0°-60°	3343.3	83.0
0°-90°	4026.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4026.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1573	1573	1573	1573	1573	
5°	1579	1564	1569	1564	1564	150
15°	1518	1503	1510	1504	1502	428
25°	1398	1382	1388	1376	1375	643
35°	1208	1196	1200	1186	1184	754
45°	982	975	975	965	965	756
55°	728	725	718	714	713	647
65°	430	422	412	410	411	429
75°	196	196	193	192	190	212
85°	46	50	50	50	50	55
90°	0	0	0	0	0	



TEST NUMBER: P523804

CATALOG NUMBER: SQ4-PP3-0U-100D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1573.2	1573.2	1573.2	1573.2	1573.2
2.5°	1583.1	1570.2	1573.2	1570.9	1564.4
5°	1578.7	1563.9	1569.1	1563.6	1563.6
7.5°	1568.0	1551.8	1556.9	1551.4	1551.2
10°	1558.0	1541.9	1547.0	1541.5	1540.1
12.5°	1543.7	1527.5	1533.8	1527.2	1526.9
15°	1518.1	1503.2	1509.8	1504.2	1501.5
17.5°	1489.1	1472.9	1480.8	1473.1	1472.0
20°	1467.0	1450.9	1458.8	1447.7	1447.7
22.5°	1440.6	1424.4	1433.4	1419.1	1419.1
25°	1398.1	1381.9	1388.5	1376.0	1374.7
27.5°	1347.6	1331.7	1338.5	1324.5	1324.2
30°	1311.2	1296.4	1304.3	1289.2	1287.8
32.5°	1271.5	1257.8	1263.5	1248.3	1247.0
35°	1207.8	1195.7	1199.6	1185.7	1184.4
37.5°	1140.8	1128.4	1132.8	1121.0	1120.4
40°	1093.4	1085.3	1086.5	1076.8	1074.1
42.5°	1049.3	1040.1	1041.3	1031.6	1031.1
45°	981.7	975.0	974.8	965.2	965.2
47.5°	910.0	904.9	903.4	895.4	895.1
50°	860.4	856.3	854.9	847.9	846.6
52.5°	808.5	806.6	801.9	796.1	795.8
55°	728.0	725.3	718.4	714.2	712.8
57.5°	640.6	635.2	627.4	621.3	622.4
60°	577.7	572.3	561.2	558.4	558.4
62.5°	517.1	510.6	499.4	495.6	497.7
65°	430.2	422.1	412.3	409.5	410.9
67.5°	351.3	344.0	333.4	333.4	332.3
70°	300.6	296.5	288.2	288.2	288.2
72.5°	255.4	253.5	247.4	247.3	246.3
75°	195.8	195.8	193.0	191.6	190.3
77.5°	146.7	147.2	145.9	144.4	142.0
80°	115.8	118.5	117.2	115.8	114.4
82.5°	87.1	89.8	89.6	87.1	86.9
85°	45.5	49.5	49.6	49.6	49.6
87.5°	12.1	16.4	17.6	17.7	18.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)