

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523814

Luminaire Tested: **SQ4-PP3-0U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523814
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-125D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4789.7 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 55.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523814

CATALOG NUMBER: SQ4-PP3-0U-125D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523814

CATALOG NUMBER: SQ4-PP3-OU-125D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17266	17266	17266
5°	17393	17286	17225
10°	17364	17240	17163
15°	17248	17155	17060
20°	17134	17038	16908
25°	16930	16813	16646
30°	16617	16530	16320
35°	16183	16071	15869
40°	15664	15566	15389
45°	15237	15130	14980
50°	14689	14596	14454
55°	13930	13745	13640
60°	12680	12317	12258
65°	11171	10706	10671
70°	9644	9247	9247
75°	8302	8185	8067
80°	7322	7407	7231
85°	5727	6246	6246



TEST NUMBER: P523814

CATALOG NUMBER: SQ4-PP3-OU-125D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.0	3.7
10°-20°	505.3	10.5
20°-30°	756.8	15.8
30°-40°	887.7	18.5
40°-50°	890.5	18.6
50°-60°	759.7	15.9
60°-70°	495.4	10.3
70°-80°	248.5	5.2
80°-90°	68.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1439.1	30.0
0°-40°	2326.8	48.6
0°-60°	3977.0	83.0
0°-90°	4789.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4789.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1871	1871	1871	1871	1871	
5°	1878	1860	1866	1860	1860	178
15°	1806	1788	1796	1789	1786	509
25°	1663	1644	1652	1637	1635	765
35°	1437	1422	1427	1410	1409	897
45°	1168	1160	1160	1148	1148	899
55°	866	863	854	850	848	770
65°	512	502	490	487	489	511
75°	233	233	230	228	226	253
85°	54	59	59	59	59	66
90°	0	0	0	0	0	



TEST NUMBER: P523814

CATALOG NUMBER: SQ4-PP3-OU-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1871.4	1871.4	1871.4	1871.4	1871.4
2.5°	1883.2	1867.8	1871.4	1868.6	1860.9
5°	1878.0	1860.3	1866.5	1859.9	1859.9
7.5°	1865.2	1845.9	1852.0	1845.5	1845.2
10°	1853.4	1834.1	1840.2	1833.6	1832.0
12.5°	1836.3	1817.1	1824.5	1816.6	1816.3
15°	1805.8	1788.2	1796.0	1789.3	1786.1
17.5°	1771.3	1752.1	1761.5	1752.3	1751.0
20°	1745.1	1725.9	1735.3	1722.1	1722.1
22.5°	1713.6	1694.4	1705.1	1688.0	1688.0
25°	1663.1	1643.9	1651.6	1636.8	1635.2
27.5°	1603.1	1584.1	1592.2	1575.5	1575.2
30°	1559.8	1542.1	1551.6	1533.5	1531.9
32.5°	1512.5	1496.2	1503.0	1484.9	1483.3
35°	1436.8	1422.3	1426.9	1410.5	1408.9
37.5°	1357.0	1342.3	1347.5	1333.4	1332.8
40°	1300.6	1291.0	1292.4	1280.9	1277.7
42.5°	1248.1	1237.2	1238.6	1227.1	1226.5
45°	1167.8	1159.8	1159.6	1148.1	1148.1
47.5°	1082.5	1076.4	1074.6	1065.1	1064.8
50°	1023.4	1018.6	1016.9	1008.6	1007.0
52.5°	961.8	959.5	953.9	947.0	946.7
55°	866.0	862.8	854.5	849.6	848.0
57.5°	762.0	755.6	746.3	739.1	740.4
60°	687.2	680.8	667.5	664.3	664.3
62.5°	615.1	607.4	594.1	589.5	592.1
65°	511.7	502.1	490.4	487.2	488.8
67.5°	417.9	409.2	396.6	396.6	395.3
70°	357.5	352.7	342.8	342.8	342.8
72.5°	303.8	301.5	294.2	294.2	292.9
75°	232.9	232.9	229.6	227.9	226.3
77.5°	174.5	175.2	173.5	171.8	168.9
80°	137.8	141.0	139.4	137.7	136.1
82.5°	103.7	106.9	106.6	103.6	103.3
85°	54.1	58.9	59.0	59.0	59.0
87.5°	14.4	19.6	21.0	21.0	22.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)