

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561818

Luminaire Tested: **SQ4-PR1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561818
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6913.5 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561818
CATALOG NUMBER: SQ4-PR1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561818

CATALOG NUMBER: SQ4-PR1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72		
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	65	61		
2	94	87	81	75	89	83	77	72	75	70	67	67	64	61	60	58	56	52		
3	86	77	69	63	82	73	66	61	66	61	56	60	56	52	54	51	48	45		
4	79	68	60	54	75	65	58	52	59	53	49	54	49	45	48	45	42	39		
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36	34		
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	32	30		
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26		
8	58	45	38	32	55	44	36	31	40	34	29	37	31	28	34	29	26	24		
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	21		
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18368	18368	18368
5°	18533	18390	18294
10°	18474	18345	18249
15°	18393	18278	18180
20°	18300	18183	18048
25°	18171	18049	17839
30°	17976	17848	17592
35°	17710	17556	17305
40°	17306	17120	16811
45°	16601	16310	15974
50°	15358	14989	14694
55°	13404	13102	12825
60°	11295	11201	10979
65°	9769	9809	9732
70°	8975	9021	9021
75°	8620	8620	8680
80°	8108	8198	8108
85°	6531	7262	7262



TEST NUMBER: P561818

CATALOG NUMBER: SQ4-PR1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.3	2.7
10°-20°	538.6	7.8
20°-30°	812.4	11.8
30°-40°	968.0	14.0
40°-50°	954.4	13.8
50°-60°	729.4	10.5
60°-70°	451.4	6.5
70°-80°	256.4	3.7
80°-90°	78.0	1.1
90°-100°	142.1	2.1
100°-110°	404.2	5.8
110°-120°	387.3	5.6
120°-130°	306.6	4.4
130°-140°	246.0	3.6
140°-150°	192.6	2.8
150°-160°	140.9	2.0
160°-170°	87.3	1.3
170°-180°	29.6	0.4
0°-30°	1539.3	22.3
0°-40°	2507.3	36.3
0°-60°	4191.0	60.6
0°-90°	4976.7	72.0
90°-120°	933.6	13.5
90°-150°	1678.9	24.3
90°-180°	1937.0	28.0
0°-180°	6913.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1991	1991	1991	1991	1991	
5°	2001	1979	1986	1979	1975	190
15°	1926	1906	1914	1907	1903	543
25°	1785	1763	1773	1754	1752	821
35°	1572	1554	1559	1538	1536	981
45°	1272	1256	1250	1228	1224	975
55°	833	820	814	801	797	747
65°	448	444	449	446	446	453
75°	242	242	242	244	244	255
85°	62	65	69	69	69	72
90°	0	0	0	0	0	3
95°	15	61	275	95	59	18
105°	63	95	412	728	692	66
115°	117	141	312	662	777	115
125°	165	183	298	495	592	147
135°	202	218	295	418	472	156
145°	238	250	297	362	394	148
155°	272	278	304	327	340	126
165°	300	301	308	314	319	84
175°	314	312	311	309	307	30
180°	312	312	312	312	312	

TEST NUMBER: P561818

CATALOG NUMBER: SQ4-PR1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1990.8	1990.8	1990.8	1990.8	1990.8
2.5°	2003.1	1985.7	1990.8	1986.4	1977.1
5°	2001.1	1979.3	1985.6	1978.7	1975.3
7.5°	1985.6	1964.2	1970.5	1963.6	1961.6
10°	1971.9	1951.8	1958.2	1951.3	1947.9
12.5°	1956.8	1935.4	1943.1	1934.8	1931.4
15°	1925.6	1905.5	1913.6	1906.7	1903.3
17.5°	1891.3	1869.9	1877.9	1870.0	1865.6
20°	1863.9	1843.8	1851.9	1839.8	1838.2
22.5°	1833.7	1813.6	1821.7	1805.6	1805.2
25°	1785.0	1763.2	1773.0	1754.1	1752.4
27.5°	1727.1	1706.9	1715.0	1695.8	1693.8
30°	1687.3	1667.2	1675.3	1654.6	1651.3
32.5°	1642.0	1623.2	1630.0	1609.4	1607.4
35°	1572.4	1553.9	1558.7	1538.1	1536.4
37.5°	1493.2	1476.4	1479.1	1456.4	1454.8
40°	1436.9	1420.2	1421.5	1397.4	1395.8
42.5°	1375.2	1358.4	1357.0	1333.0	1331.3
45°	1272.3	1255.5	1250.0	1227.7	1224.3
47.5°	1155.0	1138.3	1127.9	1109.7	1107.4
50°	1070.0	1053.2	1044.3	1028.7	1023.7
52.5°	978.1	961.3	953.7	939.5	934.5
55°	833.3	819.9	814.5	800.7	797.3
57.5°	695.8	686.8	685.2	671.8	670.4
60°	612.1	607.1	607.0	595.0	595.0
62.5°	540.8	537.1	539.8	531.9	530.5
65°	447.5	444.2	449.3	445.8	445.8
67.5°	373.8	373.8	376.9	375.5	375.5
70°	332.7	332.7	334.4	334.4	334.4
72.5°	295.6	294.3	298.7	298.7	297.3
75°	241.8	241.8	241.8	243.5	243.5
77.5°	188.3	188.6	190.0	189.6	188.3
80°	152.6	154.3	154.3	152.6	152.6
82.5°	116.9	118.6	118.7	118.3	116.9
85°	61.7	65.1	68.6	68.6	68.6
87.5°	17.8	23.2	27.4	27.4	26.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	25.1	58.3	17.0	12.8
95°	15.4	61.2	275.0	95.2	58.7
97.5°	28.3	71.7	423.6	303.1	207.7
100°	37.3	77.9	455.8	461.7	355.7
102.5°	47.3	84.6	448.7	591.0	498.4
105°	62.8	95.3	412.0	727.7	691.7
107.5°	78.6	107.7	369.0	766.2	798.2
110°	89.5	116.7	344.4	751.5	823.3

TEST NUMBER: P561818

CATALOG NUMBER: SQ4-PR1-025U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	99.9	125.8	327.8	716.6	819.1
115°	116.8	141.1	312.4	661.8	777.1
117.5°	131.6	154.4	303.3	601.8	724.0
120°	143.4	162.6	302.3	567.6	684.6
122.5°	152.9	172.1	299.9	537.5	646.2
125°	164.8	182.8	298.2	494.8	591.6
127.5°	177.7	194.5	297.2	469.3	549.0
130°	184.3	201.2	295.8	451.5	521.0
132.5°	191.5	207.8	295.8	437.6	501.6
135°	201.5	218.3	294.6	417.9	472.4
137.5°	211.0	227.4	294.5	401.3	448.4
140°	218.1	234.9	294.0	387.5	432.7
142.5°	226.2	240.2	295.4	376.5	417.1
145°	237.7	249.9	297.0	361.7	394.2
147.5°	247.5	259.4	299.6	346.8	374.9
150°	256.1	264.2	300.5	341.9	361.6
152.5°	262.7	271.3	301.5	335.2	353.5
155°	271.5	277.9	304.1	326.9	340.2
157.5°	282.4	286.2	304.7	323.1	332.7
160°	288.1	291.0	307.0	320.3	328.4
162.5°	291.4	294.8	307.5	317.9	324.1
165°	299.9	301.1	307.6	314.3	318.9
167.5°	305.7	304.7	310.4	313.4	315.2
170°	307.6	307.1	309.4	310.1	312.4
172.5°	311.9	309.9	310.8	309.1	311.0
175°	314.2	312.4	311.2	309.4	307.0
177.5°	315.1	312.3	310.8	309.0	309.4
180°	311.8	311.8	311.8	311.8	311.8

(END OF REPORT)