

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561833

Luminaire Tested: **SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561833
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4324.5 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561833
CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561833

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48		
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41		
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35		
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30		
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26		
5	68	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	22		
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23	20		
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18		
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	24	20	18	16		
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16	14		
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7625	7625	7625
5°	7693	7634	7594
10°	7669	7616	7575
15°	7636	7588	7547
20°	7596	7548	7492
25°	7543	7492	7406
30°	7462	7408	7303
35°	7351	7287	7184
40°	7184	7107	6978
45°	6892	6771	6631
50°	6376	6222	6100
55°	5564	5438	5324
60°	4689	4650	4558
65°	4056	4071	4041
70°	3725	3744	3744
75°	3579	3579	3604
80°	3369	3406	3369
85°	2710	3017	3017



TEST NUMBER: P561833

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.1	1.8
10°-20°	223.6	5.2
20°-30°	337.3	7.8
30°-40°	401.8	9.3
40°-50°	396.2	9.2
50°-60°	302.8	7.0
60°-70°	187.4	4.3
70°-80°	106.4	2.5
80°-90°	32.4	0.7
90°-100°	165.7	3.8
100°-110°	471.4	10.9
110°-120°	451.7	10.4
120°-130°	357.5	8.3
130°-140°	286.9	6.6
140°-150°	224.6	5.2
150°-160°	164.4	3.8
160°-170°	101.8	2.4
170°-180°	34.5	0.8
0°-30°	639.0	14.8
0°-40°	1040.8	24.1
0°-60°	1739.8	40.2
0°-90°	2066.0	47.8
90°-120°	1088.8	25.2
90°-150°	1957.8	45.3
90°-180°	2259.0	52.2
0°-180°	4324.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	826	826	826	826	826	
5°	831	822	824	821	820	79
15°	799	791	794	792	790	226
25°	741	732	736	728	728	341
35°	653	645	647	638	638	407
45°	528	521	519	510	508	405
55°	346	340	338	332	331	310
65°	186	184	186	185	185	188
75°	100	100	100	101	101	106
85°	26	27	28	28	28	30
90°	0	0	0	0	0	2
95°	18	71	321	111	68	21
105°	73	111	480	849	807	78
115°	136	165	364	772	906	134
125°	192	213	348	577	690	172
135°	235	255	344	487	551	181
145°	277	291	346	422	460	173
155°	317	324	355	381	397	146
165°	350	351	359	366	372	98
175°	366	364	363	361	358	35
180°	364	364	364	364	364	



TEST NUMBER: P561833

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	826.4	826.4	826.4	826.4	826.4
2.5°	831.5	824.3	826.4	824.6	820.7
5°	830.7	821.6	824.3	821.4	820.0
7.5°	824.3	815.4	818.0	815.1	814.3
10°	818.6	810.2	812.9	810.0	808.6
12.5°	812.3	803.4	806.6	803.2	801.8
15°	799.4	791.0	794.4	791.5	790.1
17.5°	785.1	776.2	779.6	776.3	774.5
20°	773.7	765.4	768.8	763.8	763.1
22.5°	761.2	752.9	756.2	749.5	749.4
25°	741.0	731.9	736.0	728.2	727.5
27.5°	716.9	708.6	712.0	704.0	703.1
30°	700.4	692.1	695.4	686.9	685.5
32.5°	681.6	673.8	676.6	668.1	667.3
35°	652.7	645.1	647.0	638.5	637.8
37.5°	619.8	612.9	614.0	604.6	603.9
40°	596.5	589.5	590.1	580.1	579.4
42.5°	570.9	563.9	563.3	553.3	552.7
45°	528.2	521.2	518.9	509.6	508.2
47.5°	479.5	472.5	468.2	460.7	459.7
50°	444.2	437.2	433.5	427.0	425.0
52.5°	406.0	399.1	395.9	390.0	387.9
55°	345.9	340.4	338.1	332.4	331.0
57.5°	288.9	285.1	284.4	278.9	278.3
60°	254.1	252.0	252.0	247.0	247.0
62.5°	224.5	223.0	224.1	220.8	220.2
65°	185.8	184.4	186.5	185.1	185.1
67.5°	155.2	155.2	156.5	155.9	155.9
70°	138.1	138.1	138.8	138.8	138.8
72.5°	122.7	122.2	124.0	124.0	123.4
75°	100.4	100.4	100.4	101.1	101.1
77.5°	78.2	78.3	78.9	78.7	78.2
80°	63.4	64.0	64.1	63.4	63.4
82.5°	48.5	49.2	49.3	49.1	48.5
85°	25.6	27.0	28.5	28.5	28.5
87.5°	7.4	9.6	11.4	11.4	10.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.5	29.3	68.0	19.8	14.9
95°	18.0	71.4	320.7	111.0	68.4
97.5°	33.0	83.6	494.0	353.5	242.2
100°	43.5	90.9	531.6	538.4	414.7
102.5°	55.2	98.7	523.3	689.2	581.2
105°	73.3	111.1	480.4	848.6	806.7
107.5°	91.7	125.6	430.4	893.5	930.8
110°	104.4	136.1	401.6	876.3	960.1

TEST NUMBER: P561833

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	116.5	146.7	382.3	835.7	955.2
115°	136.2	164.6	364.3	771.7	906.2
117.5°	153.5	180.1	353.6	701.8	844.3
120°	167.3	189.6	352.5	661.9	798.4
122.5°	178.3	200.6	349.8	626.8	753.6
125°	192.2	213.1	347.7	577.0	689.9
127.5°	207.2	226.8	346.6	547.2	640.2
130°	215.0	234.6	344.9	526.5	607.6
132.5°	223.3	242.3	344.9	510.3	584.9
135°	235.0	254.6	343.5	487.4	550.9
137.5°	246.1	265.1	343.4	468.0	522.9
140°	254.4	274.0	342.9	451.9	504.6
142.5°	263.8	280.1	344.5	439.0	486.4
145°	277.2	291.4	346.3	421.8	459.7
147.5°	288.7	302.4	349.4	404.4	437.1
150°	298.6	308.1	350.5	398.7	421.7
152.5°	306.4	316.4	351.6	390.9	412.3
155°	316.6	324.0	354.6	381.2	396.8
157.5°	329.3	333.8	355.3	376.8	387.9
160°	335.9	339.3	358.1	373.5	382.9
162.5°	339.8	343.7	358.6	370.7	378.0
165°	349.8	351.1	358.8	366.5	371.9
167.5°	356.5	355.3	361.9	365.4	367.6
170°	358.8	358.1	360.8	361.6	364.3
172.5°	363.7	361.4	362.5	360.5	362.6
175°	366.4	364.3	362.9	360.8	358.1
177.5°	367.5	364.2	362.5	360.3	360.8
180°	363.6	363.6	363.6	363.6	363.6

(END OF REPORT)