

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561834

Luminaire Tested: **SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561834
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4372.3 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561834

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561834

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48		
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41		
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35		
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30		
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26		
5	68	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	22		
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23	20		
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18		
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	24	20	18	16		
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16	14		
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7709	7709	7709
5°	7779	7718	7679
10°	7753	7700	7660
15°	7720	7672	7631
20°	7681	7632	7575
25°	7627	7576	7487
30°	7545	7490	7384
35°	7434	7368	7262
40°	7264	7185	7055
45°	6968	6846	6705
50°	6446	6291	6168
55°	5627	5500	5384
60°	4740	4702	4608
65°	4100	4117	4085
70°	3766	3785	3785
75°	3618	3618	3643
80°	3406	3443	3406
85°	2742	3049	3049



TEST NUMBER: P561834

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.0	1.8
10°-20°	226.1	5.2
20°-30°	341.0	7.8
30°-40°	406.3	9.3
40°-50°	400.6	9.2
50°-60°	306.1	7.0
60°-70°	189.4	4.3
70°-80°	107.6	2.5
80°-90°	32.7	0.7
90°-100°	167.5	3.8
100°-110°	476.6	10.9
110°-120°	456.7	10.4
120°-130°	361.4	8.3
130°-140°	290.1	6.6
140°-150°	227.1	5.2
150°-160°	166.2	3.8
160°-170°	102.9	2.4
170°-180°	34.9	0.8
0°-30°	646.1	14.8
0°-40°	1052.3	24.1
0°-60°	1759.0	40.2
0°-90°	2088.8	47.8
90°-120°	1100.8	25.2
90°-150°	1979.5	45.3
90°-180°	2283.0	52.2
0°-180°	4372.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	836	836	836	836	836	
5°	840	831	833	830	829	80
15°	808	800	803	800	799	228
25°	749	740	744	736	736	345
35°	660	652	654	646	645	412
45°	534	527	525	515	514	409
55°	350	344	342	336	335	313
65°	188	186	189	187	187	190
75°	102	102	102	102	102	107
85°	26	27	29	29	29	30
90°	0	0	0	0	0	2
95°	18	72	324	112	69	21
105°	74	112	486	858	816	78
115°	138	166	368	780	916	136
125°	194	216	352	583	698	174
135°	238	257	347	493	557	183
145°	280	295	350	426	465	175
155°	320	328	358	385	401	148
165°	354	355	363	370	376	99
175°	370	368	367	365	362	35
180°	368	368	368	368	368	



TEST NUMBER: P561834

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	835.6	835.6	835.6	835.6	835.6
2.5°	840.7	833.4	835.6	833.7	829.8
5°	839.9	830.7	833.4	830.5	829.1
7.5°	833.4	824.4	827.1	824.2	823.3
10°	827.6	819.2	821.9	819.0	817.6
12.5°	821.3	812.3	815.6	812.1	810.7
15°	808.2	799.8	803.2	800.3	798.9
17.5°	793.8	784.8	788.2	784.8	783.0
20°	782.3	773.9	777.3	772.2	771.5
22.5°	769.6	761.2	764.6	757.8	757.7
25°	749.2	740.0	744.2	736.2	735.5
27.5°	724.9	716.4	719.8	711.8	710.9
30°	708.2	699.7	703.1	694.5	693.1
32.5°	689.2	681.3	684.1	675.5	674.6
35°	660.0	652.2	654.2	645.5	644.8
37.5°	626.7	619.7	620.8	611.3	610.6
40°	603.1	596.1	596.6	586.5	585.8
42.5°	577.2	570.2	569.6	559.5	558.8
45°	534.0	527.0	524.7	515.3	513.9
47.5°	484.8	477.7	473.4	465.8	464.8
50°	449.1	442.0	438.3	431.8	429.7
52.5°	410.5	403.5	400.3	394.3	392.2
55°	349.8	344.1	341.9	336.1	334.7
57.5°	292.0	288.2	287.6	282.0	281.4
60°	256.9	254.8	254.8	249.7	249.7
62.5°	227.0	225.4	226.6	223.2	222.7
65°	187.8	186.4	188.6	187.1	187.1
67.5°	156.9	156.9	158.2	157.6	157.6
70°	139.6	139.6	140.3	140.3	140.3
72.5°	124.1	123.5	125.4	125.4	124.8
75°	101.5	101.5	101.5	102.2	102.2
77.5°	79.0	79.2	79.7	79.6	79.0
80°	64.1	64.8	64.8	64.1	64.1
82.5°	49.1	49.8	49.8	49.6	49.1
85°	25.9	27.3	28.8	28.8	28.8
87.5°	7.5	9.7	11.5	11.5	10.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.6	29.6	68.8	20.0	15.1
95°	18.2	72.2	324.3	112.2	69.2
97.5°	33.4	84.5	499.4	357.4	244.9
100°	44.0	91.9	537.4	544.4	419.3
102.5°	55.8	99.8	529.1	696.8	587.6
105°	74.1	112.3	485.7	858.0	815.6
107.5°	92.7	127.0	435.1	903.4	941.1
110°	105.5	137.6	406.1	886.0	970.8



TEST NUMBER: P561834

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	117.8	148.3	386.5	844.9	965.7
115°	137.7	166.4	368.3	780.3	916.2
117.5°	155.2	182.1	357.6	709.6	853.6
120°	169.1	191.7	356.4	669.2	807.2
122.5°	180.3	202.9	353.6	633.7	761.9
125°	194.3	215.5	351.5	583.4	697.5
127.5°	209.5	229.3	350.4	553.3	647.3
130°	217.4	237.2	348.7	532.3	614.3
132.5°	225.7	245.0	348.7	516.0	591.4
135°	237.6	257.4	347.3	492.8	557.0
137.5°	248.8	268.1	347.2	473.1	528.6
140°	257.2	277.0	346.6	456.9	510.2
142.5°	266.7	283.2	348.3	443.9	491.7
145°	280.3	294.6	350.1	426.5	464.8
147.5°	291.9	305.8	353.2	408.9	442.0
150°	301.9	311.5	354.3	403.1	426.3
152.5°	309.7	319.9	355.5	395.2	416.8
155°	320.1	327.6	358.5	385.4	401.2
157.5°	332.9	337.5	359.2	381.0	392.2
160°	339.7	343.1	362.0	377.6	387.2
162.5°	343.6	347.5	362.6	374.8	382.2
165°	353.6	355.0	362.7	370.5	376.0
167.5°	360.5	359.3	365.9	369.5	371.7
170°	362.7	362.0	364.8	365.6	368.3
172.5°	367.8	365.4	366.5	364.4	366.6
175°	370.4	368.4	366.9	364.8	362.0
177.5°	371.5	368.2	366.5	364.3	364.8
180°	367.6	367.6	367.6	367.6	367.6

(END OF REPORT)