

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523843

Luminaire Tested: **SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523843  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (4000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7515.5 lumens  
Efficiency: N/A  
Efficacy: 116.9 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 64.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523843

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523843

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	64	55	54	52	42	41	41	35
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16
7	57	45	37	32	52	41	34	30	35	29	25	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11042	11042	11042
5°	11122	11054	11016
10°	11104	11025	10976
15°	11030	10970	10910
20°	10957	10895	10813
25°	10826	10752	10645
30°	10627	10570	10436
35°	10349	10278	10148
40°	10017	9954	9841
45°	9744	9675	9580
50°	9394	9334	9244
55°	8908	8791	8723
60°	8110	7877	7839
65°	7143	6846	6824
70°	6169	5913	5913
75°	5308	5233	5158
80°	4681	4739	4628
85°	3663	4001	4001



TEST NUMBER: P523843

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.2	1.5
10°-20°	323.1	4.3
20°-30°	484.0	6.4
30°-40°	567.7	7.6
40°-50°	569.5	7.6
50°-60°	485.8	6.5
60°-70°	316.8	4.2
70°-80°	158.9	2.1
80°-90°	44.0	0.6
90°-100°	326.6	4.3
100°-110°	929.4	12.4
110°-120°	890.4	11.8
120°-130°	704.7	9.4
130°-140°	565.7	7.5
140°-150°	442.8	5.9
150°-160°	324.0	4.3
160°-170°	200.7	2.7
170°-180°	68.1	0.9
0°-30°	920.3	12.2
0°-40°	1488.0	19.8
0°-60°	2543.2	33.8
0°-90°	3063.0	40.8
90°-120°	2146.4	28.6
90°-150°	3859.7	51.4
90°-180°	4453.0	59.3
0°-180°	7515.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1197	1197	1197	1197	1197	
5°	1201	1190	1194	1189	1189	114
15°	1155	1144	1148	1144	1142	326
25°	1064	1051	1056	1047	1046	489
35°	919	910	912	902	901	574
45°	747	742	742	734	734	575
55°	554	552	546	543	542	492
65°	327	321	314	312	313	327
75°	149	149	147	146	145	162
85°	35	38	38	38	38	41
90°	0	0	0	0	0	3
95°	35	141	632	219	135	40
105°	144	219	947	1673	1590	153
115°	268	324	718	1521	1786	264
125°	379	420	686	1138	1360	339
135°	463	502	677	961	1086	358
145°	546	574	683	832	906	341
155°	624	639	699	752	782	289
165°	690	692	707	722	733	194
175°	722	718	715	711	706	68
180°	717	717	717	717	717	

TEST NUMBER: P523843

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1196.8	1196.8	1196.8	1196.8	1196.8
2.5°	1204.3	1194.5	1196.8	1195.0	1190.0
5°	1200.9	1189.7	1193.6	1189.4	1189.4
7.5°	1192.8	1180.5	1184.4	1180.2	1180.0
10°	1185.2	1172.9	1176.8	1172.6	1171.6
12.5°	1174.3	1162.0	1166.8	1161.7	1161.5
15°	1154.8	1143.5	1148.5	1144.3	1142.2
17.5°	1132.8	1120.5	1126.5	1120.6	1119.8
20°	1116.0	1103.7	1109.7	1101.3	1101.3
22.5°	1095.9	1083.5	1090.4	1079.5	1079.5
25°	1063.5	1051.2	1056.2	1046.7	1045.7
27.5°	1025.2	1013.1	1018.2	1007.5	1007.3
30°	997.5	986.2	992.2	980.7	979.6
32.5°	967.3	956.8	961.2	949.6	948.6
35°	918.8	909.6	912.5	902.0	901.0
37.5°	867.8	858.4	861.7	852.7	852.3
40°	831.7	825.6	826.5	819.1	817.1
42.5°	798.2	791.2	792.1	784.7	784.3
45°	746.8	741.7	741.5	734.2	734.2
47.5°	692.2	688.4	687.2	681.1	680.9
50°	654.5	651.4	650.3	645.0	644.0
52.5°	615.1	613.6	610.0	605.6	605.4
55°	553.8	551.7	546.5	543.3	542.3
57.5°	487.3	483.2	477.2	472.6	473.5
60°	439.5	435.4	426.9	424.8	424.8
62.5°	393.3	388.4	379.9	377.0	378.6
65°	327.2	321.1	313.6	311.5	312.6
67.5°	267.3	261.7	253.6	253.6	252.8
70°	228.7	225.6	219.2	219.2	219.2
72.5°	194.2	192.8	188.2	188.1	187.3
75°	148.9	148.9	146.8	145.8	144.7
77.5°	111.6	112.0	111.0	109.9	108.0
80°	88.1	90.2	89.2	88.1	87.1
82.5°	66.3	68.3	68.2	66.3	66.1
85°	34.6	37.7	37.8	37.8	37.8
87.5°	9.2	12.5	13.4	13.4	14.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.9	57.8	134.1	39.0	29.4
95°	35.4	140.7	632.3	218.9	134.9
97.5°	65.1	164.8	973.8	696.8	477.5
100°	85.9	179.1	1047.9	1061.5	817.6
102.5°	108.7	194.6	1031.6	1358.7	1145.8
105°	144.4	219.1	947.1	1672.9	1590.3
107.5°	180.7	247.6	848.4	1761.5	1835.1
110°	205.8	268.4	791.7	1727.6	1892.8

TEST NUMBER: P523843

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	229.8	289.2	753.6	1647.4	1883.0
115°	268.5	324.4	718.2	1521.4	1786.5
117.5°	302.5	355.0	697.2	1383.6	1664.4
120°	329.8	373.8	695.0	1304.8	1574.0
122.5°	351.6	395.6	689.5	1235.7	1485.7
125°	378.8	420.1	685.5	1137.5	1360.0
127.5°	408.5	447.2	683.3	1078.8	1262.2
130°	423.8	462.5	680.0	1037.9	1197.8
132.5°	440.2	477.7	680.0	1006.0	1153.1
135°	463.3	502.0	677.3	960.8	1086.1
137.5°	485.1	522.7	677.0	922.6	1030.8
140°	501.5	540.1	675.9	890.9	994.8
142.5°	520.0	552.3	679.2	865.5	958.8
145°	546.5	574.4	682.7	831.6	906.2
147.5°	569.1	596.3	688.7	797.3	861.8
150°	588.7	607.4	690.9	786.0	831.3
152.5°	604.0	623.7	693.1	770.6	812.7
155°	624.1	638.8	699.1	751.6	782.2
157.5°	649.2	658.0	700.4	742.9	764.8
160°	662.3	668.9	705.9	736.3	755.0
162.5°	669.9	677.6	707.0	730.8	745.1
165°	689.5	692.2	707.3	722.5	733.1
167.5°	702.9	700.5	713.5	720.4	724.7
170°	707.3	705.9	711.3	712.8	718.2
172.5°	717.1	712.5	714.6	710.6	714.9
175°	722.2	718.3	715.4	711.2	705.9
177.5°	724.4	718.0	714.6	710.3	711.3
180°	716.8	716.8	716.8	716.8	716.8

(END OF REPORT)