

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523845

Luminaire Tested: **SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523845
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7721.2 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 64.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523845
CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523845

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	64	55	54	52	42	41	41	35
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16
7	57	45	37	32	52	41	34	30	35	29	25	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11344	11344	11344
5°	11427	11357	11317
10°	11408	11327	11277
15°	11332	11270	11209
20°	11257	11194	11109
25°	11124	11046	10936
30°	10918	10860	10723
35°	10632	10559	10425
40°	10292	10227	10110
45°	10010	9940	9842
50°	9651	9590	9496
55°	9153	9030	8961
60°	8331	8093	8053
65°	7340	7034	7010
70°	6337	6075	6075
75°	5454	5379	5301
80°	4808	4867	4750
85°	3769	4107	4107



TEST NUMBER: P523845

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	1.5
10°-20°	332.0	4.3
20°-30°	497.2	6.4
30°-40°	583.2	7.6
40°-50°	585.1	7.6
50°-60°	499.1	6.5
60°-70°	325.5	4.2
70°-80°	163.3	2.1
80°-90°	45.2	0.6
90°-100°	335.6	4.3
100°-110°	954.8	12.4
110°-120°	914.8	11.8
120°-130°	724.0	9.4
130°-140°	581.1	7.5
140°-150°	455.0	5.9
150°-160°	332.9	4.3
160°-170°	206.2	2.7
170°-180°	70.0	0.9
0°-30°	945.5	12.2
0°-40°	1528.7	19.8
0°-60°	2612.9	33.8
0°-90°	3146.9	40.8
90°-120°	2205.2	28.6
90°-150°	3965.3	51.4
90°-180°	4574.0	59.2
0°-180°	7721.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1234	1222	1226	1222	1222	117
15°	1186	1175	1180	1176	1174	335
25°	1093	1080	1085	1075	1074	502
35°	944	934	938	927	926	590
45°	767	762	762	754	754	591
55°	569	567	561	558	557	506
65°	336	330	322	320	321	336
75°	153	153	151	150	149	166
85°	36	39	39	39	39	42
90°	0	0	0	0	0	3
95°	36	144	650	225	139	42
105°	148	225	973	1719	1634	157
115°	276	333	738	1563	1835	272
125°	389	432	704	1169	1397	348
135°	476	516	696	987	1116	367
145°	561	590	701	854	931	351
155°	641	656	718	772	804	296
165°	708	711	727	742	753	199
175°	742	738	735	731	725	70
180°	736	736	736	736	736	



TEST NUMBER: P523845

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.5	1229.5	1229.5	1229.5	1229.5
2.5°	1237.3	1227.2	1229.5	1227.7	1222.6
5°	1233.8	1222.2	1226.3	1222.0	1222.0
7.5°	1225.4	1212.8	1216.8	1212.5	1212.3
10°	1217.7	1205.0	1209.0	1204.7	1203.7
12.5°	1206.5	1193.8	1198.7	1193.5	1193.3
15°	1186.4	1174.8	1179.9	1175.6	1173.5
17.5°	1163.8	1151.1	1157.3	1151.3	1150.4
20°	1146.5	1133.9	1140.1	1131.5	1131.5
22.5°	1125.8	1113.2	1120.2	1109.0	1109.0
25°	1092.7	1080.0	1085.1	1075.4	1074.3
27.5°	1053.2	1040.8	1046.1	1035.1	1034.9
30°	1024.8	1013.2	1019.4	1007.5	1006.5
32.5°	993.7	983.0	987.5	975.6	974.6
35°	944.0	934.5	937.5	926.7	925.6
37.5°	891.6	881.9	885.3	876.1	875.6
40°	854.5	848.2	849.1	841.5	839.4
42.5°	820.0	812.9	813.8	806.2	805.8
45°	767.2	762.0	761.8	754.3	754.3
47.5°	711.2	707.2	706.0	699.8	699.6
50°	672.4	669.2	668.1	662.7	661.6
52.5°	631.9	630.4	626.7	622.2	622.0
55°	569.0	566.9	561.4	558.2	557.1
57.5°	500.6	496.4	490.3	485.6	486.4
60°	451.5	447.3	438.6	436.4	436.4
62.5°	404.1	399.0	390.3	387.3	389.0
65°	336.2	329.9	322.2	320.1	321.1
67.5°	274.6	268.9	260.6	260.5	259.7
70°	234.9	231.8	225.2	225.2	225.2
72.5°	199.6	198.1	193.3	193.3	192.5
75°	153.0	153.0	150.9	149.8	148.7
77.5°	114.7	115.1	114.0	112.9	111.0
80°	90.5	92.6	91.6	90.5	89.4
82.5°	68.1	70.2	70.0	68.1	67.9
85°	35.6	38.7	38.8	38.8	38.8
87.5°	9.5	12.9	13.8	13.8	14.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.2	59.4	137.8	40.1	30.2
95°	36.4	144.5	649.6	224.8	138.6
97.5°	66.9	169.3	1000.5	715.9	490.6
100°	88.2	184.0	1076.6	1090.5	840.0
102.5°	111.7	199.9	1059.8	1395.9	1177.1
105°	148.4	225.1	973.0	1718.7	1633.8
107.5°	185.6	254.4	871.7	1809.7	1885.3
110°	211.4	275.7	813.4	1774.9	1944.6

TEST NUMBER: P523845

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	236.0	297.1	774.2	1692.5	1934.6
115°	275.8	333.3	737.8	1563.0	1835.4
117.5°	310.8	364.7	716.3	1421.4	1710.0
120°	338.8	384.0	714.0	1340.5	1617.0
122.5°	361.2	406.4	708.4	1269.5	1526.3
125°	389.2	431.6	704.2	1168.6	1397.2
127.5°	419.7	459.4	702.0	1108.3	1296.7
130°	435.4	475.1	698.6	1066.4	1230.6
132.5°	452.2	490.8	698.6	1033.6	1184.7
135°	476.0	515.7	695.8	987.1	1115.8
137.5°	498.4	537.0	695.5	947.8	1059.0
140°	515.2	554.9	694.4	915.2	1022.0
142.5°	534.3	567.4	697.8	889.2	985.1
145°	561.4	590.2	701.4	854.4	931.0
147.5°	584.7	612.6	707.6	819.1	885.4
150°	604.8	624.0	709.8	807.5	854.0
152.5°	620.5	640.8	712.1	791.7	835.0
155°	641.2	656.3	718.2	772.1	803.6
157.5°	667.0	676.0	719.6	763.2	785.7
160°	680.4	687.3	725.2	756.5	775.6
162.5°	688.3	696.2	726.3	750.8	765.5
165°	708.4	711.2	726.6	742.3	753.2
167.5°	722.1	719.7	733.1	740.2	744.5
170°	726.6	725.2	730.8	732.3	737.8
172.5°	736.7	732.0	734.2	730.1	734.5
175°	742.0	737.9	735.0	730.7	725.2
177.5°	744.3	737.7	734.2	729.7	730.8
180°	736.4	736.4	736.4	736.4	736.4

(END OF REPORT)