

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P523846

Luminaire Tested: **SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523846
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7831.2 lumens
Efficiency: N/A
Efficacy: 122.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 64.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523846

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523846

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	64	55	54	52	42	41	41	35
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16
7	57	45	37	32	52	41	34	30	35	29	25	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11505	11505	11505
5°	11590	11518	11479
10°	11570	11489	11437
15°	11494	11431	11368
20°	11418	11353	11268
25°	11281	11204	11092
30°	11073	11015	10875
35°	10783	10709	10574
40°	10438	10372	10254
45°	10154	10082	9982
50°	9789	9726	9633
55°	9283	9159	9088
60°	8449	8208	8167
65°	7444	7134	7110
70°	6428	6161	6161
75°	5532	5454	5376
80°	4877	4936	4819
85°	3822	4160	4160



TEST NUMBER: P523846

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.9	1.5
10°-20°	336.7	4.3
20°-30°	504.3	6.4
30°-40°	591.5	7.6
40°-50°	593.4	7.6
50°-60°	506.2	6.5
60°-70°	330.1	4.2
70°-80°	165.6	2.1
80°-90°	45.8	0.6
90°-100°	340.3	4.3
100°-110°	968.4	12.4
110°-120°	927.8	11.8
120°-130°	734.4	9.4
130°-140°	589.4	7.5
140°-150°	461.5	5.9
150°-160°	337.6	4.3
160°-170°	209.1	2.7
170°-180°	71.0	0.9
0°-30°	958.9	12.2
0°-40°	1550.5	19.8
0°-60°	2650.1	33.8
0°-90°	3191.7	40.8
90°-120°	2236.6	28.6
90°-150°	4021.8	51.4
90°-180°	4640.0	59.2
0°-180°	7831.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1247	1247	1247	1247	1247	
5°	1251	1240	1244	1239	1239	119
15°	1203	1192	1197	1192	1190	339
25°	1108	1095	1101	1091	1090	510
35°	957	948	951	940	939	598
45°	778	773	773	765	765	599
55°	577	575	569	566	565	513
65°	341	335	327	325	326	340
75°	155	155	153	152	151	168
85°	36	39	39	39	39	42
90°	0	0	0	0	0	3
95°	37	147	659	228	141	42
105°	150	228	987	1743	1657	159
115°	280	338	748	1585	1862	275
125°	395	438	714	1185	1417	353
135°	483	523	706	1001	1132	373
145°	569	599	711	866	944	356
155°	650	666	728	783	815	301
165°	718	721	737	753	764	202
175°	753	748	746	741	736	71
180°	747	747	747	747	747	

TEST NUMBER: P523846

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.0	1247.0	1247.0	1247.0	1247.0
2.5°	1254.9	1244.6	1247.0	1245.2	1240.0
5°	1251.4	1239.6	1243.7	1239.4	1239.4
7.5°	1242.9	1230.0	1234.1	1229.8	1229.5
10°	1235.0	1222.2	1226.3	1221.9	1220.8
12.5°	1223.6	1210.8	1215.8	1210.5	1210.3
15°	1203.3	1191.6	1196.8	1192.3	1190.2
17.5°	1180.4	1167.5	1173.8	1167.7	1166.8
20°	1162.9	1150.0	1156.3	1147.6	1147.6
22.5°	1141.9	1129.1	1136.2	1124.8	1124.8
25°	1108.2	1095.4	1100.6	1090.7	1089.6
27.5°	1068.2	1055.6	1061.0	1049.9	1049.6
30°	1039.4	1027.6	1033.9	1021.9	1020.8
32.5°	1007.9	997.0	1001.6	989.5	988.4
35°	957.4	947.8	950.8	939.9	938.8
37.5°	904.3	894.5	897.9	888.5	888.1
40°	866.7	860.3	861.2	853.5	851.4
42.5°	831.7	824.4	825.4	817.7	817.3
45°	778.2	772.8	772.7	765.0	765.0
47.5°	721.3	717.3	716.1	709.7	709.5
50°	682.0	678.8	677.6	672.1	671.1
52.5°	640.9	639.4	635.6	631.0	630.8
55°	577.1	574.9	569.4	566.1	565.0
57.5°	507.8	503.5	497.3	492.5	493.3
60°	457.9	453.7	444.8	442.6	442.6
62.5°	409.8	404.7	395.9	392.8	394.5
65°	341.0	334.6	326.8	324.6	325.7
67.5°	278.5	272.7	264.3	264.2	263.4
70°	238.3	235.1	228.4	228.4	228.4
72.5°	202.4	200.9	196.1	196.1	195.2
75°	155.2	155.2	153.0	151.9	150.8
77.5°	116.3	116.7	115.6	114.5	112.6
80°	91.8	93.9	92.9	91.8	90.7
82.5°	69.1	71.2	71.0	69.1	68.9
85°	36.1	39.3	39.3	39.3	39.3
87.5°	9.6	13.0	14.0	14.0	14.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.4	60.2	139.7	40.7	30.7
95°	36.9	146.6	658.9	228.0	140.6
97.5°	67.9	171.7	1014.7	726.1	497.6
100°	89.5	186.6	1092.0	1106.1	852.0
102.5°	113.3	202.7	1074.9	1415.8	1193.9
105°	150.5	228.3	986.9	1743.2	1657.1
107.5°	188.3	258.0	884.1	1835.5	1912.1
110°	214.4	279.7	825.0	1800.2	1972.3



TEST NUMBER: P523846

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	239.4	301.3	785.2	1716.7	1962.1
115°	279.7	338.0	748.3	1585.3	1861.6
117.5°	315.2	369.9	726.5	1441.7	1734.4
120°	343.6	389.5	724.2	1359.6	1640.1
122.5°	366.4	412.2	718.5	1287.6	1548.1
125°	394.8	437.8	714.2	1185.3	1417.1
127.5°	425.7	466.0	712.0	1124.1	1315.2
130°	441.6	481.9	708.6	1081.5	1248.2
132.5°	458.7	497.8	708.6	1048.3	1201.6
135°	482.8	523.1	705.7	1001.2	1131.7
137.5°	505.5	544.7	705.4	961.3	1074.1
140°	522.6	562.8	704.3	928.3	1036.6
142.5°	541.9	575.5	707.7	901.9	999.1
145°	569.4	598.6	711.4	866.5	944.3
147.5°	593.0	621.3	717.7	830.8	898.0
150°	613.4	632.9	719.9	819.0	866.2
152.5°	629.3	649.9	722.2	803.0	846.9
155°	650.3	665.6	728.4	783.1	815.1
157.5°	676.5	685.6	729.9	774.1	796.9
160°	690.1	697.1	735.5	767.2	786.7
162.5°	698.1	706.1	736.7	761.4	776.4
165°	718.5	721.3	737.0	752.8	763.9
167.5°	732.4	729.9	743.5	750.7	755.1
170°	737.0	735.6	741.2	742.8	748.3
172.5°	747.2	742.5	744.6	740.5	744.9
175°	752.6	748.4	745.5	741.1	735.5
177.5°	754.9	748.2	744.6	740.1	741.2
180°	746.9	746.9	746.9	746.9	746.9

(END OF REPORT)