

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523858

Luminaire Tested: **SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523858  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8711.2 lumens  
Efficiency: N/A  
Efficacy: 116.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 74.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523858

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523858

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	97	93	89	86	89	86	83	80	72	70	68	60	58	56	48	47	46				40	
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39				34	
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29				25	
5	68	57	49	43	62	52	45	40	45	39	35	37	33	30	30	27	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	28	24	22				19	
7	58	46	38	32	53	43	36	31	36	31	27	31	26	23	25	22	20				17	
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16				14	
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14				12	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14912	14912	14912
5°	15021	14929	14878
10°	14996	14890	14824
15°	14897	14816	14734
20°	14798	14715	14604
25°	14623	14522	14377
30°	14351	14277	14096
35°	13976	13881	13705
40°	13529	13443	13291
45°	13160	13067	12938
50°	12687	12607	12485
55°	12030	11871	11781
60°	10952	10638	10586
65°	9649	9245	9215
70°	8330	7987	7987
75°	7169	7069	6969
80°	6323	6397	6248
85°	4944	5399	5399



TEST NUMBER: P523858

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.8	1.8
10°-20°	436.4	5.0
20°-30°	653.7	7.5
30°-40°	766.7	8.8
40°-50°	769.1	8.8
50°-60°	656.1	7.5
60°-70°	427.9	4.9
70°-80°	214.7	2.5
80°-90°	59.4	0.7
90°-100°	335.6	3.9
100°-110°	954.8	11.0
110°-120°	914.8	10.5
120°-130°	724.0	8.3
130°-140°	581.1	6.7
140°-150°	455.0	5.2
150°-160°	332.9	3.8
160°-170°	206.2	2.4
170°-180°	70.0	0.8
0°-30°	1242.9	14.3
0°-40°	2009.6	23.1
0°-60°	3434.8	39.4
0°-90°	4136.8	47.5
90°-120°	2205.2	25.3
90°-150°	3965.3	45.5
90°-180°	4574.0	52.5
0°-180°	8711.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1616	1616	1616	1616	1616	
5°	1622	1607	1612	1606	1606	154
15°	1560	1544	1551	1545	1543	440
25°	1436	1420	1426	1414	1412	660
35°	1241	1228	1232	1218	1217	775
45°	1009	1002	1002	992	992	777
55°	748	745	738	734	732	665
65°	442	434	424	421	422	441
75°	201	201	198	197	196	218
85°	47	51	51	51	51	55
90°	0	0	0	0	0	3
95°	36	144	650	225	139	42
105°	148	225	973	1719	1634	157
115°	276	333	738	1563	1835	272
125°	389	432	704	1169	1397	348
135°	476	516	696	987	1116	367
145°	561	590	701	854	931	351
155°	641	656	718	772	804	296
165°	708	711	727	742	753	199
175°	742	738	735	731	725	70
180°	736	736	736	736	736	

TEST NUMBER: P523858

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1616.3	1616.3	1616.3	1616.3	1616.3
2.5°	1626.5	1613.2	1616.3	1613.9	1607.2
5°	1621.9	1606.7	1612.0	1606.4	1606.4
7.5°	1610.9	1594.3	1599.6	1593.9	1593.6
10°	1600.7	1584.1	1589.4	1583.7	1582.3
12.5°	1586.0	1569.3	1575.8	1569.0	1568.7
15°	1559.6	1544.4	1551.1	1545.4	1542.6
17.5°	1529.9	1513.2	1521.4	1513.4	1512.3
20°	1507.2	1490.6	1498.7	1487.4	1487.4
22.5°	1480.0	1463.4	1472.6	1457.9	1457.9
25°	1436.4	1419.8	1426.5	1413.7	1412.3
27.5°	1384.5	1368.2	1375.2	1360.7	1360.5
30°	1347.1	1331.9	1340.1	1324.4	1323.1
32.5°	1306.3	1292.2	1298.1	1282.5	1281.1
35°	1240.9	1228.4	1232.4	1218.2	1216.8
37.5°	1172.1	1159.3	1163.8	1151.6	1151.1
40°	1123.3	1115.0	1116.2	1106.3	1103.5
42.5°	1078.0	1068.6	1069.8	1059.8	1059.3
45°	1008.6	1001.7	1001.5	991.6	991.6
47.5°	934.9	929.7	928.1	919.9	919.6
50°	883.9	879.8	878.3	871.1	869.8
52.5°	830.7	828.7	823.9	817.9	817.6
55°	747.9	745.2	738.0	733.7	732.4
57.5°	658.1	652.6	644.5	638.3	639.4
60°	593.5	588.0	576.5	573.7	573.7
62.5°	531.2	524.6	513.1	509.2	511.4
65°	442.0	433.7	423.5	420.7	422.1
67.5°	360.9	353.5	342.5	342.5	341.4
70°	308.8	304.7	296.1	296.1	296.1
72.5°	262.3	260.4	254.1	254.1	253.0
75°	201.1	201.1	198.3	196.9	195.5
77.5°	150.7	151.3	149.9	148.4	145.9
80°	119.0	121.8	120.4	119.0	117.6
82.5°	89.5	92.3	92.1	89.5	89.2
85°	46.7	50.9	51.0	51.0	51.0
87.5°	12.5	16.9	18.1	18.2	19.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.2	59.4	137.8	40.1	30.2
95°	36.4	144.5	649.6	224.8	138.6
97.5°	66.9	169.3	1000.5	715.9	490.6
100°	88.2	184.0	1076.6	1090.5	840.0
102.5°	111.7	199.9	1059.8	1395.9	1177.1
105°	148.4	225.1	973.0	1718.7	1633.8
107.5°	185.6	254.4	871.7	1809.7	1885.3
110°	211.4	275.7	813.4	1774.9	1944.6



TEST NUMBER: P523858

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	236.0	297.1	774.2	1692.5	1934.6
115°	275.8	333.3	737.8	1563.0	1835.4
117.5°	310.8	364.7	716.3	1421.4	1710.0
120°	338.8	384.0	714.0	1340.5	1617.0
122.5°	361.2	406.4	708.4	1269.5	1526.3
125°	389.2	431.6	704.2	1168.6	1397.2
127.5°	419.7	459.4	702.0	1108.3	1296.7
130°	435.4	475.1	698.6	1066.4	1230.6
132.5°	452.2	490.8	698.6	1033.6	1184.7
135°	476.0	515.7	695.8	987.1	1115.8
137.5°	498.4	537.0	695.5	947.8	1059.0
140°	515.2	554.9	694.4	915.2	1022.0
142.5°	534.3	567.4	697.8	889.2	985.1
145°	561.4	590.2	701.4	854.4	931.0
147.5°	584.7	612.6	707.6	819.1	885.4
150°	604.8	624.0	709.8	807.5	854.0
152.5°	620.5	640.8	712.1	791.7	835.0
155°	641.2	656.3	718.2	772.1	803.6
157.5°	667.0	676.0	719.6	763.2	785.7
160°	680.4	687.3	725.2	756.5	775.6
162.5°	688.3	696.2	726.3	750.8	765.5
165°	708.4	711.2	726.6	742.3	753.2
167.5°	722.1	719.7	733.1	740.2	744.5
170°	726.6	725.2	730.8	732.3	737.8
172.5°	736.7	732.0	734.2	730.1	734.5
175°	742.0	737.9	735.0	730.7	725.2
177.5°	744.3	737.7	734.2	729.7	730.8
180°	736.4	736.4	736.4	736.4	736.4

(END OF REPORT)