

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561861

Luminaire Tested: **SQ4-PR1-050U-100D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561861
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-100D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6486.9 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 58.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561861
CATALOG NUMBER: SQ4-PR1-050U-100D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561861

CATALOG NUMBER: SQ4-PR1-050U-100D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	55	53	50	47
3	85	75	68	62	79	71	65	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	38	34
5	72	60	52	46	67	57	49	44	51	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15393	15393	15393
5°	15532	15412	15332
10°	15482	15375	15294
15°	15414	15319	15236
20°	15337	15238	15125
25°	15229	15126	14951
30°	15065	14958	14743
35°	14843	14713	14502
40°	14505	14348	14089
45°	13913	13669	13388
50°	12871	12562	12314
55°	11234	10980	10748
60°	9466	9387	9202
65°	8189	8219	8156
70°	7521	7559	7559
75°	7222	7222	7276
80°	6796	6870	6796
85°	5473	6087	6087



TEST NUMBER: P561861

CATALOG NUMBER: SQ4-PR1-050U-100D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.8	2.4
10°-20°	451.4	7.0
20°-30°	680.9	10.5
30°-40°	811.3	12.5
40°-50°	799.8	12.3
50°-60°	611.3	9.4
60°-70°	378.3	5.8
70°-80°	214.8	3.3
80°-90°	65.3	1.0
90°-100°	169.9	2.6
100°-110°	483.4	7.5
110°-120°	463.2	7.1
120°-130°	366.6	5.7
130°-140°	294.2	4.5
140°-150°	230.4	3.6
150°-160°	168.5	2.6
160°-170°	104.4	1.6
170°-180°	35.4	0.5
0°-30°	1290.0	19.9
0°-40°	2101.3	32.4
0°-60°	3512.4	54.1
0°-90°	4170.9	64.3
90°-120°	1116.5	17.2
90°-150°	2007.7	30.9
90°-180°	2316.0	35.7
0°-180°	6486.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1668	1668	1668	1668	1668	
5°	1677	1659	1664	1658	1656	159
15°	1614	1597	1604	1598	1595	455
25°	1496	1478	1486	1470	1469	688
35°	1318	1302	1306	1289	1288	822
45°	1066	1052	1048	1029	1026	817
55°	698	687	683	671	668	626
65°	375	372	376	374	374	380
75°	203	203	203	204	204	214
85°	52	54	58	58	58	60
90°	0	0	0	0	0	3
95°	18	73	329	114	70	21
105°	75	114	493	870	827	79
115°	140	169	374	791	929	137
125°	197	218	356	592	707	176
135°	241	261	352	500	565	186
145°	284	299	355	433	471	178
155°	325	332	364	391	407	150
165°	359	360	368	376	381	101
175°	376	374	372	370	367	36
180°	373	373	373	373	373	

TEST NUMBER: P561861

CATALOG NUMBER: SQ4-PR1-050U-100D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1668.4	1668.4	1668.4	1668.4	1668.4
2.5°	1678.8	1664.2	1668.4	1664.8	1656.9
5°	1677.1	1658.8	1664.1	1658.3	1655.5
7.5°	1664.1	1646.1	1651.5	1645.7	1644.0
10°	1652.6	1635.8	1641.1	1635.3	1632.5
12.5°	1640.0	1622.0	1628.5	1621.5	1618.7
15°	1613.8	1597.0	1603.8	1597.9	1595.1
17.5°	1585.1	1567.1	1573.9	1567.2	1563.5
20°	1562.1	1545.2	1552.0	1541.9	1540.5
22.5°	1536.8	1519.9	1526.7	1513.2	1512.9
25°	1496.0	1477.7	1485.9	1470.1	1468.7
27.5°	1447.4	1430.5	1437.3	1421.2	1419.5
30°	1414.1	1397.2	1404.0	1386.7	1383.9
32.5°	1376.1	1360.4	1366.1	1348.8	1347.1
35°	1317.8	1302.3	1306.3	1289.0	1287.6
37.5°	1251.4	1237.3	1239.6	1220.6	1219.2
40°	1204.3	1190.2	1191.3	1171.2	1169.8
42.5°	1152.5	1138.5	1137.3	1117.1	1115.7
45°	1066.3	1052.2	1047.6	1028.9	1026.1
47.5°	968.0	954.0	945.3	930.0	928.1
50°	896.7	882.7	875.2	862.1	857.9
52.5°	819.7	805.6	799.3	787.4	783.2
55°	698.4	687.2	682.6	671.0	668.2
57.5°	583.2	575.6	574.2	563.0	561.9
60°	513.0	508.8	508.7	498.7	498.7
62.5°	453.2	450.2	452.4	445.8	444.6
65°	375.1	372.3	376.5	373.6	373.6
67.5°	313.3	313.3	315.9	314.7	314.7
70°	278.8	278.8	280.2	280.2	280.2
72.5°	247.7	246.6	250.3	250.3	249.2
75°	202.6	202.6	202.6	204.1	204.1
77.5°	157.8	158.1	159.2	158.9	157.8
80°	127.9	129.3	129.3	127.9	127.9
82.5°	98.0	99.4	99.4	99.1	98.0
85°	51.7	54.5	57.5	57.5	57.5
87.5°	14.9	19.4	23.0	23.0	21.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.7	30.1	69.8	20.3	15.3
95°	18.4	73.2	328.9	113.8	70.2
97.5°	33.9	85.7	506.5	362.5	248.4
100°	44.7	93.2	545.1	552.1	425.3
102.5°	56.6	101.2	536.6	706.7	596.0
105°	75.1	114.0	492.6	870.2	827.2
107.5°	94.0	128.8	441.3	916.3	954.5
110°	107.0	139.6	411.8	898.6	984.6

TEST NUMBER: P561861

CATALOG NUMBER: SQ4-PR1-050U-100D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	119.5	150.4	392.0	856.9	979.5
115°	139.6	168.8	373.6	791.4	929.3
117.5°	157.4	184.7	362.6	719.7	865.8
120°	171.5	194.4	361.5	678.7	818.7
122.5°	182.9	205.8	358.7	642.8	772.8
125°	197.1	218.5	356.5	591.7	707.4
127.5°	212.5	232.6	355.4	561.2	656.5
130°	220.4	240.5	353.7	539.9	623.1
132.5°	229.0	248.5	353.7	523.3	599.8
135°	241.0	261.1	352.3	499.8	564.9
137.5°	252.3	271.9	352.2	479.9	536.2
140°	260.9	281.0	351.6	463.4	517.5
142.5°	270.5	287.3	353.3	450.2	498.7
145°	284.2	298.8	355.1	432.6	471.4
147.5°	296.0	310.2	358.2	414.7	448.3
150°	306.2	315.9	359.4	408.8	432.4
152.5°	314.2	324.4	360.5	400.9	422.8
155°	324.6	332.3	363.6	390.9	406.9
157.5°	337.7	342.3	364.3	386.4	397.8
160°	344.5	348.0	367.2	383.0	392.7
162.5°	348.5	352.5	367.7	380.1	387.6
165°	358.7	360.1	367.9	375.8	381.4
167.5°	365.6	364.4	371.1	374.7	377.0
170°	367.9	367.2	370.0	370.8	373.6
172.5°	373.0	370.6	371.7	369.6	371.9
175°	375.7	373.6	372.1	370.0	367.2
177.5°	376.8	373.5	371.7	369.5	370.0
180°	372.9	372.9	372.9	372.9	372.9

(END OF REPORT)