

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523883

Luminaire Tested: **SQ4-PP3-125U-050D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523883
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-050D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7760.8 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523883
CATALOG NUMBER: SQ4-PP3-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523883

CATALOG NUMBER: SQ4-PP3-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	21	16
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	22	20	18	14
5	65	53	46	40	57	48	41	36	38	33	29	28	25	23	19	18	16	12
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7492	7492	7492
5°	7546	7501	7474
10°	7534	7481	7447
15°	7484	7444	7403
20°	7434	7392	7336
25°	7346	7295	7223
30°	7210	7172	7081
35°	7021	6973	6885
40°	6796	6754	6677
45°	6611	6564	6500
50°	6374	6333	6272
55°	6043	5964	5918
60°	5503	5344	5318
65°	4846	4646	4630
70°	4184	4011	4011
75°	3604	3550	3501
80°	3177	3214	3140
85°	2488	2710	2710



TEST NUMBER: P523883

CATALOG NUMBER: SQ4-PP3-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.0
10°-20°	219.2	2.8
20°-30°	328.4	4.2
30°-40°	385.2	5.0
40°-50°	386.4	5.0
50°-60°	329.6	4.2
60°-70°	215.0	2.8
70°-80°	107.9	1.4
80°-90°	29.9	0.4
90°-100°	416.8	5.4
100°-110°	1186.1	15.3
110°-120°	1136.4	14.6
120°-130°	899.4	11.6
130°-140°	721.9	9.3
140°-150°	565.2	7.3
150°-160°	413.5	5.3
160°-170°	256.2	3.3
170°-180°	86.9	1.1
0°-30°	624.4	8.0
0°-40°	1009.6	13.0
0°-60°	1725.6	22.2
0°-90°	2078.3	26.8
90°-120°	2739.4	35.3
90°-150°	4925.9	63.5
90°-180°	5682.0	73.2
0°-180°	7760.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	812	812	812	812	812	
5°	815	807	810	807	807	77
15°	784	776	779	776	775	221
25°	722	713	717	710	710	332
35°	623	617	619	612	611	389
45°	507	503	503	498	498	390
55°	376	374	371	369	368	334
65°	222	218	213	211	212	222
75°	101	101	100	99	98	110
85°	24	26	26	26	26	28
90°	0	0	0	0	0	3
95°	45	180	807	279	172	52
105°	184	280	1209	2135	2030	195
115°	343	414	916	1942	2280	337
125°	484	536	875	1452	1736	433
135°	591	641	864	1226	1386	456
145°	697	733	871	1061	1157	436
155°	796	815	892	959	998	368
165°	880	883	903	922	936	247
175°	922	917	913	908	901	87
180°	915	915	915	915	915	



TEST NUMBER: P523883

CATALOG NUMBER: SQ4-PP3-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	812.0	812.0	812.0	812.0	812.0
2.5°	817.1	810.4	812.0	810.8	807.4
5°	814.8	807.2	809.9	807.0	807.0
7.5°	809.3	800.9	803.6	800.7	800.6
10°	804.2	795.8	798.5	795.6	794.9
12.5°	796.8	788.4	791.6	788.2	788.1
15°	783.5	775.9	779.3	776.4	775.0
17.5°	768.6	760.2	764.3	760.3	759.8
20°	757.2	748.8	752.9	747.2	747.2
22.5°	743.5	735.2	739.8	732.4	732.4
25°	721.6	713.3	716.6	710.2	709.5
27.5°	695.6	687.4	690.9	683.6	683.5
30°	676.8	669.1	673.2	665.4	664.7
32.5°	656.3	649.2	652.2	644.3	643.6
35°	623.4	617.1	619.1	612.0	611.3
37.5°	588.8	582.4	584.7	578.6	578.3
40°	564.3	560.2	560.8	555.8	554.4
42.5°	541.6	536.8	537.4	532.4	532.2
45°	506.7	503.2	503.1	498.2	498.2
47.5°	469.7	467.0	466.3	462.1	462.0
50°	444.1	442.0	441.2	437.6	437.0
52.5°	417.3	416.3	413.9	410.9	410.8
55°	375.7	374.4	370.8	368.6	367.9
57.5°	330.6	327.8	323.8	320.7	321.2
60°	298.2	295.4	289.6	288.2	288.2
62.5°	266.9	263.5	257.8	255.8	256.9
65°	222.0	217.9	212.8	211.4	212.1
67.5°	181.3	177.6	172.1	172.1	171.5
70°	155.1	153.1	148.7	148.7	148.7
72.5°	131.8	130.8	127.7	127.7	127.1
75°	101.1	101.1	99.6	98.9	98.2
77.5°	75.7	76.0	75.3	74.6	73.3
80°	59.8	61.2	60.5	59.8	59.1
82.5°	45.0	46.4	46.3	45.0	44.8
85°	23.5	25.6	25.6	25.6	25.6
87.5°	6.3	8.5	9.1	9.1	9.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.9	73.8	171.1	49.8	37.6
95°	45.2	179.6	807.0	279.3	172.2
97.5°	83.1	210.3	1242.8	889.3	609.4
100°	109.6	228.6	1337.4	1354.7	1043.5
102.5°	138.8	248.3	1316.6	1734.0	1462.3
105°	184.4	279.6	1208.7	2135.1	2029.6
107.5°	230.6	316.0	1082.8	2248.1	2342.0
110°	262.6	342.5	1010.5	2204.9	2415.7

TEST NUMBER: P523883

CATALOG NUMBER: SQ4-PP3-125U-050D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	293.2	369.1	961.8	2102.5	2403.2
115°	342.6	414.0	916.5	1941.7	2280.1
117.5°	386.1	453.1	889.8	1765.8	2124.2
120°	420.9	477.0	887.0	1665.2	2008.8
122.5°	448.7	504.8	880.0	1577.0	1896.1
125°	483.5	536.2	874.8	1451.7	1735.7
127.5°	521.4	570.7	872.0	1376.8	1610.8
130°	540.9	590.2	867.9	1324.7	1528.7
132.5°	561.8	609.7	867.9	1284.0	1471.7
135°	591.3	640.6	864.4	1226.3	1386.1
137.5°	619.1	667.1	864.0	1177.4	1315.5
140°	640.0	689.3	862.6	1137.0	1269.6
142.5°	663.7	704.8	866.8	1104.6	1223.7
145°	697.4	733.1	871.3	1061.3	1156.6
147.5°	726.3	761.0	879.0	1017.6	1099.9
150°	751.3	775.1	881.8	1003.1	1060.9
152.5°	770.8	796.0	884.5	983.5	1037.2
155°	796.5	815.2	892.2	959.2	998.3
157.5°	828.5	839.8	893.9	948.1	976.0
160°	845.2	853.7	900.9	939.7	963.5
162.5°	855.0	864.8	902.3	932.6	951.0
165°	880.0	883.4	902.6	922.1	935.7
167.5°	897.1	894.0	910.6	919.5	924.9
170°	902.6	900.9	907.9	909.7	916.5
172.5°	915.2	909.4	912.0	906.9	912.4
175°	921.8	916.7	913.1	907.7	900.9
177.5°	924.5	916.4	912.0	906.5	907.9
180°	914.8	914.8	914.8	914.8	914.8

(END OF REPORT)