

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523906

Luminaire Tested: **SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523906
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9224.7 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 83.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523906

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523906

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36				
2	88	80	74	69	80	74	69	64	61	57	54	49	47	44	38	37	35	30				
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26				
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22				
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	27	25	23	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	28	24	25	22	20	17				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13920	13920	13920
5°	14022	13937	13888
10°	13998	13899	13837
15°	13906	13830	13754
20°	13813	13736	13632
25°	13649	13556	13420
30°	13397	13326	13157
35°	13046	12957	12794
40°	12629	12550	12406
45°	12285	12198	12077
50°	11843	11767	11654
55°	11231	11081	10996
60°	10223	9931	9881
65°	9007	8632	8601
70°	7777	7456	7456
75°	6695	6598	6506
80°	5903	5972	5834
85°	4615	5039	5039



TEST NUMBER: P523906

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.7	1.5
10°-20°	407.4	4.4
20°-30°	610.2	6.6
30°-40°	715.7	7.8
40°-50°	717.9	7.8
50°-60°	612.5	6.6
60°-70°	399.4	4.3
70°-80°	200.4	2.2
80°-90°	55.5	0.6
90°-100°	393.4	4.3
100°-110°	1119.5	12.1
110°-120°	1072.5	11.6
120°-130°	848.9	9.2
130°-140°	681.4	7.4
140°-150°	533.4	5.8
150°-160°	390.3	4.2
160°-170°	241.8	2.6
170°-180°	82.0	0.9
0°-30°	1160.2	12.6
0°-40°	1875.9	20.3
0°-60°	3206.3	34.8
0°-90°	3861.6	41.9
90°-120°	2585.4	28.0
90°-150°	4649.1	50.4
90°-180°	5363.0	58.1
0°-180°	9224.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1509	1509	1509	1509	1509	
5°	1514	1500	1505	1500	1500	144
15°	1456	1442	1448	1443	1440	411
25°	1341	1325	1332	1320	1318	617
35°	1158	1147	1150	1137	1136	724
45°	942	935	935	926	926	725
55°	698	696	689	685	684	620
65°	413	405	395	393	394	412
75°	188	188	185	184	182	204
85°	44	48	48	48	48	51
90°	0	0	0	0	0	3
95°	43	170	762	264	162	49
105°	174	264	1141	2015	1916	184
115°	323	391	865	1832	2152	318
125°	456	506	826	1370	1638	408
135°	558	605	816	1157	1308	431
145°	658	692	822	1002	1092	411
155°	752	769	842	905	942	348
165°	831	834	852	870	883	234
175°	870	865	862	857	850	82
180°	863	863	863	863	863	

TEST NUMBER: P523906

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1508.7	1508.7	1508.7	1508.7	1508.7
2.5°	1518.3	1505.9	1508.7	1506.5	1500.3
5°	1514.0	1499.8	1504.8	1499.5	1499.5
7.5°	1503.7	1488.2	1493.1	1487.8	1487.6
10°	1494.2	1478.7	1483.6	1478.3	1477.0
12.5°	1480.4	1464.9	1470.9	1464.6	1464.3
15°	1455.9	1441.6	1447.9	1442.6	1440.0
17.5°	1428.1	1412.6	1420.2	1412.7	1411.7
20°	1406.9	1391.4	1399.0	1388.4	1388.4
22.5°	1381.5	1366.0	1374.7	1360.9	1360.9
25°	1340.8	1325.3	1331.6	1319.6	1318.3
27.5°	1292.4	1277.2	1283.7	1270.2	1269.9
30°	1257.5	1243.3	1250.9	1236.3	1235.0
32.5°	1219.4	1206.2	1211.8	1197.2	1195.9
35°	1158.3	1146.7	1150.4	1137.2	1135.9
37.5°	1094.1	1082.2	1086.4	1075.0	1074.5
40°	1048.6	1040.8	1042.0	1032.7	1030.1
42.5°	1006.3	997.5	998.6	989.3	988.8
45°	941.5	935.0	934.9	925.6	925.6
47.5°	872.7	867.8	866.4	858.7	858.4
50°	825.1	821.2	819.8	813.2	811.9
52.5°	775.4	773.6	769.1	763.5	763.2
55°	698.2	695.6	688.9	684.9	683.6
57.5°	614.3	609.2	601.6	595.9	596.9
60°	554.0	548.9	538.2	535.5	535.5
62.5°	495.9	489.7	478.9	475.3	477.4
65°	412.6	404.8	395.4	392.8	394.0
67.5°	336.9	329.9	319.7	319.7	318.7
70°	288.3	284.4	276.4	276.4	276.4
72.5°	244.9	243.1	237.2	237.2	236.2
75°	187.8	187.8	185.1	183.8	182.5
77.5°	140.7	141.2	139.9	138.5	136.2
80°	111.1	113.7	112.4	111.0	109.8
82.5°	83.6	86.2	85.9	83.6	83.3
85°	43.6	47.5	47.6	47.6	47.6
87.5°	11.6	15.8	16.9	16.9	18.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.1	69.6	161.5	47.0	35.5
95°	42.7	169.5	761.6	263.6	162.5
97.5°	78.5	198.5	1173.0	839.3	575.2
100°	103.4	215.8	1262.3	1278.6	984.9
102.5°	131.0	234.3	1242.6	1636.6	1380.1
105°	174.0	263.9	1140.8	2015.1	1915.6
107.5°	217.7	298.2	1022.0	2121.8	2210.4
110°	247.9	323.3	953.7	2080.9	2279.9

TEST NUMBER: P523906

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	276.7	348.3	907.7	1984.4	2268.1
115°	323.4	390.8	865.0	1832.5	2151.9
117.5°	364.4	427.6	839.8	1666.5	2004.8
120°	397.2	450.2	837.1	1571.7	1895.9
122.5°	423.5	476.5	830.6	1488.4	1789.5
125°	456.3	506.1	825.6	1370.1	1638.1
127.5°	492.1	538.6	823.0	1299.5	1520.3
130°	510.5	557.0	819.1	1250.2	1442.8
132.5°	530.2	575.4	819.1	1211.8	1389.0
135°	558.1	604.6	815.8	1157.4	1308.2
137.5°	584.3	629.6	815.5	1111.3	1241.6
140°	604.0	650.6	814.2	1073.1	1198.2
142.5°	626.4	665.2	818.1	1042.6	1154.9
145°	658.2	691.9	822.4	1001.7	1091.6
147.5°	685.5	718.2	829.6	960.4	1038.0
150°	709.1	731.6	832.2	946.7	1001.3
152.5°	727.5	751.2	834.8	928.2	978.9
155°	751.8	769.4	842.1	905.3	942.2
157.5°	782.0	792.6	843.7	894.9	921.2
160°	797.7	805.8	850.3	886.9	909.4
162.5°	806.9	816.2	851.6	880.2	897.5
165°	830.6	833.8	851.9	870.3	883.1
167.5°	846.7	843.8	859.5	867.8	872.9
170°	851.9	850.3	856.8	858.6	865.0
172.5°	863.7	858.3	860.8	856.0	861.1
175°	870.0	865.1	861.8	856.7	850.3
177.5°	872.6	864.9	860.8	855.5	856.8
180°	863.4	863.4	863.4	863.4	863.4

(END OF REPORT)