

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523907

Luminaire Tested: **SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523907  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9446.1 lumens  
Efficiency: N/A  
Efficacy: 112.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 83.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523907  
CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523907

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	80	74	69	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	27	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	31	28	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14254	14254	14254
5°	14359	14271	14221
10°	14335	14233	14170
15°	14240	14162	14084
20°	14145	14066	13959
25°	13977	13880	13743
30°	13719	13646	13473
35°	13359	13268	13100
40°	12932	12851	12704
45°	12579	12491	12367
50°	12127	12050	11933
55°	11499	11348	11260
60°	10468	10169	10119
65°	9224	8839	8809
70°	7963	7634	7634
75°	6855	6759	6662
80°	6041	6115	5972
85°	4732	5155	5155



TEST NUMBER: P523907

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.1	1.5
10°-20°	417.1	4.4
20°-30°	624.8	6.6
30°-40°	732.9	7.8
40°-50°	735.2	7.8
50°-60°	627.2	6.6
60°-70°	409.0	4.3
70°-80°	205.2	2.2
80°-90°	56.8	0.6
90°-100°	402.9	4.3
100°-110°	1146.3	12.1
110°-120°	1098.3	11.6
120°-130°	869.3	9.2
130°-140°	697.7	7.4
140°-150°	546.2	5.8
150°-160°	399.7	4.2
160°-170°	247.6	2.6
170°-180°	84.0	0.9
0°-30°	1188.0	12.6
0°-40°	1920.9	20.3
0°-60°	3283.2	34.8
0°-90°	3954.2	41.9
90°-120°	2647.5	28.0
90°-150°	4760.6	50.4
90°-180°	5492.0	58.1
0°-180°	9446.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1545	1545	1545	1545	1545	
5°	1550	1536	1541	1536	1536	147
15°	1491	1476	1483	1477	1474	421
25°	1373	1357	1364	1351	1350	631
35°	1186	1174	1178	1164	1163	741
45°	964	958	957	948	948	742
55°	715	712	706	701	700	635
65°	422	414	405	402	404	422
75°	192	192	190	188	187	209
85°	45	49	49	49	49	52
90°	0	0	0	0	0	3
95°	44	174	780	270	166	50
105°	178	270	1168	2063	1962	188
115°	331	400	886	1876	2204	326
125°	467	518	846	1403	1678	418
135°	572	619	835	1185	1340	441
145°	674	708	842	1026	1118	421
155°	770	788	862	927	965	356
165°	850	854	872	891	904	239
175°	891	886	882	877	871	84
180°	884	884	884	884	884	

TEST NUMBER: P523907

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1545.0	1545.0	1545.0	1545.0	1545.0
2.5°	1554.7	1542.0	1545.0	1542.6	1536.3
5°	1550.4	1535.8	1540.9	1535.5	1535.5
7.5°	1539.8	1523.9	1529.0	1523.6	1523.3
10°	1530.1	1514.2	1519.2	1513.8	1512.5
12.5°	1516.0	1500.1	1506.2	1499.7	1499.5
15°	1490.8	1476.2	1482.7	1477.2	1474.5
17.5°	1462.4	1446.5	1454.2	1446.6	1445.6
20°	1440.7	1424.8	1432.6	1421.7	1421.7
22.5°	1414.7	1398.8	1407.7	1393.6	1393.6
25°	1373.0	1357.1	1363.5	1351.3	1350.0
27.5°	1323.4	1307.8	1314.5	1300.7	1300.4
30°	1287.7	1273.1	1280.9	1266.0	1264.7
32.5°	1248.7	1235.2	1240.8	1225.9	1224.6
35°	1186.1	1174.2	1178.0	1164.4	1163.1
37.5°	1120.3	1108.1	1112.5	1100.8	1100.3
40°	1073.7	1065.8	1067.0	1057.4	1054.8
42.5°	1030.4	1021.4	1022.6	1013.1	1012.5
45°	964.1	957.5	957.3	947.8	947.8
47.5°	893.7	888.6	887.2	879.3	879.0
50°	844.9	840.9	839.5	832.7	831.4
52.5°	794.0	792.2	787.5	781.8	781.5
55°	714.9	712.3	705.5	701.4	700.0
57.5°	629.1	623.8	616.1	610.2	611.2
60°	567.3	562.0	551.1	548.4	548.4
62.5°	507.8	501.4	490.4	486.7	488.8
65°	422.5	414.5	404.9	402.2	403.5
67.5°	345.0	337.9	327.4	327.4	326.3
70°	295.2	291.2	283.0	283.0	283.0
72.5°	250.8	248.9	242.9	242.9	241.8
75°	192.3	192.3	189.6	188.2	186.9
77.5°	144.1	144.6	143.3	141.8	139.5
80°	113.7	116.4	115.1	113.7	112.4
82.5°	85.6	88.2	88.0	85.6	85.3
85°	44.7	48.7	48.7	48.7	48.7
87.5°	11.9	16.2	17.3	17.4	18.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.4	71.3	165.4	48.1	36.3
95°	43.7	173.5	779.9	269.9	166.4
97.5°	80.3	203.3	1201.1	859.5	589.0
100°	105.9	220.9	1292.6	1309.2	1008.5
102.5°	134.1	240.0	1272.4	1675.9	1413.2
105°	178.2	270.2	1168.2	2063.4	1961.5
107.5°	222.9	305.4	1046.5	2172.7	2263.4
110°	253.8	331.0	976.6	2130.9	2334.7

TEST NUMBER: P523907

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	283.4	356.7	929.5	2032.0	2322.6
115°	331.1	400.1	885.8	1876.5	2203.6
117.5°	373.1	437.9	859.9	1706.5	2053.0
120°	406.8	461.0	857.2	1609.4	1941.3
122.5°	433.7	487.9	850.5	1524.1	1832.4
125°	467.3	518.2	845.5	1403.0	1677.5
127.5°	503.9	551.6	842.8	1330.6	1556.8
130°	522.7	570.4	838.7	1280.2	1477.4
132.5°	542.9	589.3	838.7	1240.9	1422.3
135°	571.5	619.1	835.4	1185.1	1339.6
137.5°	598.4	644.7	835.0	1137.9	1271.4
140°	618.5	666.2	833.7	1098.8	1227.0
142.5°	641.4	681.2	837.7	1067.6	1182.6
145°	674.0	708.5	842.1	1025.7	1117.7
147.5°	701.9	735.4	849.5	983.4	1063.0
150°	726.1	749.1	852.2	969.4	1025.3
152.5°	744.9	769.3	854.9	950.5	1002.4
155°	769.8	787.9	862.3	927.0	964.8
157.5°	800.7	811.6	863.9	916.3	943.3
160°	816.9	825.1	870.7	908.2	931.2
162.5°	826.3	835.8	872.0	901.3	919.1
165°	850.5	853.8	872.3	891.1	904.3
167.5°	867.0	864.0	880.1	888.6	893.9
170°	872.3	870.7	877.4	879.2	885.8
172.5°	884.4	878.9	881.4	876.5	881.8
175°	890.8	885.9	882.4	877.2	870.7
177.5°	893.5	885.6	881.4	876.1	877.4
180°	884.1	884.1	884.1	884.1	884.1

(END OF REPORT)