

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523908

Luminaire Tested: **SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523908  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (4000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9618.8 lumens  
Efficiency: N/A  
Efficacy: 114.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 83.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523908  
CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523908

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	80	74	69	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	27	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	31	28	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14515	14515	14515
5°	14621	14532	14481
10°	14596	14493	14428
15°	14500	14421	14342
20°	14403	14323	14214
25°	14233	14135	13994
30°	13969	13895	13720
35°	13604	13511	13340
40°	13169	13086	12936
45°	12809	12719	12594
50°	12350	12271	12152
55°	11710	11556	11466
60°	10660	10355	10304
65°	9392	9001	8970
70°	8109	7774	7774
75°	6980	6880	6784
80°	6153	6227	6078
85°	4817	5251	5251



TEST NUMBER: P523908

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.8	1.5
10°-20°	424.8	4.4
20°-30°	636.2	6.6
30°-40°	746.3	7.8
40°-50°	748.6	7.8
50°-60°	638.6	6.6
60°-70°	416.5	4.3
70°-80°	209.0	2.2
80°-90°	57.8	0.6
90°-100°	410.2	4.3
100°-110°	1167.3	12.1
110°-120°	1118.4	11.6
120°-130°	885.2	9.2
130°-140°	710.5	7.4
140°-150°	556.2	5.8
150°-160°	407.0	4.2
160°-170°	252.1	2.6
170°-180°	85.5	0.9
0°-30°	1209.8	12.6
0°-40°	1956.0	20.3
0°-60°	3343.3	34.8
0°-90°	4026.5	41.9
90°-120°	2695.9	28.0
90°-150°	4847.7	50.4
90°-180°	5592.0	58.1
0°-180°	9618.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1573	1573	1573	1573	1573	
5°	1579	1564	1569	1564	1564	150
15°	1518	1503	1510	1504	1502	428
25°	1398	1382	1388	1376	1375	643
35°	1208	1196	1200	1186	1184	754
45°	982	975	975	965	965	756
55°	728	725	718	714	713	647
65°	430	422	412	410	411	429
75°	196	196	193	192	190	212
85°	46	50	50	50	50	53
90°	0	0	0	0	0	4
95°	44	177	794	275	169	51
105°	181	275	1190	2101	1997	192
115°	337	408	902	1911	2244	332
125°	476	528	861	1429	1708	426
135°	582	630	851	1207	1364	449
145°	686	722	858	1044	1138	429
155°	784	802	878	944	982	362
165°	866	869	888	907	921	244
175°	907	902	899	893	887	86
180°	900	900	900	900	900	



TEST NUMBER: P523908

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1573.2	1573.2	1573.2	1573.2	1573.2
2.5°	1583.1	1570.2	1573.2	1570.9	1564.4
5°	1578.7	1563.9	1569.1	1563.6	1563.6
7.5°	1568.0	1551.8	1556.9	1551.4	1551.2
10°	1558.0	1541.9	1547.0	1541.5	1540.1
12.5°	1543.7	1527.5	1533.8	1527.2	1526.9
15°	1518.1	1503.2	1509.8	1504.2	1501.5
17.5°	1489.1	1472.9	1480.8	1473.1	1472.0
20°	1467.0	1450.9	1458.8	1447.7	1447.7
22.5°	1440.6	1424.4	1433.4	1419.1	1419.1
25°	1398.1	1381.9	1388.5	1376.0	1374.7
27.5°	1347.6	1331.7	1338.5	1324.5	1324.2
30°	1311.2	1296.4	1304.3	1289.2	1287.8
32.5°	1271.5	1257.8	1263.5	1248.3	1247.0
35°	1207.8	1195.7	1199.6	1185.7	1184.4
37.5°	1140.8	1128.4	1132.8	1121.0	1120.4
40°	1093.4	1085.3	1086.5	1076.8	1074.1
42.5°	1049.3	1040.1	1041.3	1031.6	1031.1
45°	981.7	975.0	974.8	965.2	965.2
47.5°	910.0	904.9	903.4	895.4	895.1
50°	860.4	856.3	854.9	847.9	846.6
52.5°	808.5	806.6	801.9	796.1	795.8
55°	728.0	725.3	718.4	714.2	712.8
57.5°	640.6	635.2	627.4	621.3	622.4
60°	577.7	572.3	561.2	558.4	558.4
62.5°	517.1	510.6	499.4	495.6	497.7
65°	430.2	422.1	412.3	409.5	410.9
67.5°	351.3	344.0	333.4	333.4	332.3
70°	300.6	296.5	288.2	288.2	288.2
72.5°	255.4	253.5	247.4	247.3	246.3
75°	195.8	195.8	193.0	191.6	190.3
77.5°	146.7	147.2	145.9	144.4	142.0
80°	115.8	118.5	117.2	115.8	114.4
82.5°	87.1	89.8	89.6	87.1	86.9
85°	45.5	49.5	49.6	49.6	49.6
87.5°	12.1	16.4	17.6	17.7	18.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.7	72.6	168.4	49.0	37.0
95°	44.5	176.7	794.2	274.9	169.4
97.5°	81.8	207.0	1223.1	875.2	599.7
100°	107.8	225.0	1316.2	1333.2	1026.9
102.5°	136.6	244.4	1295.7	1706.5	1439.1
105°	181.4	275.1	1189.5	2101.2	1997.4
107.5°	227.0	311.0	1065.6	2212.4	2304.8
110°	258.4	337.1	994.4	2169.9	2377.4



TEST NUMBER: P523908

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	288.6	363.2	946.5	2069.2	2365.0
115°	337.2	407.5	902.0	1910.8	2243.9
117.5°	380.0	445.9	875.6	1737.7	2090.5
120°	414.2	469.4	872.9	1638.8	1976.9
122.5°	441.6	496.8	866.1	1552.0	1866.0
125°	475.8	527.7	860.9	1428.7	1708.1
127.5°	513.1	561.7	858.2	1355.0	1585.3
130°	532.3	580.8	854.1	1303.6	1504.5
132.5°	552.8	600.0	854.1	1263.6	1448.3
135°	581.9	630.5	850.7	1206.8	1364.1
137.5°	609.3	656.5	850.3	1158.7	1294.6
140°	629.9	678.4	848.9	1118.9	1249.4
142.5°	653.1	693.6	853.0	1087.1	1204.3
145°	686.3	721.5	857.5	1044.5	1138.2
147.5°	714.8	748.9	865.0	1001.4	1082.4
150°	739.4	762.8	867.8	987.2	1044.1
152.5°	758.6	783.3	870.5	967.9	1020.8
155°	783.9	802.3	878.0	943.9	982.4
157.5°	815.4	826.4	879.7	933.1	960.5
160°	831.8	840.2	886.6	924.8	948.2
162.5°	841.4	851.1	888.0	917.8	935.9
165°	866.1	869.4	888.3	907.4	920.8
167.5°	882.8	879.8	896.2	904.9	910.2
170°	888.3	886.6	893.4	895.3	902.0
172.5°	900.6	894.9	897.5	892.5	897.9
175°	907.1	902.1	898.6	893.3	886.6
177.5°	909.9	901.8	897.5	892.1	893.4
180°	900.3	900.3	900.3	900.3	900.3

(END OF REPORT)