

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523911

Luminaire Tested: **SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523911
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10022.9 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 83.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523911

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523911

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	80	74	69	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	27	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	31	28	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15125	15125	15125
5°	15235	15142	15089
10°	15210	15102	15035
15°	15109	15027	14945
20°	15009	14925	14812
25°	14830	14728	14582
30°	14556	14479	14296
35°	14176	14079	13900
40°	13722	13635	13480
45°	13347	13254	13122
50°	12868	12786	12661
55°	12202	12040	11948
60°	11108	10789	10737
65°	9787	9379	9346
70°	8449	8101	8101
75°	7272	7169	7069
80°	6413	6487	6333
85°	5018	5473	5473



TEST NUMBER: P523911

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	1.5
10°-20°	442.6	4.4
20°-30°	663.0	6.6
30°-40°	777.6	7.8
40°-50°	780.0	7.8
50°-60°	665.5	6.6
60°-70°	434.0	4.3
70°-80°	217.7	2.2
80°-90°	60.2	0.6
90°-100°	427.5	4.3
100°-110°	1216.3	12.1
110°-120°	1165.4	11.6
120°-130°	922.3	9.2
130°-140°	740.3	7.4
140°-150°	579.6	5.8
150°-160°	424.1	4.2
160°-170°	262.7	2.6
170°-180°	89.1	0.9
0°-30°	1260.6	12.6
0°-40°	2038.2	20.3
0°-60°	3483.7	34.8
0°-90°	4195.7	41.9
90°-120°	2809.1	28.0
90°-150°	5051.4	50.4
90°-180°	5827.0	58.1
0°-180°	10022.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1639	1639	1639	1639	1639	
5°	1645	1630	1635	1629	1629	156
15°	1582	1566	1573	1567	1565	446
25°	1457	1440	1447	1434	1432	670
35°	1259	1246	1250	1236	1234	786
45°	1023	1016	1016	1006	1006	788
55°	759	756	748	744	743	674
65°	448	440	430	427	428	447
75°	204	204	201	200	198	221
85°	47	52	52	52	52	56
90°	0	0	0	0	0	4
95°	46	184	828	286	177	53
105°	189	287	1240	2189	2081	200
115°	351	425	940	1991	2338	346
125°	496	550	897	1489	1780	444
135°	606	657	886	1258	1421	468
145°	715	752	894	1088	1186	447
155°	817	836	915	984	1024	378
165°	902	906	926	946	960	254
175°	945	940	936	931	924	90
180°	938	938	938	938	938	



TEST NUMBER: P523911

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1639.3	1639.3	1639.3	1639.3	1639.3
2.5°	1649.6	1636.2	1639.3	1636.9	1630.1
5°	1645.0	1629.6	1635.0	1629.2	1629.2
7.5°	1633.8	1617.0	1622.3	1616.6	1616.3
10°	1623.5	1606.6	1612.0	1606.2	1604.8
12.5°	1608.6	1591.7	1598.2	1591.3	1591.0
15°	1581.8	1566.4	1573.2	1567.4	1564.6
17.5°	1551.7	1534.8	1543.0	1535.0	1533.8
20°	1528.7	1511.8	1520.1	1508.6	1508.6
22.5°	1501.1	1484.2	1493.6	1478.7	1478.7
25°	1456.8	1440.0	1446.8	1433.8	1432.4
27.5°	1404.3	1387.7	1394.8	1380.1	1379.8
30°	1366.3	1350.9	1359.1	1343.3	1341.9
32.5°	1324.9	1310.6	1316.6	1300.8	1299.4
35°	1258.6	1245.9	1250.0	1235.6	1234.1
37.5°	1188.7	1175.8	1180.4	1168.0	1167.5
40°	1139.3	1130.9	1132.1	1122.0	1119.2
42.5°	1093.3	1083.8	1085.0	1074.9	1074.4
45°	1022.9	1015.9	1015.8	1005.7	1005.7
47.5°	948.2	942.9	941.3	933.0	932.7
50°	896.5	892.3	890.8	883.6	882.1
52.5°	842.5	840.5	835.6	829.6	829.3
55°	758.6	755.8	748.5	744.2	742.8
57.5°	667.5	661.9	653.7	647.4	648.5
60°	602.0	596.4	584.7	581.9	581.9
62.5°	538.8	532.0	520.4	516.4	518.7
65°	448.3	439.8	429.6	426.7	428.1
67.5°	366.1	358.5	347.4	347.4	346.3
70°	313.2	309.0	300.3	300.3	300.3
72.5°	266.1	264.1	257.7	257.7	256.6
75°	204.0	204.0	201.1	199.7	198.3
77.5°	152.9	153.4	152.0	150.5	148.0
80°	120.7	123.5	122.1	120.7	119.2
82.5°	90.8	93.6	93.4	90.8	90.5
85°	47.4	51.6	51.7	51.7	51.7
87.5°	12.6	17.1	18.4	18.4	19.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.3	75.7	175.5	51.1	38.5
95°	46.4	184.1	827.5	286.4	176.6
97.5°	85.2	215.7	1274.5	912.0	624.9
100°	112.4	234.4	1371.5	1389.2	1070.1
102.5°	142.3	254.6	1350.1	1778.2	1499.5
105°	189.0	286.7	1239.5	2189.4	2081.3
107.5°	236.5	324.0	1110.4	2305.4	2401.6
110°	269.3	351.3	1036.2	2261.0	2477.2

TEST NUMBER: P523911

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	300.7	378.5	986.3	2156.1	2464.4
115°	351.3	424.6	939.9	1991.1	2338.1
117.5°	395.9	464.6	912.4	1810.7	2178.3
120°	431.6	489.1	909.6	1707.7	2059.9
122.5°	460.1	517.7	902.4	1617.2	1944.3
125°	495.8	549.9	897.1	1488.7	1779.9
127.5°	534.7	585.3	894.2	1411.9	1651.8
130°	554.7	605.2	890.0	1358.4	1567.7
132.5°	576.1	625.2	890.0	1316.7	1509.2
135°	606.4	657.0	886.4	1257.5	1421.4
137.5°	634.9	684.1	886.0	1207.4	1349.0
140°	656.3	706.9	884.6	1165.9	1301.9
142.5°	680.6	722.8	888.9	1132.8	1254.8
145°	715.2	751.8	893.5	1088.4	1186.0
147.5°	744.8	780.4	901.4	1043.5	1127.9
150°	770.5	794.9	904.2	1028.6	1087.9
152.5°	790.4	816.2	907.1	1008.6	1063.7
155°	816.8	836.0	914.9	983.6	1023.7
157.5°	849.6	861.2	916.7	972.3	1000.9
160°	866.8	875.5	923.8	963.6	988.0
162.5°	876.8	886.9	925.3	956.4	975.2
165°	902.4	905.9	925.6	945.6	959.5
167.5°	919.9	916.8	933.8	942.9	948.4
170°	925.6	923.9	931.0	932.9	939.9
172.5°	938.5	932.5	935.3	930.0	935.6
175°	945.2	940.0	936.3	930.8	923.8
177.5°	948.1	939.7	935.3	929.6	931.0
180°	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)