

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561923

Luminaire Tested: **SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561923
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8394.9 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 79.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561923

CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561923

CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	75	67	61	78	70	64	58	62	57	52	54	50	47	46	44	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	38	45	39	34	39	34	31	34	31	28	25
7	60	48	40	35	56	45	38	33	40	35	30	36	31	27	31	28	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18703	18703	18703
5°	18872	18727	18629
10°	18812	18681	18582
15°	18729	18612	18512
20°	18635	18515	18378
25°	18504	18379	18166
30°	18304	18174	17914
35°	18033	17877	17621
40°	17623	17434	17118
45°	16905	16609	16267
50°	15639	15263	14962
55°	13650	13341	13060
60°	11501	11405	11180
65°	9948	9988	9911
70°	9137	9185	9185
75°	8776	8776	8837
80°	8257	8347	8257
85°	6659	7389	7389



TEST NUMBER: P561923

CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.7	2.3
10°-20°	548.5	6.5
20°-30°	827.3	9.9
30°-40°	985.7	11.7
40°-50°	971.8	11.6
50°-60°	742.7	8.8
60°-70°	459.6	5.5
70°-80°	261.1	3.1
80°-90°	79.4	0.9
90°-100°	244.1	2.9
100°-110°	694.5	8.3
110°-120°	665.4	7.9
120°-130°	526.6	6.3
130°-140°	422.7	5.0
140°-150°	330.9	3.9
150°-160°	242.1	2.9
160°-170°	150.0	1.8
170°-180°	50.9	0.6
0°-30°	1567.5	18.7
0°-40°	2553.2	30.4
0°-60°	4267.7	50.8
0°-90°	5067.8	60.4
90°-120°	1603.9	19.1
90°-150°	2884.1	34.4
90°-180°	3327.0	39.6
0°-180°	8394.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2027	2027	2027	2027	2027	
5°	2038	2016	2022	2015	2012	193
15°	1961	1940	1949	1942	1938	553
25°	1818	1796	1805	1786	1784	836
35°	1601	1582	1587	1566	1564	999
45°	1296	1278	1273	1250	1247	993
55°	849	835	829	815	812	760
65°	456	452	458	454	454	462
75°	246	246	246	248	248	260
85°	63	66	70	70	70	73
90°	0	0	0	0	0	4
95°	26	105	472	164	101	30
105°	108	164	708	1250	1188	114
115°	201	242	537	1137	1335	198
125°	283	314	512	850	1016	253
135°	346	375	506	718	812	267
145°	408	429	510	621	677	255
155°	466	477	522	562	584	216
165°	515	517	528	540	548	145
175°	540	537	535	532	528	51
180°	536	536	536	536	536	



TEST NUMBER: P561923

CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2027.2	2027.2	2027.2	2027.2	2027.2
2.5°	2039.8	2022.0	2027.2	2022.8	2013.2
5°	2037.7	2015.5	2022.0	2014.9	2011.5
7.5°	2022.0	2000.1	2006.6	1999.6	1997.5
10°	2008.0	1987.5	1994.0	1987.0	1983.5
12.5°	1992.6	1970.8	1978.7	1970.2	1966.8
15°	1960.8	1940.4	1948.6	1941.6	1938.1
17.5°	1925.9	1904.1	1912.3	1904.2	1899.7
20°	1898.0	1877.5	1885.8	1873.5	1871.8
22.5°	1867.3	1846.8	1855.0	1838.6	1838.3
25°	1817.7	1795.5	1805.4	1786.2	1784.5
27.5°	1758.6	1738.2	1746.4	1726.8	1724.8
30°	1718.1	1697.6	1705.9	1684.9	1681.5
32.5°	1672.0	1652.9	1659.8	1638.8	1636.8
35°	1601.1	1582.4	1587.2	1566.2	1564.5
37.5°	1520.5	1503.4	1506.2	1483.1	1481.4
40°	1463.2	1446.1	1447.5	1423.0	1421.3
42.5°	1400.4	1383.3	1381.8	1357.4	1355.7
45°	1295.6	1278.5	1272.9	1250.1	1246.7
47.5°	1176.2	1159.1	1148.6	1130.0	1127.6
50°	1089.6	1072.5	1063.4	1047.5	1042.4
52.5°	996.0	978.9	971.2	956.7	951.6
55°	848.6	834.9	829.4	815.3	811.9
57.5°	708.6	699.3	697.7	684.1	682.7
60°	623.3	618.2	618.1	605.9	605.9
62.5°	550.7	547.0	549.7	541.6	540.2
65°	455.7	452.3	457.5	454.0	454.0
67.5°	380.6	380.6	383.8	382.4	382.4
70°	338.7	338.7	340.5	340.5	340.5
72.5°	301.0	299.7	304.2	304.1	302.8
75°	246.2	246.2	246.2	247.9	247.9
77.5°	191.7	192.1	193.5	193.1	191.7
80°	155.4	157.1	157.1	155.4	155.4
82.5°	119.1	120.8	120.8	120.4	119.1
85°	62.9	66.3	69.8	69.8	69.8
87.5°	18.2	23.6	27.9	27.9	26.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.1	43.2	100.2	29.2	22.0
95°	26.5	105.1	472.5	163.5	100.8
97.5°	48.7	123.2	727.7	520.7	356.8
100°	64.2	133.8	783.1	793.2	611.0
102.5°	81.3	145.4	770.8	1015.3	856.2
105°	107.9	163.7	707.7	1250.1	1188.4
107.5°	135.0	185.0	634.0	1316.3	1371.2
110°	153.8	200.6	591.6	1290.9	1414.4

TEST NUMBER: P561923

CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	171.7	216.1	563.1	1231.0	1407.1
115°	200.6	242.4	536.6	1136.8	1335.0
117.5°	226.1	265.3	521.0	1033.9	1243.7
120°	246.4	279.3	519.3	975.0	1176.1
122.5°	262.7	295.6	515.3	923.4	1110.1
125°	283.1	314.0	512.2	850.0	1016.3
127.5°	305.3	334.2	510.6	806.1	943.1
130°	316.7	345.6	508.1	775.6	895.1
132.5°	328.9	357.0	508.1	751.8	861.7
135°	346.2	375.1	506.1	718.0	811.6
137.5°	362.5	390.6	505.9	689.4	770.2
140°	374.7	403.6	505.1	665.7	743.4
142.5°	388.6	412.7	507.5	646.8	716.5
145°	408.3	429.2	510.2	621.4	677.2
147.5°	425.2	445.6	514.6	595.8	644.0
150°	439.9	453.8	516.3	587.3	621.2
152.5°	451.3	466.0	517.9	575.8	607.3
155°	466.4	477.3	522.4	561.6	584.5
157.5°	485.1	491.7	523.4	555.1	571.5
160°	494.9	499.9	527.5	550.2	564.1
162.5°	500.6	506.4	528.3	546.1	556.8
165°	515.3	517.2	528.5	539.9	547.8
167.5°	525.2	523.4	533.2	538.3	541.5
170°	528.5	527.5	531.5	532.7	536.6
172.5°	535.8	532.4	534.0	531.0	534.2
175°	539.7	536.7	534.6	531.5	527.5
177.5°	541.3	536.5	534.0	530.8	531.5
180°	535.6	535.6	535.6	535.6	535.6

(END OF REPORT)