

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523919

Luminaire Tested: **SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523919
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10252.2 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 97.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523919

CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523919

CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	75	70	66	63	60	56	53	50	47	42	41	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	45	40	45	39	35	37	33	30	30	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19	
7	58	46	38	32	53	43	36	31	36	31	27	31	26	23	25	22	20				17	
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17624	17624	17624
5°	17753	17645	17583
10°	17723	17598	17519
15°	17606	17510	17414
20°	17489	17390	17259
25°	17282	17161	16991
30°	16961	16872	16658
35°	16517	16405	16197
40°	15990	15888	15707
45°	15553	15443	15291
50°	14995	14899	14754
55°	14218	14030	13922
60°	12944	12573	12511
65°	11402	10929	10892
70°	9846	9439	9439
75°	8473	8356	8235
80°	7470	7561	7385
85°	5843	6383	6383



TEST NUMBER: P523919

CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.6	1.8
10°-20°	515.7	5.0
20°-30°	772.5	7.5
30°-40°	906.1	8.8
40°-50°	909.0	8.9
50°-60°	775.4	7.6
60°-70°	505.7	4.9
70°-80°	253.7	2.5
80°-90°	70.2	0.7
90°-100°	393.4	3.8
100°-110°	1119.5	10.9
110°-120°	1072.5	10.5
120°-130°	848.9	8.3
130°-140°	681.4	6.6
140°-150°	533.4	5.2
150°-160°	390.3	3.8
160°-170°	241.8	2.4
170°-180°	82.0	0.8
0°-30°	1468.9	14.3
0°-40°	2375.0	23.2
0°-60°	4059.4	39.6
0°-90°	4889.0	47.7
90°-120°	2585.4	25.2
90°-150°	4649.1	45.3
90°-180°	5363.0	52.3
0°-180°	10252.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1910	1910	1910	1910	1910	
5°	1917	1899	1905	1898	1898	182
15°	1843	1825	1833	1826	1823	520
25°	1698	1678	1686	1671	1669	781
35°	1466	1452	1456	1440	1438	916
45°	1192	1184	1184	1172	1172	918
55°	884	881	872	867	866	786
65°	522	512	501	497	499	521
75°	238	238	234	233	231	258
85°	55	60	60	60	60	65
90°	0	0	0	0	0	4
95°	43	170	762	264	162	49
105°	174	264	1141	2015	1916	184
115°	323	391	865	1832	2152	318
125°	456	506	826	1370	1638	408
135°	558	605	816	1157	1308	431
145°	658	692	822	1002	1092	411
155°	752	769	842	905	942	348
165°	831	834	852	870	883	234
175°	870	865	862	857	850	82
180°	863	863	863	863	863	



TEST NUMBER: P523919

CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1910.2	1910.2	1910.2	1910.2	1910.2
2.5°	1922.2	1906.5	1910.2	1907.3	1899.5
5°	1916.9	1898.9	1905.2	1898.5	1898.5
7.5°	1903.8	1884.2	1890.4	1883.7	1883.4
10°	1891.8	1872.1	1878.4	1871.6	1870.0
12.5°	1874.4	1854.7	1862.3	1854.3	1853.9
15°	1843.2	1825.2	1833.2	1826.4	1823.1
17.5°	1808.1	1788.4	1798.0	1788.6	1787.3
20°	1781.3	1761.6	1771.2	1757.8	1757.8
22.5°	1749.1	1729.5	1740.4	1723.0	1723.0
25°	1697.6	1677.9	1685.8	1670.7	1669.1
27.5°	1636.3	1617.0	1625.2	1608.2	1607.8
30°	1592.1	1574.1	1583.7	1565.3	1563.6
32.5°	1543.9	1527.2	1534.2	1515.7	1514.1
35°	1466.5	1451.8	1456.5	1439.7	1438.1
37.5°	1385.2	1370.1	1375.5	1361.1	1360.4
40°	1327.6	1317.8	1319.2	1307.4	1304.1
42.5°	1274.0	1262.9	1264.3	1252.6	1251.9
45°	1192.0	1183.8	1183.6	1171.9	1171.9
47.5°	1104.9	1098.7	1096.9	1087.2	1086.8
50°	1044.7	1039.7	1038.0	1029.6	1027.9
52.5°	981.7	979.4	973.7	966.6	966.3
55°	883.9	880.7	872.2	867.2	865.5
57.5°	777.8	771.3	761.7	754.4	755.7
60°	701.5	694.9	681.4	678.0	678.0
62.5°	627.8	619.9	606.4	601.7	604.4
65°	522.3	512.5	500.6	497.3	498.9
67.5°	426.6	417.7	404.8	404.8	403.5
70°	365.0	360.0	349.9	349.9	349.9
72.5°	310.0	307.8	300.3	300.3	299.0
75°	237.7	237.7	234.4	232.7	231.0
77.5°	178.1	178.8	177.1	175.4	172.4
80°	140.6	143.9	142.3	140.6	139.0
82.5°	105.8	109.1	108.8	105.8	105.5
85°	55.2	60.2	60.3	60.3	60.3
87.5°	14.7	20.0	21.4	21.5	22.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.1	69.6	161.5	47.0	35.5
95°	42.7	169.5	761.6	263.6	162.5
97.5°	78.5	198.5	1173.0	839.3	575.2
100°	103.4	215.8	1262.3	1278.6	984.9
102.5°	131.0	234.3	1242.6	1636.6	1380.1
105°	174.0	263.9	1140.8	2015.1	1915.6
107.5°	217.7	298.2	1022.0	2121.8	2210.4
110°	247.9	323.3	953.7	2080.9	2279.9

TEST NUMBER: P523919

CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	276.7	348.3	907.7	1984.4	2268.1
115°	323.4	390.8	865.0	1832.5	2151.9
117.5°	364.4	427.6	839.8	1666.5	2004.8
120°	397.2	450.2	837.1	1571.7	1895.9
122.5°	423.5	476.5	830.6	1488.4	1789.5
125°	456.3	506.1	825.6	1370.1	1638.1
127.5°	492.1	538.6	823.0	1299.5	1520.3
130°	510.5	557.0	819.1	1250.2	1442.8
132.5°	530.2	575.4	819.1	1211.8	1389.0
135°	558.1	604.6	815.8	1157.4	1308.2
137.5°	584.3	629.6	815.5	1111.3	1241.6
140°	604.0	650.6	814.2	1073.1	1198.2
142.5°	626.4	665.2	818.1	1042.6	1154.9
145°	658.2	691.9	822.4	1001.7	1091.6
147.5°	685.5	718.2	829.6	960.4	1038.0
150°	709.1	731.6	832.2	946.7	1001.3
152.5°	727.5	751.2	834.8	928.2	978.9
155°	751.8	769.4	842.1	905.3	942.2
157.5°	782.0	792.6	843.7	894.9	921.2
160°	797.7	805.8	850.3	886.9	909.4
162.5°	806.9	816.2	851.6	880.2	897.5
165°	830.6	833.8	851.9	870.3	883.1
167.5°	846.7	843.8	859.5	867.8	872.9
170°	851.9	850.3	856.8	858.6	865.0
172.5°	863.7	858.3	860.8	856.0	861.1
175°	870.0	865.1	861.8	856.7	850.3
177.5°	872.6	864.9	860.8	855.5	856.8
180°	863.4	863.4	863.4	863.4	863.4

(END OF REPORT)