

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523921

Luminaire Tested: **SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523921
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10690.2 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 97.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523921
CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523921

CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	75	70	66	63	60	56	53	50	47	42	41	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	45	40	45	39	35	37	33	30	30	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19	
7	58	46	38	32	53	43	36	31	36	31	27	31	26	23	25	22	20				17	
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18377	18377	18377
5°	18512	18399	18334
10°	18480	18349	18268
15°	18358	18258	18158
20°	18237	18133	17996
25°	18020	17895	17717
30°	17686	17593	17371
35°	17224	17105	16889
40°	16672	16568	16379
45°	16217	16104	15944
50°	15635	15535	15384
55°	14826	14630	14517
60°	13496	13110	13046
65°	11889	11396	11357
70°	10267	9841	9841
75°	8837	8712	8587
80°	7789	7885	7699
85°	6097	6648	6648



TEST NUMBER: P523921

CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.3	1.8
10°-20°	537.8	5.0
20°-30°	805.5	7.5
30°-40°	944.8	8.8
40°-50°	947.8	8.9
50°-60°	808.5	7.6
60°-70°	527.3	4.9
70°-80°	264.5	2.5
80°-90°	73.2	0.7
90°-100°	410.2	3.8
100°-110°	1167.3	10.9
110°-120°	1118.4	10.5
120°-130°	885.2	8.3
130°-140°	710.5	6.6
140°-150°	556.2	5.2
150°-160°	407.0	3.8
160°-170°	252.1	2.4
170°-180°	85.5	0.8
0°-30°	1531.7	14.3
0°-40°	2476.5	23.2
0°-60°	4232.8	39.6
0°-90°	5097.9	47.7
90°-120°	2695.9	25.2
90°-150°	4847.7	45.3
90°-180°	5592.0	52.3
0°-180°	10690.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1992	1992	1992	1992	1992	
5°	1999	1980	1987	1980	1980	190
15°	1922	1903	1912	1904	1901	542
25°	1770	1750	1758	1742	1740	814
35°	1529	1514	1519	1501	1500	955
45°	1243	1234	1234	1222	1222	957
55°	922	918	910	904	902	819
65°	545	534	522	518	520	544
75°	248	248	244	243	241	269
85°	58	63	63	63	63	68
90°	0	0	0	0	0	4
95°	44	177	794	275	169	51
105°	181	275	1190	2101	1997	192
115°	337	408	902	1911	2244	332
125°	476	528	861	1429	1708	426
135°	582	630	851	1207	1364	449
145°	686	722	858	1044	1138	429
155°	784	802	878	944	982	362
165°	866	869	888	907	921	244
175°	907	902	899	893	887	86
180°	900	900	900	900	900	

TEST NUMBER: P523921

CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1991.8	1991.8	1991.8	1991.8	1991.8
2.5°	2004.4	1988.0	1991.8	1988.8	1980.6
5°	1998.8	1980.0	1986.6	1979.6	1979.6
7.5°	1985.2	1964.7	1971.2	1964.2	1963.9
10°	1972.6	1952.1	1958.6	1951.6	1949.9
12.5°	1954.4	1934.0	1941.9	1933.5	1933.1
15°	1922.0	1903.2	1911.5	1904.4	1901.0
17.5°	1885.3	1864.8	1874.8	1865.0	1863.7
20°	1857.4	1836.9	1846.9	1832.9	1832.9
22.5°	1823.9	1803.4	1814.8	1796.6	1796.6
25°	1770.1	1749.6	1757.9	1742.1	1740.4
27.5°	1706.2	1686.1	1694.7	1676.9	1676.5
30°	1660.1	1641.4	1651.4	1632.2	1630.5
32.5°	1609.9	1592.4	1599.7	1580.5	1578.8
35°	1529.2	1513.8	1518.7	1501.2	1499.5
37.5°	1444.4	1428.7	1434.2	1419.2	1418.5
40°	1384.3	1374.1	1375.6	1363.3	1359.9
42.5°	1328.5	1316.8	1318.3	1306.1	1305.4
45°	1242.9	1234.4	1234.2	1222.0	1222.0
47.5°	1152.1	1145.7	1143.8	1133.6	1133.3
50°	1089.3	1084.2	1082.3	1073.5	1071.8
52.5°	1023.7	1021.3	1015.3	1007.9	1007.6
55°	921.7	918.3	909.5	904.2	902.5
57.5°	811.0	804.2	794.3	786.6	788.0
60°	731.4	724.6	710.5	707.0	707.0
62.5°	654.6	646.4	632.3	627.5	630.2
65°	544.6	534.4	522.0	518.5	520.2
67.5°	444.8	435.6	422.1	422.1	420.7
70°	380.6	375.4	364.8	364.8	364.8
72.5°	323.3	320.9	313.2	313.1	311.8
75°	247.9	247.9	244.4	242.6	240.9
77.5°	185.7	186.4	184.7	182.9	179.8
80°	146.6	150.0	148.4	146.6	144.9
82.5°	110.3	113.7	113.5	110.3	110.0
85°	57.6	62.7	62.8	62.8	62.8
87.5°	15.4	20.8	22.3	22.4	23.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.7	72.6	168.4	49.0	37.0
95°	44.5	176.7	794.2	274.9	169.4
97.5°	81.8	207.0	1223.1	875.2	599.7
100°	107.8	225.0	1316.2	1333.2	1026.9
102.5°	136.6	244.4	1295.7	1706.5	1439.1
105°	181.4	275.1	1189.5	2101.2	1997.4
107.5°	227.0	311.0	1065.6	2212.4	2304.8
110°	258.4	337.1	994.4	2169.9	2377.4

TEST NUMBER: P523921

CATALOG NUMBER: SQ4-PP3-125U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.6	363.2	946.5	2069.2	2365.0
115°	337.2	407.5	902.0	1910.8	2243.9
117.5°	380.0	445.9	875.6	1737.7	2090.5
120°	414.2	469.4	872.9	1638.8	1976.9
122.5°	441.6	496.8	866.1	1552.0	1866.0
125°	475.8	527.7	860.9	1428.7	1708.1
127.5°	513.1	561.7	858.2	1355.0	1585.3
130°	532.3	580.8	854.1	1303.6	1504.5
132.5°	552.8	600.0	854.1	1263.6	1448.3
135°	581.9	630.5	850.7	1206.8	1364.1
137.5°	609.3	656.5	850.3	1158.7	1294.6
140°	629.9	678.4	848.9	1118.9	1249.4
142.5°	653.1	693.6	853.0	1087.1	1204.3
145°	686.3	721.5	857.5	1044.5	1138.2
147.5°	714.8	748.9	865.0	1001.4	1082.4
150°	739.4	762.8	867.8	987.2	1044.1
152.5°	758.6	783.3	870.5	967.9	1020.8
155°	783.9	802.3	878.0	943.9	982.4
157.5°	815.4	826.4	879.7	933.1	960.5
160°	831.8	840.2	886.6	924.8	948.2
162.5°	841.4	851.1	888.0	917.8	935.9
165°	866.1	869.4	888.3	907.4	920.8
167.5°	882.8	879.8	896.2	904.9	910.2
170°	888.3	886.6	893.4	895.3	902.0
172.5°	900.6	894.9	897.5	892.5	897.9
175°	907.1	902.1	898.6	893.3	886.6
177.5°	909.9	901.8	897.5	892.1	893.4
180°	900.3	900.3	900.3	900.3	900.3

(END OF REPORT)