

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561790

Luminaire Tested: **SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561790
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4713.8 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561790
CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561790

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56	52
2	92	84	78	73	86	79	74	69	70	65	62	61	58	55	52	50	48	44
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	34	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	27	31	28	25	22
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10558	10558	10558
5°	10653	10571	10516
10°	10619	10546	10490
15°	10573	10507	10450
20°	10519	10452	10375
25°	10446	10375	10255
30°	10333	10259	10112
35°	10181	10092	9948
40°	9948	9841	9664
45°	9543	9376	9183
50°	8829	8616	8447
55°	7705	7531	7372
60°	6493	6438	6311
65°	5617	5639	5595
70°	5158	5185	5185
75°	4955	4955	4991
80°	4660	4713	4660
85°	3758	4171	4171



TEST NUMBER: P561790

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.2	2.3
10°-20°	309.6	6.6
20°-30°	467.0	9.9
30°-40°	556.4	11.8
40°-50°	548.6	11.6
50°-60°	419.3	8.9
60°-70°	259.5	5.5
70°-80°	147.4	3.1
80°-90°	44.8	1.0
90°-100°	135.9	2.9
100°-110°	386.8	8.2
110°-120°	370.6	7.9
120°-130°	293.3	6.2
130°-140°	235.4	5.0
140°-150°	184.3	3.9
150°-160°	134.8	2.9
160°-170°	83.5	1.8
170°-180°	28.3	0.6
0°-30°	884.9	18.8
0°-40°	1441.3	30.6
0°-60°	2409.2	51.1
0°-90°	2860.8	60.7
90°-120°	893.2	18.9
90°-150°	1606.2	34.1
90°-180°	1853.0	39.3
0°-180°	4713.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1144	1144	1144	1144	1144	
5°	1150	1138	1141	1137	1136	109
15°	1107	1095	1100	1096	1094	312
25°	1026	1014	1019	1008	1007	472
35°	904	893	896	884	883	564
45°	731	722	719	706	704	560
55°	479	471	468	460	458	429
65°	257	255	258	256	256	261
75°	139	139	139	140	140	147
85°	36	37	39	39	39	41
90°	0	0	0	0	0	2
95°	15	59	263	91	56	17
105°	60	91	394	696	662	64
115°	112	135	299	633	744	110
125°	158	175	285	473	566	141
135°	193	209	282	400	452	149
145°	227	239	284	346	377	142
155°	260	266	291	313	326	120
165°	287	288	294	301	305	81
175°	301	299	298	296	294	28
180°	298	298	298	298	298	



TEST NUMBER: P561790

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1144.4	1144.4	1144.4	1144.4	1144.4
2.5°	1151.5	1141.5	1144.4	1141.9	1136.5
5°	1150.3	1137.8	1141.4	1137.4	1135.5
7.5°	1141.4	1129.1	1132.8	1128.8	1127.6
10°	1133.5	1122.0	1125.7	1121.7	1119.7
12.5°	1124.9	1112.5	1117.0	1112.2	1110.3
15°	1106.9	1095.4	1100.0	1096.0	1094.1
17.5°	1087.2	1074.9	1079.5	1074.9	1072.4
20°	1071.4	1059.9	1064.5	1057.6	1056.7
22.5°	1054.1	1042.5	1047.2	1037.9	1037.7
25°	1026.1	1013.6	1019.2	1008.3	1007.4
27.5°	992.8	981.2	985.9	974.8	973.7
30°	969.9	958.4	963.0	951.1	949.2
32.5°	943.9	933.1	937.0	925.1	924.0
35°	903.9	893.3	896.0	884.1	883.2
37.5°	858.3	848.7	850.3	837.2	836.3
40°	826.0	816.4	817.1	803.3	802.4
42.5°	790.5	780.9	780.1	766.3	765.3
45°	731.4	721.7	718.6	705.7	703.8
47.5°	664.0	654.3	648.4	637.9	636.6
50°	615.1	605.4	600.3	591.3	588.5
52.5°	562.2	552.6	548.2	540.1	537.2
55°	479.0	471.3	468.2	460.3	458.3
57.5°	400.0	394.8	393.9	386.2	385.4
60°	351.9	349.0	348.9	342.0	342.0
62.5°	310.9	308.8	310.3	305.7	305.0
65°	257.3	255.3	258.3	256.3	256.3
67.5°	214.9	214.9	216.7	215.9	215.9
70°	191.2	191.2	192.2	192.2	192.2
72.5°	169.9	169.2	171.7	171.7	170.9
75°	139.0	139.0	139.0	140.0	140.0
77.5°	108.2	108.4	109.2	109.0	108.2
80°	87.7	88.7	88.7	87.7	87.7
82.5°	67.2	68.2	68.2	68.0	67.2
85°	35.5	37.4	39.4	39.4	39.4
87.5°	10.3	13.3	15.8	15.8	15.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.5	24.1	55.8	16.2	12.2
95°	14.7	58.6	263.1	91.1	56.1
97.5°	27.1	68.6	405.3	290.0	198.7
100°	35.7	74.5	436.1	441.7	340.3
102.5°	45.3	81.0	429.3	565.4	476.8
105°	60.1	91.2	394.1	696.2	661.8
107.5°	75.2	103.0	353.1	733.1	763.7
110°	85.6	111.7	329.5	719.0	787.7

TEST NUMBER: P561790

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	95.6	120.3	313.6	685.6	783.6
115°	111.7	135.0	298.9	633.1	743.5
117.5°	125.9	147.7	290.1	575.8	692.7
120°	137.2	155.5	289.2	543.0	655.0
122.5°	146.3	164.6	287.0	514.2	618.3
125°	157.7	174.8	285.3	473.4	566.0
127.5°	170.0	186.1	284.3	449.0	525.3
130°	176.4	192.5	283.0	431.9	498.5
132.5°	183.2	198.8	283.0	418.7	479.9
135°	192.8	208.9	281.9	399.9	452.0
137.5°	201.9	217.5	281.7	383.9	429.0
140°	208.7	224.8	281.3	370.7	414.0
142.5°	216.4	229.8	282.6	360.2	399.0
145°	227.4	239.1	284.1	346.1	377.1
147.5°	236.8	248.1	286.6	331.8	358.6
150°	245.0	252.8	287.5	327.1	345.9
152.5°	251.3	259.6	288.4	320.7	338.2
155°	259.7	265.8	290.9	312.8	325.5
157.5°	270.2	273.8	291.5	309.2	318.3
160°	275.6	278.4	293.8	306.4	314.2
162.5°	278.8	282.0	294.2	304.1	310.1
165°	287.0	288.1	294.3	300.7	305.1
167.5°	292.5	291.5	296.9	299.8	301.6
170°	294.3	293.8	296.0	296.6	298.9
172.5°	298.4	296.5	297.4	295.7	297.5
175°	300.6	298.9	297.7	296.0	293.8
177.5°	301.5	298.8	297.4	295.6	296.0
180°	298.3	298.3	298.3	298.3	298.3

(END OF REPORT)