

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561792

Luminaire Tested: **SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561792
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4927.0 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561792
CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561792

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61		
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56	52		
2	92	84	78	73	86	79	74	69	70	65	62	61	58	55	52	50	48	44		
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	41	38		
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33		
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	28		
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	34	31	28	25		
7	61	48	40	35	57	46	38	33	41	35	30	36	31	27	31	28	25	22		
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20		
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18		
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11035	11035	11035
5°	11135	11049	10992
10°	11100	11023	10965
15°	11051	10983	10923
20°	10996	10925	10843
25°	10918	10845	10719
30°	10801	10724	10569
35°	10640	10548	10397
40°	10399	10287	10100
45°	9975	9800	9598
50°	9228	9005	8829
55°	8054	7872	7707
60°	6787	6730	6597
65°	5870	5892	5849
70°	5392	5419	5419
75°	5180	5180	5215
80°	4872	4925	4872
85°	3927	4361	4361



TEST NUMBER: P561792

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	2.3
10°-20°	323.6	6.6
20°-30°	488.1	9.9
30°-40°	581.6	11.8
40°-50°	573.4	11.6
50°-60°	438.2	8.9
60°-70°	271.2	5.5
70°-80°	154.0	3.1
80°-90°	46.9	1.0
90°-100°	142.1	2.9
100°-110°	404.2	8.2
110°-120°	387.3	7.9
120°-130°	306.6	6.2
130°-140°	246.0	5.0
140°-150°	192.6	3.9
150°-160°	140.9	2.9
160°-170°	87.3	1.8
170°-180°	29.6	0.6
0°-30°	924.9	18.8
0°-40°	1506.5	30.6
0°-60°	2518.1	51.1
0°-90°	2990.2	60.7
90°-120°	933.6	18.9
90°-150°	1678.9	34.1
90°-180°	1937.0	39.3
0°-180°	4927.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1202	1189	1193	1189	1187	114
15°	1157	1145	1150	1146	1144	326
25°	1072	1059	1065	1054	1053	494
35°	945	934	936	924	923	590
45°	764	754	751	738	736	586
55°	501	493	489	481	479	449
65°	269	267	270	268	268	272
75°	145	145	145	146	146	153
85°	37	39	41	41	41	43
90°	0	0	0	0	0	2
95°	15	61	275	95	59	18
105°	63	95	412	728	692	66
115°	117	141	312	662	777	115
125°	165	183	298	495	592	147
135°	202	218	295	418	472	156
145°	238	250	297	362	394	148
155°	272	278	304	327	340	126
165°	300	301	308	314	319	84
175°	314	312	311	309	307	30
180°	312	312	312	312	312	

TEST NUMBER: P561792

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1203.6	1193.1	1196.1	1193.5	1187.9
5°	1202.3	1189.2	1193.0	1188.9	1186.9
7.5°	1193.0	1180.1	1184.0	1179.8	1178.6
10°	1184.8	1172.7	1176.6	1172.4	1170.4
12.5°	1175.7	1162.8	1167.5	1162.5	1160.5
15°	1157.0	1144.9	1149.8	1145.6	1143.6
17.5°	1136.4	1123.5	1128.3	1123.5	1120.9
20°	1119.9	1107.8	1112.7	1105.4	1104.4
22.5°	1101.8	1089.7	1094.5	1084.9	1084.7
25°	1072.5	1059.4	1065.3	1053.9	1052.9
27.5°	1037.7	1025.6	1030.5	1018.9	1017.7
30°	1013.8	1001.7	1006.6	994.2	992.1
32.5°	986.6	975.3	979.4	967.0	965.8
35°	944.7	933.7	936.5	924.1	923.1
37.5°	897.2	887.1	888.7	875.1	874.1
40°	863.4	853.3	854.1	839.6	838.6
42.5°	826.3	816.2	815.3	800.9	799.9
45°	764.5	754.4	751.1	737.6	735.6
47.5°	694.0	683.9	677.7	666.8	665.3
50°	642.9	632.8	627.4	618.1	615.1
52.5°	587.7	577.6	573.0	564.5	561.5
55°	500.7	492.6	489.4	481.1	479.1
57.5°	418.1	412.6	411.7	403.6	402.8
60°	367.8	364.8	364.7	357.5	357.5
62.5°	324.9	322.7	324.3	319.6	318.8
65°	268.9	266.9	269.9	267.9	267.9
67.5°	224.6	224.6	226.5	225.6	225.6
70°	199.9	199.9	200.9	200.9	200.9
72.5°	177.6	176.8	179.5	179.5	178.6
75°	145.3	145.3	145.3	146.3	146.3
77.5°	113.1	113.3	114.2	113.9	113.1
80°	91.7	92.7	92.7	91.7	91.7
82.5°	70.3	71.3	71.3	71.1	70.3
85°	37.1	39.1	41.2	41.2	41.2
87.5°	10.7	13.9	16.5	16.5	15.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	25.1	58.3	17.0	12.8
95°	15.4	61.2	275.0	95.2	58.7
97.5°	28.3	71.7	423.6	303.1	207.7
100°	37.3	77.9	455.8	461.7	355.7
102.5°	47.3	84.6	448.7	591.0	498.4
105°	62.8	95.3	412.0	727.7	691.7
107.5°	78.6	107.7	369.0	766.2	798.2
110°	89.5	116.7	344.4	751.5	823.3

TEST NUMBER: P561792

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	99.9	125.8	327.8	716.6	819.1
115°	116.8	141.1	312.4	661.8	777.1
117.5°	131.6	154.4	303.3	601.8	724.0
120°	143.4	162.6	302.3	567.6	684.6
122.5°	152.9	172.1	299.9	537.5	646.2
125°	164.8	182.8	298.2	494.8	591.6
127.5°	177.7	194.5	297.2	469.3	549.0
130°	184.3	201.2	295.8	451.5	521.0
132.5°	191.5	207.8	295.8	437.6	501.6
135°	201.5	218.3	294.6	417.9	472.4
137.5°	211.0	227.4	294.5	401.3	448.4
140°	218.1	234.9	294.0	387.5	432.7
142.5°	226.2	240.2	295.4	376.5	417.1
145°	237.7	249.9	297.0	361.7	394.2
147.5°	247.5	259.4	299.6	346.8	374.9
150°	256.1	264.2	300.5	341.9	361.6
152.5°	262.7	271.3	301.5	335.2	353.5
155°	271.5	277.9	304.1	326.9	340.2
157.5°	282.4	286.2	304.7	323.1	332.7
160°	288.1	291.0	307.0	320.3	328.4
162.5°	291.4	294.8	307.5	317.9	324.1
165°	299.9	301.1	307.6	314.3	318.9
167.5°	305.7	304.7	310.4	313.4	315.2
170°	307.6	307.1	309.4	310.1	312.4
172.5°	311.9	309.9	310.8	309.1	311.0
175°	314.2	312.4	311.2	309.4	307.0
177.5°	315.1	312.3	310.8	309.0	309.4
180°	311.8	311.8	311.8	311.8	311.8

(END OF REPORT)