

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561964

Luminaire Tested: **SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561964  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (5000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4112.3 lumens  
Efficiency: N/A  
Efficacy: 97.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 42.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561964

CATALOG NUMBER: SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (5000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561964

CATALOG NUMBER: SQ4-PR1-OU-100D-92765-1D-UNV-STD-W-4 (5000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85				
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72				
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62				
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54				
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47				
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41				
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37				
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33				
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30				
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15177	15177	15177
5°	15314	15195	15117
10°	15265	15159	15080
15°	15199	15103	15022
20°	15121	15024	14913
25°	15015	14915	14742
30°	14853	14748	14537
35°	14634	14506	14299
40°	14300	14147	13890
45°	13717	13477	13200
50°	12690	12386	12142
55°	11076	10825	10597
60°	9333	9256	9073
65°	8073	8104	8043
70°	7416	7453	7453
75°	7122	7122	7172
80°	6700	6774	6700
85°	5399	6002	6002



TEST NUMBER: P561964

CATALOG NUMBER: SQ4-PR1-OU-100D-92765-1D-UNV-STD-W-4 (5000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.6	3.8
10°-20°	445.1	10.8
20°-30°	671.3	16.3
30°-40°	799.9	19.5
40°-50°	788.6	19.2
50°-60°	602.7	14.7
60°-70°	373.0	9.1
70°-80°	211.9	5.2
80°-90°	64.4	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1271.9	30.9
0°-40°	2071.8	50.4
0°-60°	3463.1	84.2
0°-90°	4112.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4112.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1645	1645	1645	1645	1645	
5°	1654	1636	1641	1635	1632	157
15°	1591	1574	1581	1576	1573	449
25°	1475	1457	1465	1449	1448	679
35°	1299	1284	1288	1271	1270	811
45°	1051	1038	1033	1014	1012	805
55°	689	678	673	662	659	617
65°	370	367	371	368	368	375
75°	200	200	200	201	201	211
85°	51	54	57	57	57	61
90°	0	0	0	0	0	



TEST NUMBER: P561964

CATALOG NUMBER: SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1645.0	1645.0	1645.0	1645.0	1645.0
2.5°	1655.2	1640.8	1645.0	1641.4	1633.7
5°	1653.5	1635.5	1640.7	1635.0	1632.2
7.5°	1640.7	1623.0	1628.3	1622.6	1620.9
10°	1629.4	1612.8	1618.1	1612.3	1609.6
12.5°	1616.9	1599.2	1605.6	1598.7	1596.0
15°	1591.2	1574.5	1581.2	1575.5	1572.7
17.5°	1562.8	1545.1	1551.8	1545.2	1541.6
20°	1540.1	1523.5	1530.2	1520.3	1518.9
22.5°	1515.2	1498.6	1505.3	1492.0	1491.7
25°	1475.0	1457.0	1465.1	1449.4	1448.1
27.5°	1427.1	1410.5	1417.2	1401.3	1399.6
30°	1394.2	1377.6	1384.3	1367.2	1364.5
32.5°	1356.8	1341.3	1346.9	1329.8	1328.2
35°	1299.3	1284.0	1287.9	1270.9	1269.5
37.5°	1233.8	1220.0	1222.2	1203.5	1202.1
40°	1187.3	1173.5	1174.6	1154.7	1153.3
42.5°	1136.3	1122.5	1121.3	1101.5	1100.1
45°	1051.3	1037.5	1032.9	1014.4	1011.7
47.5°	954.4	940.6	932.0	917.0	915.0
50°	884.1	870.3	862.9	850.0	845.9
52.5°	808.2	794.3	788.1	776.4	772.2
55°	688.6	677.5	673.0	661.6	658.8
57.5°	575.0	567.5	566.2	555.1	554.0
60°	505.8	501.7	501.6	491.7	491.7
62.5°	446.9	443.8	446.0	439.5	438.4
65°	369.8	367.0	371.2	368.4	368.4
67.5°	308.9	308.9	311.4	310.3	310.3
70°	274.9	274.9	276.3	276.3	276.3
72.5°	244.3	243.2	246.8	246.8	245.7
75°	199.8	199.8	199.8	201.2	201.2
77.5°	155.6	155.9	157.0	156.7	155.6
80°	126.1	127.5	127.5	126.1	126.1
82.5°	96.6	98.0	98.0	97.7	96.6
85°	51.0	53.8	56.7	56.7	56.7
87.5°	14.7	19.2	22.7	22.6	21.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)