

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561797

Luminaire Tested: **SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561797
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5277.4 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 45.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561797

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561797

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56	52
2	92	84	78	73	86	79	74	69	70	65	62	61	58	55	52	50	48	44
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	34	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	27	31	28	25	22
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11821	11821	11821
5°	11927	11835	11774
10°	11890	11806	11744
15°	11837	11764	11700
20°	11778	11701	11615
25°	11695	11616	11481
30°	11569	11487	11321
35°	11398	11298	11137
40°	11138	11018	10819
45°	10684	10497	10280
50°	9884	9647	9456
55°	8627	8432	8253
60°	7270	7209	7065
65°	6287	6311	6263
70°	5775	5805	5805
75°	5547	5547	5586
80°	5218	5276	5218
85°	4203	4668	4668



TEST NUMBER: P561797

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.2	2.3
10°-20°	346.6	6.6
20°-30°	522.9	9.9
30°-40°	623.0	11.8
40°-50°	614.2	11.6
50°-60°	469.4	8.9
60°-70°	290.5	5.5
70°-80°	165.0	3.1
80°-90°	50.2	1.0
90°-100°	152.2	2.9
100°-110°	433.0	8.2
110°-120°	414.9	7.9
120°-130°	328.4	6.2
130°-140°	263.6	5.0
140°-150°	206.3	3.9
150°-160°	151.0	2.9
160°-170°	93.5	1.8
170°-180°	31.7	0.6
0°-30°	990.7	18.8
0°-40°	1613.6	30.6
0°-60°	2697.3	51.1
0°-90°	3202.9	60.7
90°-120°	1000.1	18.9
90°-150°	1798.3	34.1
90°-180°	2075.0	39.3
0°-180°	5277.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1281	1281	1281	1281	1281	
5°	1288	1274	1278	1273	1271	122
15°	1239	1226	1232	1227	1225	350
25°	1149	1135	1141	1129	1128	529
35°	1012	1000	1003	990	989	632
45°	819	808	804	790	788	627
55°	536	528	524	515	513	481
65°	288	286	289	287	287	292
75°	156	156	156	157	157	164
85°	40	42	44	44	44	46
90°	0	0	0	0	0	2
95°	16	66	295	102	63	19
105°	67	102	441	779	741	71
115°	125	151	335	709	832	123
125°	176	196	319	530	634	158
135°	216	234	316	448	506	167
145°	255	268	318	388	422	159
155°	291	298	326	350	364	134
165°	321	322	330	337	342	90
175°	336	335	333	331	329	32
180°	334	334	334	334	334	

TEST NUMBER: P561797

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1281.2	1281.2	1281.2	1281.2	1281.2
2.5°	1289.2	1277.9	1281.2	1278.4	1272.4
5°	1287.8	1273.8	1277.9	1273.4	1271.3
7.5°	1277.9	1264.1	1268.2	1263.8	1262.5
10°	1269.1	1256.1	1260.2	1255.8	1253.6
12.5°	1259.4	1245.6	1250.5	1245.2	1243.0
15°	1239.3	1226.3	1231.6	1227.1	1224.9
17.5°	1217.2	1203.4	1208.6	1203.5	1200.7
20°	1199.6	1186.6	1191.8	1184.1	1183.0
22.5°	1180.1	1167.2	1172.4	1162.0	1161.8
25°	1148.8	1134.8	1141.1	1128.9	1127.8
27.5°	1111.5	1098.5	1103.8	1091.4	1090.1
30°	1085.9	1072.9	1078.2	1064.9	1062.7
32.5°	1056.8	1044.7	1049.0	1035.8	1034.5
35°	1012.0	1000.1	1003.1	989.9	988.8
37.5°	961.0	950.2	951.9	937.3	936.2
40°	924.8	914.0	914.8	899.4	898.3
42.5°	885.0	874.3	873.3	857.9	856.8
45°	818.8	808.0	804.5	790.1	787.9
47.5°	743.3	732.6	725.9	714.2	712.7
50°	688.6	677.8	672.1	662.1	658.8
52.5°	629.5	618.7	613.8	604.7	601.4
55°	536.3	527.7	524.2	515.3	513.1
57.5°	447.8	442.0	441.0	432.3	431.5
60°	394.0	390.7	390.7	382.9	382.9
62.5°	348.1	345.7	347.4	342.3	341.4
65°	288.0	285.9	289.1	286.9	286.9
67.5°	240.6	240.6	242.6	241.7	241.7
70°	214.1	214.1	215.2	215.2	215.2
72.5°	190.3	189.4	192.2	192.2	191.4
75°	155.6	155.6	155.6	156.7	156.7
77.5°	121.2	121.4	122.3	122.0	121.2
80°	98.2	99.3	99.3	98.2	98.2
82.5°	75.3	76.3	76.4	76.1	75.3
85°	39.7	41.9	44.1	44.1	44.1
87.5°	11.5	14.9	17.7	17.6	16.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.1	26.9	62.5	18.2	13.7
95°	16.5	65.6	294.6	102.0	62.9
97.5°	30.3	76.8	453.7	324.7	222.5
100°	40.0	83.5	488.3	494.6	381.0
102.5°	50.7	90.6	480.6	633.0	533.8
105°	67.3	102.1	441.3	779.4	740.9
107.5°	84.2	115.4	395.3	820.7	855.0
110°	95.9	125.1	368.9	804.9	881.9

TEST NUMBER: P561797

CATALOG NUMBER: SQ4-PR1-025U-075D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	107.0	134.7	351.1	767.6	877.3
115°	125.1	151.2	334.6	708.8	832.4
117.5°	141.0	165.4	324.8	644.6	775.5
120°	153.7	174.1	323.8	607.9	733.3
122.5°	163.8	184.3	321.3	575.7	692.2
125°	176.5	195.8	319.4	530.0	633.6
127.5°	190.3	208.4	318.3	502.6	588.1
130°	197.5	215.5	316.8	483.6	558.1
132.5°	205.1	222.6	316.8	468.7	537.3
135°	215.9	233.9	315.6	447.7	506.0
137.5°	226.0	243.5	315.4	429.8	480.3
140°	233.7	251.7	314.9	415.1	463.5
142.5°	242.3	257.3	316.4	403.3	446.7
145°	254.6	267.6	318.1	387.5	422.2
147.5°	265.1	277.8	320.9	371.5	401.5
150°	274.3	283.0	321.9	366.2	387.3
152.5°	281.4	290.6	322.9	359.0	378.7
155°	290.8	297.6	325.7	350.2	364.4
157.5°	302.5	306.6	326.3	346.1	356.3
160°	308.6	311.7	328.9	343.1	351.7
162.5°	312.1	315.7	329.4	340.5	347.2
165°	321.3	322.5	329.5	336.6	341.6
167.5°	327.5	326.4	332.4	335.7	337.6
170°	329.5	328.9	331.4	332.1	334.6
172.5°	334.1	332.0	333.0	331.1	333.1
175°	336.5	334.6	333.3	331.4	328.9
177.5°	337.5	334.5	333.0	330.9	331.4
180°	334.0	334.0	334.0	334.0	334.0

(END OF REPORT)