

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P561966

Luminaire Tested: **SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561966
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4210.4 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 42.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561966

CATALOG NUMBER: SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561966

CATALOG NUMBER: SQ4-PR1-OU-100D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85				
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72				
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62				
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54				
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47				
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41				
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37				
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33				
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30				
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15539	15539	15539
5°	15680	15558	15478
10°	15630	15521	15439
15°	15561	15464	15381
20°	15483	15382	15268
25°	15374	15270	15093
30°	15208	15099	14883
35°	14983	14853	14640
40°	14642	14484	14223
45°	14045	13799	13515
50°	12993	12681	12431
55°	11340	11084	10851
60°	9557	9475	9289
65°	8265	8298	8235
70°	7591	7631	7631
75°	7290	7290	7343
80°	6859	6939	6859
85°	5526	6140	6140



TEST NUMBER: P561966

CATALOG NUMBER: SQ4-PR1-OU-100D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.3	3.8
10°-20°	455.7	10.8
20°-30°	687.3	16.3
30°-40°	819.0	19.5
40°-50°	807.4	19.2
50°-60°	617.1	14.7
60°-70°	381.9	9.1
70°-80°	216.9	5.2
80°-90°	66.0	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1302.3	30.9
0°-40°	2121.2	50.4
0°-60°	3545.7	84.2
0°-90°	4210.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4210.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1684	1684	1684	1684	1684	
5°	1693	1674	1680	1674	1671	161
15°	1629	1612	1619	1613	1610	460
25°	1510	1492	1500	1484	1483	695
35°	1330	1315	1319	1301	1300	830
45°	1076	1062	1058	1039	1036	825
55°	705	694	689	677	675	632
65°	379	376	380	377	377	384
75°	204	204	204	206	206	216
85°	52	55	58	58	58	63
90°	0	0	0	0	0	



TEST NUMBER: P561966

CATALOG NUMBER: SQ4-PR1-OU-100D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.2	1684.2	1684.2	1684.2	1684.2
2.5°	1694.7	1679.9	1684.2	1680.6	1672.6
5°	1693.0	1674.5	1679.9	1674.0	1671.2
7.5°	1679.9	1661.7	1667.1	1661.3	1659.6
10°	1668.3	1651.3	1656.7	1650.8	1648.0
12.5°	1655.5	1637.4	1643.9	1636.9	1634.1
15°	1629.1	1612.1	1619.0	1613.1	1610.3
17.5°	1600.1	1582.0	1588.8	1582.0	1578.3
20°	1576.9	1559.9	1566.7	1556.6	1555.1
22.5°	1551.4	1534.3	1541.2	1527.6	1527.3
25°	1510.2	1491.7	1500.0	1484.0	1482.6
27.5°	1461.1	1444.1	1451.0	1434.7	1433.0
30°	1427.5	1410.5	1417.3	1399.8	1397.0
32.5°	1389.2	1373.3	1379.0	1361.6	1359.9
35°	1330.3	1314.7	1318.7	1301.2	1299.8
37.5°	1263.3	1249.1	1251.4	1232.2	1230.8
40°	1215.7	1201.5	1202.6	1182.3	1180.9
42.5°	1163.5	1149.3	1148.1	1127.7	1126.3
45°	1076.4	1062.2	1057.6	1038.6	1035.8
47.5°	977.2	963.0	954.3	938.8	936.9
50°	905.2	891.0	883.5	870.3	866.1
52.5°	827.5	813.3	806.9	794.9	790.6
55°	705.0	693.7	689.1	677.4	674.6
57.5°	588.7	581.0	579.7	568.4	567.2
60°	517.9	513.6	513.5	503.4	503.4
62.5°	457.5	454.4	456.7	450.0	448.8
65°	378.6	375.8	380.1	377.2	377.2
67.5°	316.3	316.3	318.9	317.7	317.7
70°	281.4	281.4	282.9	282.9	282.9
72.5°	250.1	249.0	252.7	252.7	251.5
75°	204.5	204.5	204.5	206.0	206.0
77.5°	159.3	159.6	160.7	160.4	159.3
80°	129.1	130.5	130.6	129.1	129.1
82.5°	98.9	100.4	100.4	100.1	98.9
85°	52.2	55.1	58.0	58.0	58.0
87.5°	15.1	19.6	23.2	23.2	22.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)