

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P561973

Luminaire Tested: **SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561973  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4860.1 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 55.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561973  
CATALOG NUMBER: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561973

CATALOG NUMBER: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85				
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72				
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62				
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54				
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47				
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41				
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37				
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33				
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30				
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17937	17937	17937
5°	18099	17959	17865
10°	18041	17915	17822
15°	17962	17850	17754
20°	17871	17756	17625
25°	17746	17627	17422
30°	17554	17429	17180
35°	17295	17144	16899
40°	16900	16719	16417
45°	16212	15927	15600
50°	14998	14638	14349
55°	13090	12794	12526
60°	11031	10939	10723
65°	9542	9577	9505
70°	8764	8808	8808
75°	8416	8416	8477
80°	7917	8007	7917
85°	6383	7093	7093



TEST NUMBER: P561973

CATALOG NUMBER: SQ4-PR1-OU-125D-92765-1D-UNV-STD-W-4 (3000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.8	3.8
10°-20°	526.0	10.8
20°-30°	793.4	16.3
30°-40°	945.3	19.5
40°-50°	932.0	19.2
50°-60°	712.3	14.7
60°-70°	440.8	9.1
70°-80°	250.4	5.2
80°-90°	76.2	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1503.2	30.9
0°-40°	2448.5	50.4
0°-60°	4092.8	84.2
0°-90°	4860.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4860.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1944	1944	1944	1944	1944	
5°	1954	1933	1939	1932	1929	185
15°	1880	1861	1869	1862	1859	531
25°	1743	1722	1732	1713	1711	802
35°	1536	1518	1522	1502	1500	958
45°	1242	1226	1221	1199	1196	952
55°	814	801	795	782	779	729
65°	437	434	439	435	435	443
75°	236	236	236	238	238	249
85°	60	64	67	67	67	72
90°	0	0	0	0	0	



TEST NUMBER: P561973

CATALOG NUMBER: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1944.1	1944.1	1944.1	1944.1	1944.1
2.5°	1956.2	1939.1	1944.1	1939.9	1930.7
5°	1954.2	1932.9	1939.1	1932.3	1929.0
7.5°	1939.1	1918.1	1924.4	1917.6	1915.7
10°	1925.7	1906.1	1912.3	1905.5	1902.3
12.5°	1911.0	1890.0	1897.6	1889.5	1886.2
15°	1880.5	1860.8	1868.8	1862.0	1858.7
17.5°	1847.0	1826.0	1833.9	1826.1	1821.9
20°	1820.2	1800.6	1808.5	1796.7	1795.1
22.5°	1790.7	1771.1	1779.0	1763.3	1762.9
25°	1743.2	1721.9	1731.5	1713.0	1711.4
27.5°	1686.6	1666.9	1674.9	1656.1	1654.1
30°	1647.7	1628.1	1636.0	1615.8	1612.6
32.5°	1603.5	1585.2	1591.8	1571.7	1569.7
35°	1535.5	1517.5	1522.1	1502.0	1500.4
37.5°	1458.2	1441.8	1444.4	1422.3	1420.7
40°	1403.2	1386.9	1388.2	1364.7	1363.1
42.5°	1343.0	1326.6	1325.2	1301.7	1300.1
45°	1242.5	1226.1	1220.7	1198.9	1195.6
47.5°	1128.0	1111.6	1101.5	1083.7	1081.4
50°	1044.9	1028.5	1019.8	1004.6	999.7
52.5°	955.1	938.8	931.4	917.5	912.6
55°	813.8	800.7	795.4	781.9	778.7
57.5°	679.5	670.7	669.1	656.0	654.7
60°	597.8	592.9	592.8	581.1	581.1
62.5°	528.1	524.5	527.1	519.4	518.1
65°	437.1	433.8	438.7	435.4	435.4
67.5°	365.0	365.0	368.1	366.7	366.7
70°	324.9	324.9	326.5	326.5	326.5
72.5°	288.7	287.4	291.7	291.7	290.4
75°	236.1	236.1	236.1	237.8	237.8
77.5°	183.9	184.2	185.5	185.2	183.9
80°	149.0	150.7	150.7	149.0	149.0
82.5°	114.2	115.8	115.9	115.5	114.2
85°	60.3	63.6	67.0	67.0	67.0
87.5°	17.4	22.7	26.8	26.8	25.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)