

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P561979

Luminaire Tested: **SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561979  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (6500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5330.7 lumens  
Efficiency: N/A  
Efficacy: 96.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 55.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561979

CATALOG NUMBER: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (6500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561979

CATALOG NUMBER: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (6500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85				
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72				
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62				
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54				
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47				
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41				
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37				
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33				
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30				
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19674	19674	19674
5°	19851	19698	19595
10°	19788	19650	19547
15°	19701	19578	19473
20°	19602	19476	19331
25°	19464	19333	19109
30°	19254	19117	18843
35°	18969	18804	18536
40°	18537	18338	18007
45°	17782	17470	17111
50°	16450	16054	15739
55°	14358	14033	13739
60°	12099	11998	11760
65°	10466	10505	10424
70°	9611	9663	9663
75°	9233	9233	9297
80°	8687	8783	8687
85°	6997	7781	7781



TEST NUMBER: P561979

CATALOG NUMBER: SQ4-PR1-OU-125D-92765-1D-UNV-STD-W-4 (6500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	201.7	3.8
10°-20°	576.9	10.8
20°-30°	870.2	16.3
30°-40°	1036.8	19.5
40°-50°	1022.2	19.2
50°-60°	781.2	14.7
60°-70°	483.5	9.1
70°-80°	274.6	5.2
80°-90°	83.5	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1648.8	30.9
0°-40°	2685.6	50.4
0°-60°	4489.1	84.2
0°-90°	5330.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5330.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2132	2132	2132	2132	2132	
5°	2143	2120	2127	2119	2116	203
15°	2063	2041	2050	2042	2039	582
25°	1912	1889	1899	1879	1877	880
35°	1684	1664	1670	1648	1646	1051
45°	1363	1345	1339	1315	1311	1044
55°	893	878	872	858	854	800
65°	479	476	481	478	478	486
75°	259	259	259	261	261	274
85°	66	70	74	74	74	79
90°	0	0	0	0	0	



TEST NUMBER: P561979

CATALOG NUMBER: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2132.4	2132.4	2132.4	2132.4	2132.4
2.5°	2145.6	2126.9	2132.4	2127.7	2117.7
5°	2143.4	2120.1	2126.9	2119.4	2115.8
7.5°	2126.9	2103.9	2110.7	2103.3	2101.2
10°	2112.2	2090.6	2097.5	2090.1	2086.5
12.5°	2096.0	2073.0	2081.3	2072.4	2068.8
15°	2062.6	2041.0	2049.7	2042.3	2038.7
17.5°	2025.9	2002.9	2011.5	2003.0	1998.3
20°	1996.5	1974.9	1983.6	1970.7	1968.9
22.5°	1964.1	1942.6	1951.3	1934.0	1933.7
25°	1912.0	1888.6	1899.1	1878.9	1877.1
27.5°	1849.9	1828.3	1837.0	1816.4	1814.3
30°	1807.3	1785.7	1794.4	1772.3	1768.7
32.5°	1758.8	1738.7	1745.9	1723.9	1721.7
35°	1684.2	1664.5	1669.5	1647.5	1645.7
37.5°	1599.4	1581.4	1584.3	1560.0	1558.2
40°	1539.1	1521.2	1522.6	1496.8	1495.1
42.5°	1473.0	1455.1	1453.5	1427.8	1426.0
45°	1362.8	1344.9	1338.9	1315.0	1311.4
47.5°	1237.2	1219.2	1208.2	1188.6	1186.1
50°	1146.1	1128.1	1118.5	1101.9	1096.5
52.5°	1047.6	1029.7	1021.6	1006.4	1001.0
55°	892.6	878.3	872.4	857.6	854.1
57.5°	745.3	735.6	733.9	719.6	718.1
60°	655.7	650.3	650.2	637.3	637.3
62.5°	579.3	575.3	578.2	569.7	568.3
65°	479.4	475.8	481.2	477.5	477.5
67.5°	400.4	400.4	403.7	402.2	402.2
70°	356.3	356.3	358.2	358.2	358.2
72.5°	316.6	315.2	319.9	319.9	318.5
75°	259.0	259.0	259.0	260.8	260.8
77.5°	201.7	202.0	203.5	203.1	201.7
80°	163.5	165.3	165.3	163.5	163.5
82.5°	125.3	127.1	127.1	126.7	125.3
85°	66.1	69.7	73.5	73.5	73.5
87.5°	19.1	24.8	29.4	29.4	27.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)