

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561985

Luminaire Tested: **SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561985  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6093.6 lumens  
Efficiency: N/A  
Efficacy: 115.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 52.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561985  
CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561985

CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31		
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27		
2	86	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23		
3	78	69	62	57	70	62	56	52	50	46	42	38	35	33	27	26	24	19		
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17		
5	66	54	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15		
6	60	49	41	35	54	44	37	33	36	31	27	28	24	22	20	18	16	13		
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14	12		
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10		
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9		
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	11	8		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7050	7050	7050
5°	7114	7059	7022
10°	7091	7041	7005
15°	7060	7016	6978
20°	7024	6979	6928
25°	6975	6927	6847
30°	6899	6850	6752
35°	6797	6739	6642
40°	6642	6571	6452
45°	6373	6260	6131
50°	5895	5753	5639
55°	5146	5028	4922
60°	4336	4299	4215
65°	3751	3764	3735
70°	3445	3461	3461
75°	3308	3308	3333
80°	3114	3145	3114
85°	2509	2784	2784



TEST NUMBER: P561985

CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.3	1.2
10°-20°	206.7	3.4
20°-30°	311.8	5.1
30°-40°	371.6	6.1
40°-50°	366.3	6.0
50°-60°	280.0	4.6
60°-70°	173.2	2.8
70°-80°	98.4	1.6
80°-90°	29.9	0.5
90°-100°	306.9	5.0
100°-110°	873.2	14.3
110°-120°	836.6	13.7
120°-130°	662.1	10.9
130°-140°	531.5	8.7
140°-150°	416.1	6.8
150°-160°	304.4	5.0
160°-170°	188.6	3.1
170°-180°	64.0	1.1
0°-30°	590.8	9.7
0°-40°	962.4	15.8
0°-60°	1608.6	26.4
0°-90°	1910.2	31.3
90°-120°	2016.7	33.1
90°-150°	3626.3	59.5
90°-180°	4183.0	68.6
0°-180°	6093.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	764	764	764	764	764	
5°	768	760	762	760	758	73
15°	739	731	734	732	731	209
25°	685	677	680	673	673	315
35°	604	596	598	590	590	377
45°	488	482	480	471	470	374
55°	320	315	313	307	306	287
65°	172	170	172	171	171	174
75°	93	93	93	94	94	98
85°	24	25	26	26	26	28
90°	0	0	0	0	0	2
95°	33	132	594	206	127	38
105°	136	206	890	1572	1494	144
115°	252	305	675	1429	1678	248
125°	356	395	644	1069	1278	319
135°	435	472	636	903	1020	336
145°	513	540	642	781	851	321
155°	586	600	657	706	735	271
165°	648	650	664	679	689	182
175°	679	675	672	668	663	64
180°	674	674	674	674	674	



TEST NUMBER: P561985

CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	764.1	764.1	764.1	764.1	764.1
2.5°	768.9	762.2	764.1	762.5	758.9
5°	768.1	759.7	762.2	759.5	758.2
7.5°	762.2	753.9	756.4	753.7	752.9
10°	756.9	749.2	751.6	749.0	747.7
12.5°	751.1	742.9	745.8	742.6	741.4
15°	739.1	731.4	734.5	731.9	730.6
17.5°	726.0	717.7	720.8	717.8	716.1
20°	715.4	707.7	710.8	706.2	705.6
22.5°	703.8	696.1	699.2	693.0	692.9
25°	685.2	676.8	680.5	673.3	672.6
27.5°	662.9	655.2	658.3	650.9	650.1
30°	647.6	639.9	643.0	635.1	633.8
32.5°	630.3	623.1	625.7	617.7	617.0
35°	603.5	596.5	598.3	590.4	589.7
37.5°	573.1	566.7	567.7	559.0	558.4
40°	551.5	545.1	545.6	536.4	535.7
42.5°	527.8	521.4	520.9	511.6	511.0
45°	488.4	481.9	479.8	471.2	469.9
47.5°	443.3	436.9	432.9	425.9	425.0
50°	410.7	404.3	400.8	394.9	392.9
52.5°	375.4	369.0	366.1	360.6	358.7
55°	319.9	314.7	312.6	307.3	306.0
57.5°	267.1	263.6	263.0	257.9	257.3
60°	235.0	233.0	233.0	228.4	228.4
62.5°	207.6	206.2	207.2	204.2	203.6
65°	171.8	170.5	172.4	171.1	171.1
67.5°	143.5	143.5	144.7	144.1	144.1
70°	127.7	127.7	128.3	128.3	128.3
72.5°	113.5	113.0	114.7	114.6	114.1
75°	92.8	92.8	92.8	93.5	93.5
77.5°	72.3	72.4	72.9	72.8	72.3
80°	58.6	59.2	59.2	58.6	58.6
82.5°	44.9	45.5	45.5	45.4	44.9
85°	23.7	25.0	26.3	26.3	26.3
87.5°	6.8	8.9	10.5	10.5	10.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.2	54.3	126.0	36.7	27.7
95°	33.3	132.2	594.1	205.6	126.8
97.5°	61.2	154.8	914.9	654.7	448.6
100°	80.7	168.3	984.6	997.3	768.2
102.5°	102.2	182.8	969.2	1276.6	1076.5
105°	135.7	205.8	889.8	1571.8	1494.2
107.5°	169.8	232.6	797.1	1655.0	1724.1
110°	193.3	252.2	743.9	1623.2	1778.4

TEST NUMBER: P561985

CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	215.9	271.7	708.0	1547.9	1769.2
115°	252.2	304.8	674.7	1429.4	1678.5
117.5°	284.2	333.6	655.0	1299.9	1563.8
120°	309.8	351.2	653.0	1225.9	1478.8
122.5°	330.3	371.6	647.9	1161.0	1395.8
125°	355.9	394.7	644.0	1068.7	1277.8
127.5°	383.8	420.2	642.0	1013.6	1185.9
130°	398.2	434.5	638.9	975.2	1125.4
132.5°	413.6	448.9	638.9	945.2	1083.4
135°	435.3	471.6	636.3	902.8	1020.4
137.5°	455.8	491.1	636.1	866.8	968.5
140°	471.2	507.5	635.1	837.0	934.7
142.5°	488.6	518.9	638.1	813.2	900.9
145°	513.4	539.7	641.5	781.3	851.4
147.5°	534.7	560.2	647.1	749.1	809.7
150°	553.1	570.6	649.1	738.5	781.0
152.5°	567.5	586.0	651.2	724.0	763.6
155°	586.4	600.2	656.8	706.1	734.9
157.5°	610.0	618.2	658.1	698.0	718.5
160°	622.3	628.5	663.2	691.8	709.3
162.5°	629.4	636.7	664.2	686.6	700.1
165°	647.9	650.4	664.5	678.8	688.8
167.5°	660.4	658.2	670.4	676.9	680.9
170°	664.5	663.3	668.3	669.7	674.7
172.5°	673.7	669.5	671.4	667.7	671.7
175°	678.6	674.8	672.2	668.2	663.2
177.5°	680.6	674.6	671.4	667.3	668.3
180°	673.5	673.5	673.5	673.5	673.5

(END OF REPORT)