

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561829

Luminaire Tested: **SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561829
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3998.5 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561829
CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561829

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48	48	48	48	48	48	48		
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41	41	41	41		
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35	35	35	35		
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30	30	30	30	30	30	30		
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26	26	26	26	26	26	26		
5	68	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	22	22	22	22	22	22	22		
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23	20	20	20	20	20	20	20		
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	18	18	18	18		
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	24	20	18	16	16	16	16	16	16	16		
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16	14	14	14	14	14	14	14		
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13	13	13	13	13	13	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7050	7050	7050
5°	7114	7059	7022
10°	7091	7041	7005
15°	7060	7016	6978
20°	7024	6979	6928
25°	6975	6927	6847
30°	6899	6850	6752
35°	6797	6739	6642
40°	6642	6571	6452
45°	6373	6260	6131
50°	5895	5753	5639
55°	5146	5028	4922
60°	4336	4299	4215
65°	3751	3764	3735
70°	3445	3461	3461
75°	3308	3308	3333
80°	3114	3145	3114
85°	2509	2784	2784



TEST NUMBER: P561829

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.8
10°-20°	206.7	5.2
20°-30°	311.8	7.8
30°-40°	371.6	9.3
40°-50°	366.3	9.2
50°-60°	280.0	7.0
60°-70°	173.2	4.3
70°-80°	98.4	2.5
80°-90°	29.9	0.7
90°-100°	153.2	3.8
100°-110°	435.9	10.9
110°-120°	417.6	10.4
120°-130°	330.5	8.3
130°-140°	265.3	6.6
140°-150°	207.7	5.2
150°-160°	152.0	3.8
160°-170°	94.1	2.4
170°-180°	31.9	0.8
0°-30°	590.8	14.8
0°-40°	962.4	24.1
0°-60°	1608.6	40.2
0°-90°	1910.2	47.8
90°-120°	1006.7	25.2
90°-150°	1810.2	45.3
90°-180°	2088.0	52.2
0°-180°	3998.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	764	764	764	764	764	
5°	768	760	762	760	758	73
15°	739	731	734	732	731	209
25°	685	677	680	673	673	315
35°	604	596	598	590	590	377
45°	488	482	480	471	470	374
55°	320	315	313	307	306	287
65°	172	170	172	171	171	174
75°	93	93	93	94	94	98
85°	24	25	26	26	26	28
90°	0	0	0	0	0	2
95°	17	66	297	103	63	19
105°	68	103	444	785	746	72
115°	126	152	337	714	838	124
125°	178	197	322	534	638	159
135°	217	235	318	451	509	168
145°	256	269	320	390	425	160
155°	293	300	328	352	367	135
165°	323	325	332	339	344	91
175°	339	337	336	334	331	32
180°	336	336	336	336	336	

TEST NUMBER: P561829

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	764.1	764.1	764.1	764.1	764.1
2.5°	768.9	762.2	764.1	762.5	758.9
5°	768.1	759.7	762.2	759.5	758.2
7.5°	762.2	753.9	756.4	753.7	752.9
10°	756.9	749.2	751.6	749.0	747.7
12.5°	751.1	742.9	745.8	742.6	741.4
15°	739.1	731.4	734.5	731.9	730.6
17.5°	726.0	717.7	720.8	717.8	716.1
20°	715.4	707.7	710.8	706.2	705.6
22.5°	703.8	696.1	699.2	693.0	692.9
25°	685.2	676.8	680.5	673.3	672.6
27.5°	662.9	655.2	658.3	650.9	650.1
30°	647.6	639.9	643.0	635.1	633.8
32.5°	630.3	623.1	625.7	617.7	617.0
35°	603.5	596.5	598.3	590.4	589.7
37.5°	573.1	566.7	567.7	559.0	558.4
40°	551.5	545.1	545.6	536.4	535.7
42.5°	527.8	521.4	520.9	511.6	511.0
45°	488.4	481.9	479.8	471.2	469.9
47.5°	443.3	436.9	432.9	425.9	425.0
50°	410.7	404.3	400.8	394.9	392.9
52.5°	375.4	369.0	366.1	360.6	358.7
55°	319.9	314.7	312.6	307.3	306.0
57.5°	267.1	263.6	263.0	257.9	257.3
60°	235.0	233.0	233.0	228.4	228.4
62.5°	207.6	206.2	207.2	204.2	203.6
65°	171.8	170.5	172.4	171.1	171.1
67.5°	143.5	143.5	144.7	144.1	144.1
70°	127.7	127.7	128.3	128.3	128.3
72.5°	113.5	113.0	114.7	114.6	114.1
75°	92.8	92.8	92.8	93.5	93.5
77.5°	72.3	72.4	72.9	72.8	72.3
80°	58.6	59.2	59.2	58.6	58.6
82.5°	44.9	45.5	45.5	45.4	44.9
85°	23.7	25.0	26.3	26.3	26.3
87.5°	6.8	8.9	10.5	10.5	10.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.1	27.1	62.9	18.3	13.8
95°	16.6	66.0	296.6	102.6	63.3
97.5°	30.6	77.3	456.7	326.8	224.0
100°	40.3	84.0	491.5	497.8	383.5
102.5°	51.0	91.2	483.8	637.3	537.4
105°	67.7	102.7	444.2	784.6	745.9
107.5°	84.8	116.1	397.9	826.2	860.7
110°	96.5	125.9	371.3	810.3	887.8



TEST NUMBER: P561829

CATALOG NUMBER: SQ4-PR1-050U-050D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	107.8	135.6	353.4	772.7	883.2
115°	125.9	152.2	336.8	713.6	837.9
117.5°	141.9	166.5	327.0	648.9	780.6
120°	154.7	175.3	326.0	612.0	738.2
122.5°	164.9	185.5	323.4	579.6	696.8
125°	177.7	197.1	321.5	533.5	637.9
127.5°	191.6	209.7	320.5	506.0	592.0
130°	198.8	216.9	318.9	486.8	561.8
132.5°	206.4	224.1	318.9	471.8	540.8
135°	217.3	235.4	317.7	450.7	509.4
137.5°	227.5	245.2	317.5	432.7	483.4
140°	235.2	253.3	317.0	417.8	466.6
142.5°	243.9	259.0	318.5	406.0	449.7
145°	256.3	269.4	320.2	390.0	425.0
147.5°	266.9	279.7	323.0	373.9	404.2
150°	276.1	284.9	324.0	368.6	389.9
152.5°	283.3	292.5	325.1	361.4	381.2
155°	292.7	299.6	327.9	352.5	366.9
157.5°	304.5	308.6	328.5	348.4	358.7
160°	310.6	313.7	331.1	345.3	354.1
162.5°	314.2	317.8	331.6	342.7	349.5
165°	323.4	324.7	331.7	338.9	343.9
167.5°	329.7	328.5	334.7	337.9	339.9
170°	331.7	331.1	333.6	334.3	336.8
172.5°	336.3	334.2	335.2	333.3	335.3
175°	338.7	336.9	335.5	333.6	331.1
177.5°	339.8	336.8	335.2	333.1	333.6
180°	336.2	336.2	336.2	336.2	336.2

(END OF REPORT)