

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561986

Luminaire Tested: **SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561986
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6219.9 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561986

CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561986

CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	86	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	57	70	62	56	52	50	46	42	38	35	33	27	26	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	66	54	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	33	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14	12
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	11	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7196	7196	7196
5°	7261	7205	7167
10°	7238	7188	7150
15°	7206	7161	7123
20°	7170	7124	7071
25°	7120	7071	6990
30°	7043	6993	6892
35°	6938	6878	6779
40°	6781	6707	6587
45°	6504	6390	6259
50°	6017	5872	5757
55°	5252	5133	5025
60°	4425	4388	4301
65°	3827	3842	3814
70°	3515	3534	3534
75°	3376	3376	3401
80°	3177	3214	3177
85°	2562	2848	2848



TEST NUMBER: P561986

CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.2
10°-20°	211.0	3.4
20°-30°	318.3	5.1
30°-40°	379.2	6.1
40°-50°	373.9	6.0
50°-60°	285.8	4.6
60°-70°	176.8	2.8
70°-80°	100.4	1.6
80°-90°	30.6	0.5
90°-100°	313.2	5.0
100°-110°	891.3	14.3
110°-120°	853.9	13.7
120°-130°	675.9	10.9
130°-140°	542.5	8.7
140°-150°	424.7	6.8
150°-160°	310.7	5.0
160°-170°	192.5	3.1
170°-180°	65.3	1.1
0°-30°	603.1	9.7
0°-40°	982.3	15.8
0°-60°	1642.0	26.4
0°-90°	1949.8	31.3
90°-120°	2058.5	33.1
90°-150°	3701.5	59.5
90°-180°	4270.0	68.7
0°-180°	6219.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	780	780	780	780	780	
5°	784	776	778	775	774	74
15°	754	747	750	747	746	213
25°	699	691	695	687	687	322
35°	616	609	611	603	602	384
45°	498	492	490	481	480	382
55°	326	321	319	314	312	293
65°	175	174	176	175	175	178
75°	95	95	95	95	95	100
85°	24	26	27	27	27	28
90°	0	0	0	0	0	2
95°	34	135	606	210	129	39
105°	138	210	908	1604	1525	147
115°	258	311	689	1459	1713	253
125°	363	403	657	1091	1304	325
135°	444	481	650	922	1042	343
145°	524	551	655	798	869	327
155°	599	613	670	721	750	277
165°	661	664	678	693	703	186
175°	693	689	686	682	677	66
180°	687	687	687	687	687	



TEST NUMBER: P561986

CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	780.0	780.0	780.0	780.0	780.0
2.5°	784.8	778.0	780.0	778.3	774.6
5°	784.0	775.5	778.0	775.2	773.9
7.5°	778.0	769.5	772.0	769.3	768.5
10°	772.6	764.7	767.2	764.5	763.2
12.5°	766.7	758.3	761.3	758.0	756.7
15°	754.4	746.6	749.7	747.0	745.7
17.5°	741.0	732.6	735.8	732.6	730.9
20°	730.3	722.4	725.6	720.8	720.2
22.5°	718.4	710.5	713.7	707.4	707.3
25°	699.4	690.8	694.6	687.2	686.6
27.5°	676.6	668.8	671.9	664.4	663.6
30°	661.1	653.2	656.4	648.3	646.9
32.5°	643.3	636.0	638.6	630.5	629.8
35°	616.0	608.8	610.7	602.6	601.9
37.5°	585.0	578.4	579.5	570.6	570.0
40°	563.0	556.4	556.9	547.5	546.9
42.5°	538.8	532.2	531.7	522.2	521.6
45°	498.5	491.9	489.7	481.0	479.7
47.5°	452.5	446.0	441.9	434.8	433.9
50°	419.2	412.6	409.1	403.0	401.1
52.5°	383.2	376.6	373.7	368.1	366.1
55°	326.5	321.2	319.1	313.7	312.4
57.5°	272.6	269.1	268.5	263.2	262.7
60°	239.8	237.9	237.8	233.1	233.1
62.5°	211.9	210.4	211.5	208.4	207.9
65°	175.3	174.0	176.0	174.7	174.7
67.5°	146.5	146.5	147.7	147.1	147.1
70°	130.3	130.3	131.0	131.0	131.0
72.5°	115.8	115.3	117.0	117.0	116.5
75°	94.7	94.7	94.7	95.4	95.4
77.5°	73.8	73.9	74.4	74.3	73.8
80°	59.8	60.4	60.5	59.8	59.8
82.5°	45.8	46.5	46.5	46.3	45.8
85°	24.2	25.5	26.9	26.9	26.9
87.5°	7.0	9.1	10.7	10.7	10.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.5	55.4	128.6	37.4	28.2
95°	34.0	134.9	606.4	209.9	129.4
97.5°	62.5	158.1	933.9	668.3	457.9
100°	82.3	171.8	1005.0	1018.0	784.1
102.5°	104.3	186.6	989.3	1303.0	1098.8
105°	138.5	210.1	908.3	1604.4	1525.1
107.5°	173.3	237.4	813.7	1689.3	1759.9
110°	197.3	257.4	759.3	1656.8	1815.3

TEST NUMBER: P561986

CATALOG NUMBER: SQ4-PR1-100U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	220.3	277.3	722.7	1579.9	1805.9
115°	257.5	311.1	688.7	1459.0	1713.3
117.5°	290.1	340.5	668.6	1326.9	1596.2
120°	316.3	358.4	666.5	1251.3	1509.5
122.5°	337.2	379.3	661.3	1185.0	1424.8
125°	363.3	402.9	657.4	1090.9	1304.3
127.5°	391.8	428.9	655.3	1034.6	1210.4
130°	406.4	443.5	652.1	995.4	1148.8
132.5°	422.1	458.2	652.1	964.8	1105.9
135°	444.3	481.4	649.5	921.5	1041.6
137.5°	465.3	501.3	649.3	884.8	988.5
140°	480.9	518.0	648.2	854.4	954.0
142.5°	498.7	529.6	651.4	830.1	919.5
145°	524.1	550.9	654.8	797.5	869.1
147.5°	545.8	571.8	660.5	764.6	826.5
150°	564.6	582.5	662.6	753.8	797.2
152.5°	579.2	598.1	664.7	739.0	779.4
155°	598.6	612.6	670.4	720.8	750.2
157.5°	622.6	631.0	671.7	712.5	733.4
160°	635.1	641.5	677.0	706.1	724.0
162.5°	642.5	649.9	678.0	700.8	714.6
165°	661.3	663.8	678.3	692.9	703.1
167.5°	674.1	671.8	684.3	690.9	695.0
170°	678.3	677.0	682.2	683.6	688.7
172.5°	687.7	683.3	685.3	681.5	685.6
175°	692.7	688.8	686.1	682.1	677.0
177.5°	694.7	688.6	685.3	681.2	682.2
180°	687.4	687.4	687.4	687.4	687.4

(END OF REPORT)