

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562013

Luminaire Tested: **SQ4-PR1-100U-100D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562013
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-100U-100D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8303.4 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 74.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562013

CATALOG NUMBER: SQ4-PR1-100U-100D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562013

CATALOG NUMBER: SQ4-PR1-100U-100D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	97	93	89	86	89	86	83	80	72	70	68	60	58	56	48	47	46				40	
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	42	41	39				34	
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	41	45	40	35	38	34	30	31	28	25				22	
6	63	51	43	38	58	48	40	35	41	35	31	34	30	27	28	25	22				20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	25	22	20				17	
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	23	20	18				16	
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14507	14507	14507
5°	14638	14525	14450
10°	14591	14490	14413
15°	14527	14437	14359
20°	14455	14361	14255
25°	14353	14256	14090
30°	14198	14097	13894
35°	13988	13866	13668
40°	13669	13523	13277
45°	13112	12882	12617
50°	12130	11839	11605
55°	10587	10348	10131
60°	8922	8846	8673
65°	7717	7746	7687
70°	7086	7124	7124
75°	6809	6809	6855
80°	6402	6477	6402
85°	5166	5738	5738



TEST NUMBER: P562013

CATALOG NUMBER: SQ4-PR1-100U-100D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.7	1.8
10°-20°	425.4	5.1
20°-30°	641.7	7.7
30°-40°	764.6	9.2
40°-50°	753.8	9.1
50°-60°	576.1	6.9
60°-70°	356.5	4.3
70°-80°	202.5	2.4
80°-90°	61.6	0.7
90°-100°	320.7	3.9
100°-110°	912.7	11.0
110°-120°	874.4	10.5
120°-130°	692.1	8.3
130°-140°	555.5	6.7
140°-150°	434.9	5.2
150°-160°	318.2	3.8
160°-170°	197.1	2.4
170°-180°	66.9	0.8
0°-30°	1215.8	14.6
0°-40°	1980.4	23.9
0°-60°	3310.2	39.9
0°-90°	3930.8	47.3
90°-120°	2107.9	25.4
90°-150°	3790.4	45.6
90°-180°	4373.0	52.7
0°-180°	8303.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1580	1563	1568	1563	1560	150
15°	1521	1505	1512	1506	1503	429
25°	1410	1393	1400	1386	1384	649
35°	1242	1227	1231	1215	1214	775
45°	1005	992	987	970	967	770
55°	658	648	643	632	630	590
65°	354	351	355	352	352	358
75°	191	191	191	192	192	202
85°	49	51	54	54	54	57
90°	0	0	0	0	0	3
95°	35	138	621	215	132	40
105°	142	215	930	1643	1562	150
115°	264	319	705	1494	1754	260
125°	372	413	673	1117	1336	333
135°	455	493	665	944	1067	351
145°	537	564	670	817	890	335
155°	613	627	686	738	768	283
165°	677	680	695	710	720	190
175°	709	705	703	698	693	67
180°	704	704	704	704	704	



TEST NUMBER: P562013

CATALOG NUMBER: SQ4-PR1-100U-100D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1572.4	1572.4	1572.4	1572.4	1572.4
2.5°	1582.2	1568.4	1572.4	1569.0	1561.6
5°	1580.5	1563.3	1568.3	1562.9	1560.2
7.5°	1568.3	1551.4	1556.4	1551.0	1549.4
10°	1557.5	1541.6	1546.7	1541.2	1538.5
12.5°	1545.6	1528.6	1534.7	1528.2	1525.5
15°	1520.9	1505.0	1511.5	1506.0	1503.3
17.5°	1493.8	1476.9	1483.3	1477.0	1473.5
20°	1472.2	1456.3	1462.7	1453.2	1451.9
22.5°	1448.3	1432.5	1438.9	1426.1	1425.9
25°	1409.9	1392.7	1400.4	1385.5	1384.1
27.5°	1364.1	1348.2	1354.6	1339.4	1337.8
30°	1332.7	1316.8	1323.2	1306.9	1304.2
32.5°	1296.9	1282.1	1287.4	1271.2	1269.6
35°	1241.9	1227.4	1231.1	1214.8	1213.5
37.5°	1179.4	1166.1	1168.3	1150.4	1149.0
40°	1134.9	1121.7	1122.8	1103.8	1102.4
42.5°	1086.2	1072.9	1071.8	1052.8	1051.5
45°	1004.9	991.7	987.3	969.7	967.0
47.5°	912.3	899.0	890.9	876.5	874.6
50°	845.1	831.9	824.8	812.5	808.5
52.5°	772.5	759.3	753.3	742.1	738.1
55°	658.2	647.6	643.3	632.4	629.8
57.5°	549.6	542.4	541.2	530.6	529.6
60°	483.5	479.5	479.4	470.0	470.0
62.5°	427.2	424.2	426.3	420.1	419.0
65°	353.5	350.8	354.8	352.1	352.1
67.5°	295.2	295.2	297.7	296.6	296.6
70°	262.7	262.7	264.1	264.1	264.1
72.5°	233.5	232.4	235.9	235.9	234.8
75°	191.0	191.0	191.0	192.3	192.3
77.5°	148.7	149.0	150.1	149.8	148.7
80°	120.5	121.9	121.9	120.5	120.5
82.5°	92.4	93.7	93.7	93.4	92.4
85°	48.8	51.4	54.2	54.2	54.2
87.5°	14.1	18.3	21.7	21.6	20.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.7	56.8	131.7	38.3	28.9
95°	34.8	138.2	620.9	214.9	132.5
97.5°	64.0	161.8	956.3	684.3	468.9
100°	84.3	175.9	1029.1	1042.4	802.9
102.5°	106.8	191.1	1013.1	1334.3	1125.2
105°	141.9	215.1	930.1	1642.9	1561.7
107.5°	177.5	243.1	833.2	1729.9	1802.1
110°	202.1	263.6	777.5	1696.6	1858.8

TEST NUMBER: P562013

CATALOG NUMBER: SQ4-PR1-100U-100D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.6	284.0	740.1	1617.8	1849.2
115°	263.6	318.6	705.3	1494.1	1754.4
117.5°	297.1	348.6	684.6	1358.7	1634.5
120°	323.9	367.0	682.5	1281.4	1545.7
122.5°	345.3	388.4	677.2	1213.5	1459.0
125°	372.0	412.6	673.1	1117.1	1335.6
127.5°	401.2	439.2	671.0	1059.4	1239.5
130°	416.2	454.1	667.8	1019.3	1176.3
132.5°	432.3	469.2	667.8	988.0	1132.4
135°	455.0	493.0	665.1	943.6	1066.6
137.5°	476.4	513.3	664.8	906.0	1012.3
140°	492.5	530.4	663.8	874.9	976.9
142.5°	510.7	542.3	667.0	850.0	941.6
145°	536.6	564.1	670.5	816.7	889.9
147.5°	558.9	585.5	676.4	783.0	846.3
150°	578.1	596.4	678.5	771.8	816.3
152.5°	593.1	612.5	680.6	756.8	798.1
155°	612.9	627.3	686.5	738.1	768.2
157.5°	637.5	646.2	687.9	729.6	751.0
160°	650.4	656.9	693.2	723.1	741.4
162.5°	657.9	665.5	694.3	717.6	731.8
165°	677.2	679.8	694.6	709.5	720.0
167.5°	690.3	687.9	700.7	707.5	711.7
170°	694.6	693.2	698.6	700.0	705.3
172.5°	704.2	699.7	701.8	697.9	702.0
175°	709.3	705.3	702.6	698.4	693.2
177.5°	711.4	705.1	701.8	697.5	698.6
180°	703.9	703.9	703.9	703.9	703.9

(END OF REPORT)