

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561898

Luminaire Tested: **SQ4-PR1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561898  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6474.8 lumens  
Efficiency: N/A  
Efficacy: 116.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 55.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561898  
CATALOG NUMBER: SQ4-PR1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561898

CATALOG NUMBER: SQ4-PR1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39				35	
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34				30	
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29				26	
5	68	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26				22	
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23				20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20				18	
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	24	20	18				16	
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16				14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11419	11419	11419
5°	11522	11433	11374
10°	11485	11405	11345
15°	11435	11364	11302
20°	11377	11304	11220
25°	11297	11221	11091
30°	11176	11096	10937
35°	11011	10914	10759
40°	10759	10643	10452
45°	10321	10139	9931
50°	9548	9318	9135
55°	8334	8146	7974
60°	7023	6964	6826
65°	6073	6097	6052
70°	5579	5608	5608
75°	5358	5358	5397
80°	5042	5095	5042
85°	4065	4510	4510



TEST NUMBER: P561898

CATALOG NUMBER: SQ4-PR1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.0	1.8
10°-20°	334.9	5.2
20°-30°	505.1	7.8
30°-40°	601.8	9.3
40°-50°	593.3	9.2
50°-60°	453.5	7.0
60°-70°	280.6	4.3
70°-80°	159.4	2.5
80°-90°	48.5	0.7
90°-100°	248.0	3.8
100°-110°	705.7	10.9
110°-120°	676.1	10.4
120°-130°	535.1	8.3
130°-140°	429.5	6.6
140°-150°	336.2	5.2
150°-160°	246.0	3.8
160°-170°	152.4	2.4
170°-180°	51.7	0.8
0°-30°	957.0	14.8
0°-40°	1558.8	24.1
0°-60°	2605.6	40.2
0°-90°	3094.0	47.8
90°-120°	1629.8	25.2
90°-150°	2930.6	45.3
90°-180°	3381.0	52.2
0°-180°	6474.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1238	1238	1238	1238	1238	
5°	1244	1230	1234	1230	1228	118
15°	1197	1185	1190	1185	1183	338
25°	1110	1096	1102	1090	1090	511
35°	978	966	969	956	955	610
45°	791	781	777	763	761	606
55°	518	510	506	498	496	464
65°	278	276	279	277	277	282
75°	150	150	150	151	151	159
85°	38	40	43	43	43	45
90°	0	0	0	0	0	3
95°	27	107	480	166	102	31
105°	110	166	719	1270	1208	116
115°	204	246	545	1155	1356	201
125°	288	319	520	864	1033	257
135°	352	381	514	730	825	271
145°	415	436	518	631	688	259
155°	474	485	531	571	594	219
165°	524	526	537	549	557	147
175°	548	545	543	540	536	52
180°	544	544	544	544	544	



TEST NUMBER: P561898

CATALOG NUMBER: SQ4-PR1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1237.7	1237.7	1237.7	1237.7	1237.7
2.5°	1245.3	1234.5	1237.7	1235.0	1229.1
5°	1244.1	1230.5	1234.5	1230.2	1228.1
7.5°	1234.5	1221.1	1225.1	1220.8	1219.5
10°	1225.9	1213.4	1217.4	1213.1	1211.0
12.5°	1216.6	1203.2	1208.0	1202.9	1200.8
15°	1197.2	1184.6	1189.7	1185.4	1183.3
17.5°	1175.8	1162.5	1167.5	1162.6	1159.8
20°	1158.8	1146.3	1151.3	1143.8	1142.8
22.5°	1140.0	1127.5	1132.6	1122.5	1122.3
25°	1109.7	1096.2	1102.3	1090.5	1089.5
27.5°	1073.7	1061.2	1066.2	1054.3	1053.0
30°	1049.0	1036.5	1041.5	1028.7	1026.6
32.5°	1020.8	1009.2	1013.4	1000.5	999.3
35°	977.6	966.1	969.0	956.2	955.2
37.5°	928.3	917.9	919.6	905.5	904.4
40°	893.3	882.9	883.7	868.8	867.8
42.5°	855.0	844.5	843.7	828.7	827.7
45°	791.0	780.6	777.1	763.2	761.1
47.5°	718.1	707.7	701.2	689.9	688.4
50°	665.2	654.8	649.2	639.5	636.4
52.5°	608.1	597.6	592.9	584.1	581.0
55°	518.1	509.8	506.4	497.8	495.7
57.5°	432.6	427.0	426.0	417.7	416.8
60°	380.6	377.4	377.4	369.9	369.9
62.5°	336.2	333.9	335.6	330.7	329.8
65°	278.2	276.1	279.3	277.2	277.2
67.5°	232.4	232.4	234.3	233.5	233.5
70°	206.8	206.8	207.9	207.9	207.9
72.5°	183.8	183.0	185.7	185.7	184.8
75°	150.3	150.3	150.3	151.4	151.4
77.5°	117.1	117.3	118.1	117.9	117.1
80°	94.9	95.9	95.9	94.9	94.9
82.5°	72.7	73.7	73.8	73.5	72.7
85°	38.4	40.5	42.6	42.6	42.6
87.5°	11.1	14.4	17.1	17.0	16.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.3	43.9	101.8	29.6	22.3
95°	26.9	106.8	480.1	166.2	102.4
97.5°	49.5	125.1	739.4	529.1	362.6
100°	65.2	136.0	795.7	806.0	620.8
102.5°	82.6	147.7	783.3	1031.7	870.0
105°	109.7	166.3	719.1	1270.2	1207.5
107.5°	137.2	188.0	644.2	1337.5	1393.4
110°	156.2	203.8	601.2	1311.8	1437.2

TEST NUMBER: P561898

CATALOG NUMBER: SQ4-PR1-075U-075D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	174.5	219.6	572.2	1250.9	1429.8
115°	203.8	246.3	545.3	1155.2	1356.5
117.5°	229.7	269.6	529.4	1050.5	1263.8
120°	250.4	283.8	527.7	990.7	1195.1
122.5°	267.0	300.3	523.6	938.3	1128.1
125°	287.7	319.0	520.5	863.7	1032.7
127.5°	310.2	339.5	518.8	819.1	958.4
130°	321.8	351.1	516.3	788.1	909.5
132.5°	334.2	362.7	516.3	763.9	875.6
135°	351.8	381.1	514.3	729.6	824.7
137.5°	368.4	396.9	514.0	700.5	782.7
140°	380.8	410.1	513.2	676.4	755.3
142.5°	394.8	419.3	515.7	657.2	728.0
145°	414.9	436.2	518.4	631.4	688.1
147.5°	432.1	452.7	522.9	605.4	654.4
150°	447.0	461.2	524.6	596.8	631.2
152.5°	458.6	473.6	526.3	585.1	617.1
155°	473.9	485.0	530.8	570.7	593.9
157.5°	492.9	499.6	531.8	564.1	580.7
160°	502.9	507.9	536.0	559.1	573.2
162.5°	508.7	514.5	536.8	554.9	565.8
165°	523.6	525.6	537.0	548.6	556.7
167.5°	533.7	531.9	541.8	547.0	550.3
170°	537.0	536.0	540.1	541.3	545.3
172.5°	544.5	541.0	542.6	539.6	542.8
175°	548.4	545.4	543.2	540.0	536.0
177.5°	550.1	545.2	542.6	539.3	540.1
180°	544.3	544.3	544.3	544.3	544.3

(END OF REPORT)