

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562026

Luminaire Tested: **SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562026
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9349.3 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 88.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562026
CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P562026

CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	87	91	88	85	82	75	73	71	63	62	60	53	52	51	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	37	34	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18368	18368	18368
5°	18533	18390	18294
10°	18474	18345	18249
15°	18393	18278	18180
20°	18300	18183	18048
25°	18171	18049	17839
30°	17976	17848	17592
35°	17710	17556	17305
40°	17306	17120	16811
45°	16601	16310	15974
50°	15358	14989	14694
55°	13404	13102	12825
60°	11295	11201	10979
65°	9769	9809	9732
70°	8975	9021	9021
75°	8620	8620	8680
80°	8108	8198	8108
85°	6531	7262	7262



TEST NUMBER: P562026

CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.3	2.0
10°-20°	538.6	5.8
20°-30°	812.4	8.7
30°-40°	968.0	10.4
40°-50°	954.4	10.2
50°-60°	729.4	7.8
60°-70°	451.4	4.8
70°-80°	256.4	2.7
80°-90°	78.0	0.8
90°-100°	320.7	3.4
100°-110°	912.7	9.8
110°-120°	874.4	9.4
120°-130°	692.1	7.4
130°-140°	555.5	5.9
140°-150°	434.9	4.7
150°-160°	318.2	3.4
160°-170°	197.1	2.1
170°-180°	66.9	0.7
0°-30°	1539.3	16.5
0°-40°	2507.3	26.8
0°-60°	4191.0	44.8
0°-90°	4976.7	53.2
90°-120°	2107.9	22.5
90°-150°	3790.4	40.5
90°-180°	4373.0	46.8
0°-180°	9349.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1991	1991	1991	1991	1991	
5°	2001	1979	1986	1979	1975	190
15°	1926	1906	1914	1907	1903	543
25°	1785	1763	1773	1754	1752	821
35°	1572	1554	1559	1538	1536	981
45°	1272	1256	1250	1228	1224	975
55°	833	820	814	801	797	747
65°	448	444	449	446	446	453
75°	242	242	242	244	244	255
85°	62	65	69	69	69	72
90°	0	0	0	0	0	4
95°	35	138	621	215	132	40
105°	142	215	930	1643	1562	150
115°	264	319	705	1494	1754	260
125°	372	413	673	1117	1336	333
135°	455	493	665	944	1067	351
145°	537	564	670	817	890	335
155°	613	627	686	738	768	283
165°	677	680	695	710	720	190
175°	709	705	703	698	693	67
180°	704	704	704	704	704	

TEST NUMBER: P562026

CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1990.8	1990.8	1990.8	1990.8	1990.8
2.5°	2003.1	1985.7	1990.8	1986.4	1977.1
5°	2001.1	1979.3	1985.6	1978.7	1975.3
7.5°	1985.6	1964.2	1970.5	1963.6	1961.6
10°	1971.9	1951.8	1958.2	1951.3	1947.9
12.5°	1956.8	1935.4	1943.1	1934.8	1931.4
15°	1925.6	1905.5	1913.6	1906.7	1903.3
17.5°	1891.3	1869.9	1877.9	1870.0	1865.6
20°	1863.9	1843.8	1851.9	1839.8	1838.2
22.5°	1833.7	1813.6	1821.7	1805.6	1805.2
25°	1785.0	1763.2	1773.0	1754.1	1752.4
27.5°	1727.1	1706.9	1715.0	1695.8	1693.8
30°	1687.3	1667.2	1675.3	1654.6	1651.3
32.5°	1642.0	1623.2	1630.0	1609.4	1607.4
35°	1572.4	1553.9	1558.7	1538.1	1536.4
37.5°	1493.2	1476.4	1479.1	1456.4	1454.8
40°	1436.9	1420.2	1421.5	1397.4	1395.8
42.5°	1375.2	1358.4	1357.0	1333.0	1331.3
45°	1272.3	1255.5	1250.0	1227.7	1224.3
47.5°	1155.0	1138.3	1127.9	1109.7	1107.4
50°	1070.0	1053.2	1044.3	1028.7	1023.7
52.5°	978.1	961.3	953.7	939.5	934.5
55°	833.3	819.9	814.5	800.7	797.3
57.5°	695.8	686.8	685.2	671.8	670.4
60°	612.1	607.1	607.0	595.0	595.0
62.5°	540.8	537.1	539.8	531.9	530.5
65°	447.5	444.2	449.3	445.8	445.8
67.5°	373.8	373.8	376.9	375.5	375.5
70°	332.7	332.7	334.4	334.4	334.4
72.5°	295.6	294.3	298.7	298.7	297.3
75°	241.8	241.8	241.8	243.5	243.5
77.5°	188.3	188.6	190.0	189.6	188.3
80°	152.6	154.3	154.3	152.6	152.6
82.5°	116.9	118.6	118.7	118.3	116.9
85°	61.7	65.1	68.6	68.6	68.6
87.5°	17.8	23.2	27.4	27.4	26.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.7	56.8	131.7	38.3	28.9
95°	34.8	138.2	620.9	214.9	132.5
97.5°	64.0	161.8	956.3	684.3	468.9
100°	84.3	175.9	1029.1	1042.4	802.9
102.5°	106.8	191.1	1013.1	1334.3	1125.2
105°	141.9	215.1	930.1	1642.9	1561.7
107.5°	177.5	243.1	833.2	1729.9	1802.1
110°	202.1	263.6	777.5	1696.6	1858.8

TEST NUMBER: P562026

CATALOG NUMBER: SQ4-PR1-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.6	284.0	740.1	1617.8	1849.2
115°	263.6	318.6	705.3	1494.1	1754.4
117.5°	297.1	348.6	684.6	1358.7	1634.5
120°	323.9	367.0	682.5	1281.4	1545.7
122.5°	345.3	388.4	677.2	1213.5	1459.0
125°	372.0	412.6	673.1	1117.1	1335.6
127.5°	401.2	439.2	671.0	1059.4	1239.5
130°	416.2	454.1	667.8	1019.3	1176.3
132.5°	432.3	469.2	667.8	988.0	1132.4
135°	455.0	493.0	665.1	943.6	1066.6
137.5°	476.4	513.3	664.8	906.0	1012.3
140°	492.5	530.4	663.8	874.9	976.9
142.5°	510.7	542.3	667.0	850.0	941.6
145°	536.6	564.1	670.5	816.7	889.9
147.5°	558.9	585.5	676.4	783.0	846.3
150°	578.1	596.4	678.5	771.8	816.3
152.5°	593.1	612.5	680.6	756.8	798.1
155°	612.9	627.3	686.5	738.1	768.2
157.5°	637.5	646.2	687.9	729.6	751.0
160°	650.4	656.9	693.2	723.1	741.4
162.5°	657.9	665.5	694.3	717.6	731.8
165°	677.2	679.8	694.6	709.5	720.0
167.5°	690.3	687.9	700.7	707.5	711.7
170°	694.6	693.2	698.6	700.0	705.3
172.5°	704.2	699.7	701.8	697.9	702.0
175°	709.3	705.3	702.6	698.4	693.2
177.5°	711.4	705.1	701.8	697.5	698.6
180°	703.9	703.9	703.9	703.9	703.9

(END OF REPORT)