

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562040

Luminaire Tested: **SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562040
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7625.4 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 62.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562040
CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P562040

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	85	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19	14
5	65	54	46	40	58	48	42	37	38	33	30	29	25	23	20	18	16	12
6	59	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7504	7504	7504
5°	7571	7513	7474
10°	7547	7495	7455
15°	7514	7467	7427
20°	7477	7429	7373
25°	7423	7373	7288
30°	7343	7291	7187
35°	7235	7172	7070
40°	7070	6994	6867
45°	6782	6664	6527
50°	6274	6123	6003
55°	5475	5352	5239
60°	4615	4576	4486
65°	3991	4006	3975
70°	3666	3685	3685
75°	3522	3522	3547
80°	3310	3347	3310
85°	2668	2964	2964



TEST NUMBER: P562040

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.9	1.0
10°-20°	220.0	2.9
20°-30°	331.9	4.4
30°-40°	395.5	5.2
40°-50°	389.9	5.1
50°-60°	298.0	3.9
60°-70°	184.4	2.4
70°-80°	104.7	1.4
80°-90°	31.9	0.4
90°-100°	410.2	5.4
100°-110°	1167.3	15.3
110°-120°	1118.4	14.7
120°-130°	885.2	11.6
130°-140°	710.5	9.3
140°-150°	556.2	7.3
150°-160°	407.0	5.3
160°-170°	252.1	3.3
170°-180°	85.5	1.1
0°-30°	628.9	8.2
0°-40°	1024.3	13.4
0°-60°	1712.2	22.5
0°-90°	2033.1	26.7
90°-120°	2695.9	35.4
90°-150°	4847.7	63.6
90°-180°	5592.0	73.3
0°-180°	7625.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	813	813	813	813	813	
5°	818	809	811	808	807	78
15°	787	778	782	779	778	222
25°	729	720	724	717	716	336
35°	642	635	637	628	628	401
45°	520	513	511	502	500	398
55°	340	335	333	327	326	305
65°	183	182	184	182	182	185
75°	99	99	99	100	100	104
85°	25	27	28	28	28	29
90°	0	0	0	0	0	3
95°	44	177	794	275	169	51
105°	181	275	1190	2101	1997	192
115°	337	408	902	1911	2244	332
125°	476	528	861	1429	1708	426
135°	582	630	851	1207	1364	449
145°	686	722	858	1044	1138	429
155°	784	802	878	944	982	362
165°	866	869	888	907	921	244
175°	907	902	899	893	887	86
180°	900	900	900	900	900	



TEST NUMBER: P562040

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	813.3	813.3	813.3	813.3	813.3
2.5°	818.3	811.2	813.3	811.5	807.7
5°	817.5	808.6	811.2	808.4	807.0
7.5°	811.2	802.4	805.0	802.2	801.4
10°	805.6	797.4	800.0	797.2	795.8
12.5°	799.4	790.7	793.8	790.4	789.1
15°	786.7	778.5	781.8	778.9	777.6
17.5°	772.7	763.9	767.2	763.9	762.2
20°	761.5	753.2	756.6	751.6	750.9
22.5°	749.1	740.9	744.2	737.6	737.5
25°	729.2	720.3	724.3	716.6	715.9
27.5°	705.6	697.3	700.7	692.8	692.0
30°	689.3	681.1	684.4	676.0	674.6
32.5°	670.8	663.1	665.9	657.5	656.7
35°	642.4	634.8	636.8	628.3	627.7
37.5°	610.0	603.2	604.3	595.0	594.3
40°	587.0	580.2	580.7	570.9	570.2
42.5°	561.8	555.0	554.4	544.6	543.9
45°	519.8	512.9	510.7	501.5	500.2
47.5°	471.9	465.0	460.8	453.3	452.4
50°	437.1	430.3	426.6	420.3	418.2
52.5°	399.6	392.7	389.6	383.8	381.8
55°	340.4	335.0	332.7	327.1	325.7
57.5°	284.3	280.6	279.9	274.4	273.9
60°	250.1	248.0	248.0	243.1	243.1
62.5°	220.9	219.4	220.5	217.3	216.7
65°	182.8	181.5	183.5	182.1	182.1
67.5°	152.7	152.7	154.0	153.4	153.4
70°	135.9	135.9	136.6	136.6	136.6
72.5°	120.8	120.2	122.0	122.0	121.5
75°	98.8	98.8	98.8	99.5	99.5
77.5°	76.9	77.1	77.6	77.5	76.9
80°	62.3	63.0	63.0	62.3	62.3
82.5°	47.8	48.5	48.5	48.3	47.8
85°	25.2	26.6	28.0	28.0	28.0
87.5°	7.3	9.5	11.2	11.2	10.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.7	72.6	168.4	49.0	37.0
95°	44.5	176.7	794.2	274.9	169.4
97.5°	81.8	207.0	1223.1	875.2	599.7
100°	107.8	225.0	1316.2	1333.2	1026.9
102.5°	136.6	244.4	1295.7	1706.5	1439.1
105°	181.4	275.1	1189.5	2101.2	1997.4
107.5°	227.0	311.0	1065.6	2212.4	2304.8
110°	258.4	337.1	994.4	2169.9	2377.4



TEST NUMBER: P562040

CATALOG NUMBER: SQ4-PR1-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.6	363.2	946.5	2069.2	2365.0
115°	337.2	407.5	902.0	1910.8	2243.9
117.5°	380.0	445.9	875.6	1737.7	2090.5
120°	414.2	469.4	872.9	1638.8	1976.9
122.5°	441.6	496.8	866.1	1552.0	1866.0
125°	475.8	527.7	860.9	1428.7	1708.1
127.5°	513.1	561.7	858.2	1355.0	1585.3
130°	532.3	580.8	854.1	1303.6	1504.5
132.5°	552.8	600.0	854.1	1263.6	1448.3
135°	581.9	630.5	850.7	1206.8	1364.1
137.5°	609.3	656.5	850.3	1158.7	1294.6
140°	629.9	678.4	848.9	1118.9	1249.4
142.5°	653.1	693.6	853.0	1087.1	1204.3
145°	686.3	721.5	857.5	1044.5	1138.2
147.5°	714.8	748.9	865.0	1001.4	1082.4
150°	739.4	762.8	867.8	987.2	1044.1
152.5°	758.6	783.3	870.5	967.9	1020.8
155°	783.9	802.3	878.0	943.9	982.4
157.5°	815.4	826.4	879.7	933.1	960.5
160°	831.8	840.2	886.6	924.8	948.2
162.5°	841.4	851.1	888.0	917.8	935.9
165°	866.1	869.4	888.3	907.4	920.8
167.5°	882.8	879.8	896.2	904.9	910.2
170°	888.3	886.6	893.4	895.3	902.0
172.5°	900.6	894.9	897.5	892.5	897.9
175°	907.1	902.1	898.6	893.3	886.6
177.5°	909.9	901.8	897.5	892.1	893.4
180°	900.3	900.3	900.3	900.3	900.3

(END OF REPORT)