

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P561910

Luminaire Tested: **SQ4-PR1-075U-100D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561910  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-075U-100D-92765-1D-UNV-STD-W-4 (4000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7329.9 lumens  
Efficiency: N/A  
Efficacy: 110.9 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561910  
CATALOG NUMBER: SQ4-PR1-075U-100D-92765-1D-UNV-STD-W-4 (4000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561910

CATALOG NUMBER: SQ4-PR1-075U-100D-92765-1D-UNV-STD-W-4 (4000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55		
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47		
2	91	83	77	72	84	78	72	68	67	63	59	57	54	52	48	46	44	40		
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34		
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29		
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26		
6	64	52	44	38	60	49	42	37	43	37	33	37	32	29	31	28	25	23		
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20		
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18		
9	51	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16		
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14773	14773	14773
5°	14905	14791	14715
10°	14858	14755	14678
15°	14794	14701	14622
20°	14719	14624	14515
25°	14615	14517	14349
30°	14458	14355	14149
35°	14244	14119	13918
40°	13919	13770	13521
45°	13352	13118	12848
50°	12353	12055	11817
55°	10782	10538	10316
60°	9084	9008	8831
65°	7859	7888	7829
70°	7219	7254	7254
75°	6933	6933	6980
80°	6519	6594	6519
85°	5251	5843	5843



TEST NUMBER: P561910

CATALOG NUMBER: SQ4-PR1-075U-100D-92765-1D-UNV-STD-W-4 (4000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.4	2.1
10°-20°	433.2	5.9
20°-30°	653.4	8.9
30°-40°	778.5	10.6
40°-50°	767.6	10.5
50°-60°	586.6	8.0
60°-70°	363.0	5.0
70°-80°	206.2	2.8
80°-90°	62.7	0.9
90°-100°	244.1	3.3
100°-110°	694.5	9.5
110°-120°	665.4	9.1
120°-130°	526.6	7.2
130°-140°	422.7	5.8
140°-150°	330.9	4.5
150°-160°	242.1	3.3
160°-170°	150.0	2.0
170°-180°	50.9	0.7
0°-30°	1238.0	16.9
0°-40°	2016.6	27.5
0°-60°	3370.8	46.0
0°-90°	4002.7	54.6
90°-120°	1603.9	21.9
90°-150°	2884.1	39.3
90°-180°	3327.0	45.4
0°-180°	7329.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1601	1601	1601	1601	1601	
5°	1609	1592	1597	1592	1589	153
15°	1549	1533	1539	1534	1531	437
25°	1436	1418	1426	1411	1410	661
35°	1265	1250	1254	1237	1236	789
45°	1023	1010	1005	987	985	784
55°	670	660	655	644	641	601
65°	360	357	361	359	359	365
75°	194	194	194	196	196	205
85°	50	52	55	55	55	58
90°	0	0	0	0	0	3
95°	26	105	472	164	101	30
105°	108	164	708	1250	1188	114
115°	201	242	537	1137	1335	198
125°	283	314	512	850	1016	253
135°	346	375	506	718	812	267
145°	408	429	510	621	677	255
155°	466	477	522	562	584	216
165°	515	517	528	540	548	145
175°	540	537	535	532	528	51
180°	536	536	536	536	536	

TEST NUMBER: P561910

CATALOG NUMBER: SQ4-PR1-075U-100D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1601.2	1601.2	1601.2	1601.2	1601.2
2.5°	1611.1	1597.1	1601.2	1597.7	1590.1
5°	1609.4	1591.9	1597.0	1591.5	1588.8
7.5°	1597.0	1579.8	1584.9	1579.3	1577.7
10°	1586.0	1569.8	1575.0	1569.4	1566.7
12.5°	1573.9	1556.6	1562.8	1556.1	1553.4
15°	1548.8	1532.6	1539.1	1533.5	1530.8
17.5°	1521.2	1503.9	1510.4	1504.0	1500.5
20°	1499.1	1482.9	1489.5	1479.8	1478.4
22.5°	1474.8	1458.7	1465.2	1452.2	1451.9
25°	1435.7	1418.1	1426.0	1410.8	1409.5
27.5°	1389.1	1372.9	1379.4	1363.9	1362.3
30°	1357.1	1340.9	1347.4	1330.8	1328.1
32.5°	1320.7	1305.5	1311.0	1294.4	1292.8
35°	1264.7	1249.8	1253.6	1237.0	1235.7
37.5°	1200.9	1187.5	1189.6	1171.4	1170.1
40°	1155.7	1142.2	1143.3	1124.0	1122.6
42.5°	1106.1	1092.6	1091.4	1072.1	1070.8
45°	1023.3	1009.8	1005.4	987.4	984.7
47.5°	929.0	915.5	907.2	892.5	890.6
50°	860.6	847.1	839.9	827.4	823.3
52.5°	786.7	773.2	767.1	755.7	751.6
55°	670.3	659.5	655.1	644.0	641.3
57.5°	559.6	552.4	551.1	540.3	539.2
60°	492.3	488.3	488.2	478.6	478.6
62.5°	435.0	432.0	434.1	427.8	426.7
65°	360.0	357.3	361.3	358.6	358.6
67.5°	300.6	300.6	303.1	302.0	302.0
70°	267.6	267.6	268.9	268.9	268.9
72.5°	237.8	236.7	240.2	240.2	239.1
75°	194.5	194.5	194.5	195.8	195.8
77.5°	151.4	151.7	152.8	152.5	151.4
80°	122.7	124.1	124.1	122.7	122.7
82.5°	94.1	95.4	95.4	95.1	94.1
85°	49.6	52.3	55.2	55.2	55.2
87.5°	14.3	18.7	22.1	22.0	21.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.1	43.2	100.2	29.2	22.0
95°	26.5	105.1	472.5	163.5	100.8
97.5°	48.7	123.2	727.7	520.7	356.8
100°	64.2	133.8	783.1	793.2	611.0
102.5°	81.3	145.4	770.8	1015.3	856.2
105°	107.9	163.7	707.7	1250.1	1188.4
107.5°	135.0	185.0	634.0	1316.3	1371.2
110°	153.8	200.6	591.6	1290.9	1414.4

TEST NUMBER: P561910

CATALOG NUMBER: SQ4-PR1-075U-100D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	171.7	216.1	563.1	1231.0	1407.1
115°	200.6	242.4	536.6	1136.8	1335.0
117.5°	226.1	265.3	521.0	1033.9	1243.7
120°	246.4	279.3	519.3	975.0	1176.1
122.5°	262.7	295.6	515.3	923.4	1110.1
125°	283.1	314.0	512.2	850.0	1016.3
127.5°	305.3	334.2	510.6	806.1	943.1
130°	316.7	345.6	508.1	775.6	895.1
132.5°	328.9	357.0	508.1	751.8	861.7
135°	346.2	375.1	506.1	718.0	811.6
137.5°	362.5	390.6	505.9	689.4	770.2
140°	374.7	403.6	505.1	665.7	743.4
142.5°	388.6	412.7	507.5	646.8	716.5
145°	408.3	429.2	510.2	621.4	677.2
147.5°	425.2	445.6	514.6	595.8	644.0
150°	439.9	453.8	516.3	587.3	621.2
152.5°	451.3	466.0	517.9	575.8	607.3
155°	466.4	477.3	522.4	561.6	584.5
157.5°	485.1	491.7	523.4	555.1	571.5
160°	494.9	499.9	527.5	550.2	564.1
162.5°	500.6	506.4	528.3	546.1	556.8
165°	515.3	517.2	528.5	539.9	547.8
167.5°	525.2	523.4	533.2	538.3	541.5
170°	528.5	527.5	531.5	532.7	536.6
172.5°	535.8	532.4	534.0	531.0	534.2
175°	539.7	536.7	534.6	531.5	527.5
177.5°	541.3	536.5	534.0	530.8	531.5
180°	535.6	535.6	535.6	535.6	535.6

(END OF REPORT)