

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561921

Luminaire Tested: **SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561921
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8050.9 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 79.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561921
CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561921

CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	75	67	61	78	70	64	58	62	57	52	54	50	47	46	44	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	38	45	39	34	39	34	31	34	31	28	25
7	60	48	40	35	56	45	38	33	40	35	30	36	31	27	31	28	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17937	17937	17937
5°	18099	17959	17865
10°	18041	17915	17822
15°	17962	17850	17754
20°	17871	17756	17625
25°	17746	17627	17422
30°	17554	17429	17180
35°	17295	17144	16899
40°	16900	16719	16417
45°	16212	15927	15600
50°	14998	14638	14349
55°	13090	12794	12526
60°	11031	10939	10723
65°	9542	9577	9505
70°	8764	8808	8808
75°	8416	8416	8477
80°	7917	8007	7917
85°	6383	7093	7093



TEST NUMBER: P561921

CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	2.3
10°-20°	526.0	6.5
20°-30°	793.4	9.9
30°-40°	945.3	11.7
40°-50°	932.0	11.6
50°-60°	712.3	8.8
60°-70°	440.8	5.5
70°-80°	250.4	3.1
80°-90°	76.2	0.9
90°-100°	234.1	2.9
100°-110°	666.0	8.3
110°-120°	638.1	7.9
120°-130°	505.0	6.3
130°-140°	405.4	5.0
140°-150°	317.4	3.9
150°-160°	232.2	2.9
160°-170°	143.8	1.8
170°-180°	48.8	0.6
0°-30°	1503.2	18.7
0°-40°	2448.5	30.4
0°-60°	4092.8	50.8
0°-90°	4860.1	60.4
90°-120°	1538.2	19.1
90°-150°	2766.0	34.4
90°-180°	3191.0	39.6
0°-180°	8050.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1944	1944	1944	1944	1944	
5°	1954	1933	1939	1932	1929	185
15°	1880	1861	1869	1862	1859	531
25°	1743	1722	1732	1713	1711	802
35°	1536	1518	1522	1502	1500	958
45°	1242	1226	1221	1199	1196	952
55°	814	801	795	782	779	729
65°	437	434	439	435	435	443
75°	236	236	236	238	238	249
85°	60	64	67	67	67	70
90°	0	0	0	0	0	3
95°	25	101	453	157	97	29
105°	104	157	679	1199	1140	110
115°	192	232	515	1090	1280	189
125°	272	301	491	815	975	243
135°	332	360	485	689	778	256
145°	392	412	489	596	649	245
155°	447	458	501	539	560	207
165°	494	496	507	518	525	139
175°	518	515	513	510	506	49
180°	514	514	514	514	514	



TEST NUMBER: P561921

CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1944.1	1944.1	1944.1	1944.1	1944.1
2.5°	1956.2	1939.1	1944.1	1939.9	1930.7
5°	1954.2	1932.9	1939.1	1932.3	1929.0
7.5°	1939.1	1918.1	1924.4	1917.6	1915.7
10°	1925.7	1906.1	1912.3	1905.5	1902.3
12.5°	1911.0	1890.0	1897.6	1889.5	1886.2
15°	1880.5	1860.8	1868.8	1862.0	1858.7
17.5°	1847.0	1826.0	1833.9	1826.1	1821.9
20°	1820.2	1800.6	1808.5	1796.7	1795.1
22.5°	1790.7	1771.1	1779.0	1763.3	1762.9
25°	1743.2	1721.9	1731.5	1713.0	1711.4
27.5°	1686.6	1666.9	1674.9	1656.1	1654.1
30°	1647.7	1628.1	1636.0	1615.8	1612.6
32.5°	1603.5	1585.2	1591.8	1571.7	1569.7
35°	1535.5	1517.5	1522.1	1502.0	1500.4
37.5°	1458.2	1441.8	1444.4	1422.3	1420.7
40°	1403.2	1386.9	1388.2	1364.7	1363.1
42.5°	1343.0	1326.6	1325.2	1301.7	1300.1
45°	1242.5	1226.1	1220.7	1198.9	1195.6
47.5°	1128.0	1111.6	1101.5	1083.7	1081.4
50°	1044.9	1028.5	1019.8	1004.6	999.7
52.5°	955.1	938.8	931.4	917.5	912.6
55°	813.8	800.7	795.4	781.9	778.7
57.5°	679.5	670.7	669.1	656.0	654.7
60°	597.8	592.9	592.8	581.1	581.1
62.5°	528.1	524.5	527.1	519.4	518.1
65°	437.1	433.8	438.7	435.4	435.4
67.5°	365.0	365.0	368.1	366.7	366.7
70°	324.9	324.9	326.5	326.5	326.5
72.5°	288.7	287.4	291.7	291.7	290.4
75°	236.1	236.1	236.1	237.8	237.8
77.5°	183.9	184.2	185.5	185.2	183.9
80°	149.0	150.7	150.7	149.0	149.0
82.5°	114.2	115.8	115.9	115.5	114.2
85°	60.3	63.6	67.0	67.0	67.0
87.5°	17.4	22.7	26.8	26.8	25.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.8	41.4	96.1	28.0	21.1
95°	25.4	100.8	453.1	156.8	96.7
97.5°	46.7	118.1	697.9	499.4	342.2
100°	61.5	128.4	751.0	760.7	585.9
102.5°	77.9	139.4	739.3	973.7	821.1
105°	103.5	157.0	678.7	1198.9	1139.7
107.5°	129.5	177.4	608.0	1262.3	1315.0
110°	147.5	192.3	567.4	1238.0	1356.5

TEST NUMBER: P561921

CATALOG NUMBER: SQ4-PR1-075U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.6	207.2	540.0	1180.6	1349.4
115°	192.4	232.5	514.7	1090.3	1280.3
117.5°	216.8	254.4	499.6	991.5	1192.8
120°	236.3	267.8	498.0	935.1	1127.9
122.5°	252.0	283.5	494.1	885.5	1064.7
125°	271.5	301.1	491.2	815.2	974.6
127.5°	292.8	320.5	489.7	773.1	904.5
130°	303.7	331.4	487.3	743.8	858.4
132.5°	315.4	342.4	487.3	721.0	826.4
135°	332.0	359.7	485.4	688.6	778.3
137.5°	347.7	374.6	485.2	661.1	738.7
140°	359.4	387.1	484.4	638.4	712.9
142.5°	372.7	395.8	486.7	620.3	687.1
145°	391.6	411.7	489.3	595.9	649.4
147.5°	407.8	427.3	493.6	571.4	617.6
150°	421.9	435.2	495.1	563.2	595.7
152.5°	432.8	446.9	496.7	552.3	582.4
155°	447.3	457.8	501.0	538.6	560.5
157.5°	465.2	471.5	502.0	532.4	548.0
160°	474.6	479.4	505.9	527.6	541.0
162.5°	480.1	485.6	506.6	523.7	534.0
165°	494.1	496.1	506.8	517.8	525.4
167.5°	503.7	502.0	511.3	516.3	519.3
170°	506.8	505.9	509.8	510.8	514.7
172.5°	513.9	510.6	512.1	509.3	512.3
175°	517.6	514.7	512.7	509.7	505.9
177.5°	519.1	514.6	512.1	509.0	509.8
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)