

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561939

Luminaire Tested: **SQ4-PR1-0U-050D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561939
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-0U-050D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2118.6 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561939

CATALOG NUMBER: SQ4-PR1-0U-050D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561939

CATALOG NUMBER: SQ4-PR1-0U-050D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85			85	
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72			72	
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62			62	
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54			54	
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47			47	
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41			41	
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37			37	
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33			33	
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30			30	
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27			27	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7889	7829	7788
10°	7864	7810	7768
15°	7830	7781	7739
20°	7790	7740	7683
25°	7736	7684	7594
30°	7652	7598	7488
35°	7540	7473	7366
40°	7367	7288	7157
45°	7067	6943	6801
50°	6538	6380	6255
55°	5707	5577	5459
60°	4809	4768	4674
65°	4159	4174	4144
70°	3820	3839	3839
75°	3668	3668	3697
80°	3454	3491	3454
85°	2784	3091	3091



TEST NUMBER: P561939

CATALOG NUMBER: SQ4-PR1-OU-050D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.1	3.8
10°-20°	229.3	10.8
20°-30°	345.8	16.3
30°-40°	412.1	19.5
40°-50°	406.3	19.2
50°-60°	310.5	14.7
60°-70°	192.1	9.1
70°-80°	109.1	5.2
80°-90°	33.2	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.3	30.9
0°-40°	1067.3	50.4
0°-60°	1784.1	84.2
0°-90°	2118.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2118.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	848	848	848	848	848	
5°	852	843	845	842	841	81
15°	820	811	815	812	810	231
25°	760	751	755	747	746	350
35°	669	662	664	655	654	418
45°	542	534	532	523	521	415
55°	355	349	347	341	339	318
65°	190	189	191	190	190	193
75°	103	103	103	104	104	109
85°	26	28	29	29	29	32
90°	0	0	0	0	0	



TEST NUMBER: P561939

CATALOG NUMBER: SQ4-PR1-0U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	847.5	847.5	847.5	847.5	847.5
2.5°	852.7	845.3	847.5	845.6	841.6
5°	851.8	842.6	845.3	842.3	840.9
7.5°	845.3	836.1	838.8	835.9	835.1
10°	839.4	830.9	833.6	830.6	829.2
12.5°	833.0	823.9	827.2	823.6	822.2
15°	819.7	811.2	814.6	811.7	810.2
17.5°	805.1	796.0	799.4	796.0	794.2
20°	793.4	784.9	788.3	783.2	782.5
22.5°	780.6	772.0	775.5	768.6	768.5
25°	759.9	750.6	754.8	746.7	746.0
27.5°	735.2	726.6	730.1	721.9	721.0
30°	718.3	709.7	713.2	704.4	702.9
32.5°	699.0	691.0	693.9	685.1	684.2
35°	669.4	661.5	663.5	654.7	654.0
37.5°	635.6	628.5	629.6	620.0	619.3
40°	611.7	604.6	605.1	594.9	594.2
42.5°	585.4	578.3	577.7	567.4	566.7
45°	541.6	534.5	532.1	522.6	521.2
47.5°	491.7	484.5	480.2	472.4	471.4
50°	455.5	448.3	444.5	437.9	435.8
52.5°	416.4	409.2	406.0	400.0	397.8
55°	354.8	349.0	346.7	340.8	339.4
57.5°	296.2	292.4	291.7	286.0	285.4
60°	260.6	258.4	258.4	253.3	253.3
62.5°	230.2	228.7	229.8	226.4	225.8
65°	190.5	189.1	191.2	189.8	189.8
67.5°	159.1	159.1	160.4	159.9	159.9
70°	141.6	141.6	142.3	142.3	142.3
72.5°	125.8	125.3	127.2	127.1	126.6
75°	102.9	102.9	102.9	103.7	103.7
77.5°	80.1	80.3	80.9	80.7	80.1
80°	65.0	65.7	65.7	65.0	65.0
82.5°	49.8	50.5	50.5	50.4	49.8
85°	26.3	27.7	29.2	29.2	29.2
87.5°	7.6	9.9	11.7	11.7	11.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)