

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561960

Luminaire Tested: **SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561960
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3838.7 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 42.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561960
CATALOG NUMBER: SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561960

CATALOG NUMBER: SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14168	14168	14168
5°	14295	14185	14111
10°	14250	14150	14076
15°	14187	14098	14023
20°	14116	14024	13920
25°	14016	13922	13760
30°	13866	13766	13569
35°	13660	13542	13348
40°	13348	13205	12967
45°	12805	12581	12321
50°	11846	11562	11333
55°	10340	10105	9893
60°	8713	8639	8468
65°	7536	7564	7508
70°	6922	6957	6957
75°	6648	6648	6695
80°	6254	6323	6254
85°	5039	5600	5600



TEST NUMBER: P561960

CATALOG NUMBER: SQ4-PR1-OU-100D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.2	3.8
10°-20°	415.5	10.8
20°-30°	626.6	16.3
30°-40°	746.6	19.5
40°-50°	736.1	19.2
50°-60°	562.6	14.7
60°-70°	348.2	9.1
70°-80°	197.7	5.2
80°-90°	60.1	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1187.3	30.9
0°-40°	1934.0	50.4
0°-60°	3232.7	84.2
0°-90°	3838.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3838.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1544	1527	1532	1526	1524	146
15°	1485	1470	1476	1471	1468	419
25°	1377	1360	1368	1353	1352	634
35°	1213	1199	1202	1186	1185	757
45°	981	968	964	947	944	752
55°	643	632	628	618	615	576
65°	345	343	346	344	344	350
75°	186	186	186	188	188	197
85°	48	50	53	53	53	57
90°	0	0	0	0	0	



TEST NUMBER: P561960

CATALOG NUMBER: SQ4-PR1-0U-100D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1535.6	1535.6	1535.6	1535.6	1535.6
2.5°	1545.1	1531.6	1535.6	1532.2	1525.0
5°	1543.5	1526.7	1531.6	1526.2	1523.6
7.5°	1531.6	1515.0	1519.9	1514.6	1513.1
10°	1521.0	1505.5	1510.4	1505.1	1502.5
12.5°	1509.4	1492.8	1498.8	1492.4	1489.8
15°	1485.3	1469.8	1476.0	1470.7	1468.1
17.5°	1458.8	1442.3	1448.5	1442.4	1439.0
20°	1437.7	1422.2	1428.4	1419.1	1417.8
22.5°	1414.4	1398.9	1405.1	1392.7	1392.4
25°	1376.8	1360.0	1367.6	1353.0	1351.7
27.5°	1332.1	1316.6	1322.9	1308.0	1306.5
30°	1301.5	1285.9	1292.2	1276.3	1273.7
32.5°	1266.5	1252.0	1257.3	1241.4	1239.8
35°	1212.8	1198.6	1202.3	1186.4	1185.1
37.5°	1151.7	1138.8	1140.9	1123.4	1122.1
40°	1108.3	1095.4	1096.4	1077.9	1076.6
42.5°	1060.7	1047.8	1046.7	1028.2	1026.9
45°	981.4	968.4	964.2	946.9	944.3
47.5°	890.9	878.0	870.0	856.0	854.1
50°	825.3	812.4	805.5	793.5	789.6
52.5°	754.4	741.5	735.6	724.7	720.8
55°	642.8	632.4	628.2	617.6	615.0
57.5°	536.7	529.7	528.5	518.2	517.1
60°	472.2	468.3	468.2	458.9	458.9
62.5°	417.2	414.3	416.4	410.3	409.2
65°	345.2	342.6	346.5	343.9	343.9
67.5°	288.3	288.3	290.7	289.7	289.7
70°	256.6	256.6	257.9	257.9	257.9
72.5°	228.0	227.0	230.4	230.4	229.3
75°	186.5	186.5	186.5	187.8	187.8
77.5°	145.2	145.5	146.5	146.3	145.2
80°	117.7	119.0	119.0	117.7	117.7
82.5°	90.2	91.5	91.5	91.2	90.2
85°	47.6	50.2	52.9	52.9	52.9
87.5°	13.8	17.9	21.2	21.1	20.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)