

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561978

Luminaire Tested: **SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561978
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5280.6 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 55.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561978

CATALOG NUMBER: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561978

CATALOG NUMBER: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85		
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72		
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62		
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54		
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47		
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41		
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37		
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33		
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30		
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19489	19489	19489
5°	19665	19513	19412
10°	19602	19466	19364
15°	19516	19395	19291
20°	19418	19293	19150
25°	19281	19152	18930
30°	19073	18938	18666
35°	18791	18628	18361
40°	18363	18166	17837
45°	17615	17307	16950
50°	16295	15904	15591
55°	14223	13901	13608
60°	11985	11885	11649
65°	10368	10407	10326
70°	9522	9571	9571
75°	9144	9144	9211
80°	8602	8698	8602
85°	6934	7707	7707



TEST NUMBER: P561978

CATALOG NUMBER: SQ4-PR1-OU-125D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.8	3.8
10°-20°	571.5	10.8
20°-30°	862.0	16.3
30°-40°	1027.1	19.5
40°-50°	1012.6	19.2
50°-60°	773.9	14.7
60°-70°	478.9	9.1
70°-80°	272.0	5.2
80°-90°	82.8	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1633.3	30.9
0°-40°	2660.4	50.4
0°-60°	4447.0	84.2
0°-90°	5280.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5280.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2112	2112	2112	2112	2112	
5°	2123	2100	2107	2100	2096	201
15°	2043	2022	2030	2023	2020	577
25°	1894	1871	1881	1861	1860	872
35°	1668	1649	1654	1632	1630	1041
45°	1350	1332	1326	1303	1299	1034
55°	884	870	864	850	846	792
65°	475	471	477	473	473	481
75°	256	256	256	258	258	271
85°	66	69	73	73	73	79
90°	0	0	0	0	0	



TEST NUMBER: P561978

CATALOG NUMBER: SQ4-PR1-0U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2112.4	2112.4	2112.4	2112.4	2112.4
2.5°	2125.4	2106.9	2112.4	2107.8	2097.8
5°	2123.3	2100.1	2106.9	2099.5	2096.0
7.5°	2106.9	2084.1	2090.9	2083.6	2081.4
10°	2092.3	2071.0	2077.8	2070.4	2066.9
12.5°	2076.3	2053.6	2061.8	2053.0	2049.4
15°	2043.2	2021.9	2030.5	2023.1	2019.6
17.5°	2006.8	1984.1	1992.6	1984.2	1979.5
20°	1977.7	1956.4	1965.0	1952.2	1950.4
22.5°	1945.7	1924.3	1933.0	1915.8	1915.5
25°	1894.0	1870.9	1881.3	1861.2	1859.5
27.5°	1832.5	1811.2	1819.8	1799.4	1797.2
30°	1790.3	1769.0	1777.6	1755.7	1752.1
32.5°	1742.3	1722.4	1729.5	1707.7	1705.5
35°	1668.4	1648.8	1653.9	1632.0	1630.2
37.5°	1584.4	1566.6	1569.4	1545.4	1543.6
40°	1524.7	1506.9	1508.3	1482.8	1481.0
42.5°	1459.2	1441.4	1439.9	1414.4	1412.6
45°	1350.0	1332.2	1326.4	1302.6	1299.1
47.5°	1225.6	1207.8	1196.8	1177.5	1175.0
50°	1135.3	1117.5	1108.0	1091.5	1086.2
52.5°	1037.8	1020.0	1012.0	996.9	991.6
55°	884.2	870.0	864.2	849.6	846.0
57.5°	738.3	728.7	727.0	712.8	711.4
60°	649.5	644.2	644.1	631.3	631.3
62.5°	573.8	569.9	572.8	564.4	562.9
65°	474.9	471.3	476.7	473.0	473.0
67.5°	396.6	396.6	399.9	398.5	398.5
70°	353.0	353.0	354.8	354.8	354.8
72.5°	313.7	312.2	316.9	316.9	315.5
75°	256.5	256.5	256.5	258.4	258.4
77.5°	199.8	200.1	201.6	201.2	199.8
80°	161.9	163.7	163.7	161.9	161.9
82.5°	124.1	125.9	125.9	125.5	124.1
85°	65.5	69.1	72.8	72.8	72.8
87.5°	18.9	24.6	29.1	29.1	27.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)