

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P562108

Luminaire Tested: **SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562108
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10195.5 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 82.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562108
CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P562108

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	52	50	46	42	38	35	33	27	26	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	65	54	47	41	59	49	43	37	40	35	31	30	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14	11
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11710	11710	11710
5°	11815	11724	11663
10°	11778	11696	11635
15°	11726	11653	11590
20°	11667	11592	11506
25°	11585	11506	11373
30°	11460	11378	11215
35°	11290	11192	11032
40°	11033	10914	10717
45°	10583	10398	10184
50°	9790	9555	9367
55°	8546	8353	8176
60°	7202	7141	6999
65°	6228	6252	6204
70°	5722	5751	5751
75°	5493	5493	5532
80°	5170	5228	5170
85°	4171	4626	4626



TEST NUMBER: P562108

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.0	1.2
10°-20°	343.4	3.4
20°-30°	517.9	5.1
30°-40°	617.1	6.1
40°-50°	608.4	6.0
50°-60°	465.0	4.6
60°-70°	287.8	2.8
70°-80°	163.4	1.6
80°-90°	49.7	0.5
90°-100°	515.2	5.1
100°-110°	1465.8	14.4
110°-120°	1404.4	13.8
120°-130°	1111.5	10.9
130°-140°	892.2	8.8
140°-150°	698.5	6.9
150°-160°	511.1	5.0
160°-170°	316.6	3.1
170°-180°	107.4	1.1
0°-30°	981.4	9.6
0°-40°	1598.5	15.7
0°-60°	2671.9	26.2
0°-90°	3172.8	31.1
90°-120°	3385.4	33.2
90°-150°	6087.6	59.7
90°-180°	7023.0	68.9
0°-180°	10195.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1276	1262	1266	1262	1259	121
15°	1228	1215	1220	1216	1213	346
25°	1138	1124	1130	1118	1117	524
35°	1002	991	994	981	980	626
45°	811	800	797	783	780	621
55°	531	523	519	510	508	476
65°	285	283	286	284	284	289
75°	154	154	154	155	155	163
85°	39	42	44	44	44	46
90°	0	0	0	0	0	4
95°	56	222	997	345	213	64
105°	228	346	1494	2639	2508	241
115°	423	512	1133	2400	2818	417
125°	598	663	1081	1794	2145	535
135°	731	792	1068	1516	1713	564
145°	862	906	1077	1312	1429	538
155°	984	1008	1103	1185	1234	455
165°	1088	1092	1116	1140	1156	306
175°	1139	1133	1128	1122	1113	108
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P562108

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1269.2	1269.2	1269.2	1269.2	1269.2
2.5°	1277.1	1265.9	1269.2	1266.4	1260.4
5°	1275.7	1261.8	1265.9	1261.5	1259.3
7.5°	1265.9	1252.2	1256.3	1251.9	1250.6
10°	1257.2	1244.3	1248.4	1244.0	1241.9
12.5°	1247.5	1233.9	1238.8	1233.5	1231.4
15°	1227.6	1214.8	1220.0	1215.6	1213.4
17.5°	1205.8	1192.1	1197.3	1192.2	1189.4
20°	1188.3	1175.5	1180.6	1173.0	1171.9
22.5°	1169.0	1156.2	1161.4	1151.1	1150.9
25°	1138.0	1124.1	1130.3	1118.3	1117.2
27.5°	1101.1	1088.2	1093.4	1081.1	1079.8
30°	1075.7	1062.9	1068.0	1054.9	1052.7
32.5°	1046.8	1034.9	1039.2	1026.0	1024.7
35°	1002.4	990.7	993.7	980.6	979.5
37.5°	951.9	941.3	943.0	928.5	927.5
40°	916.1	905.4	906.2	890.9	889.8
42.5°	876.7	866.0	865.1	849.8	848.7
45°	811.1	800.5	796.9	782.7	780.5
47.5°	736.4	725.7	719.1	707.5	706.0
50°	682.1	671.5	665.7	655.8	652.6
52.5°	623.5	612.9	608.0	599.0	595.8
55°	531.3	522.7	519.3	510.5	508.3
57.5°	443.6	437.8	436.8	428.3	427.4
60°	390.3	387.1	387.0	379.3	379.3
62.5°	344.8	342.4	344.1	339.1	338.2
65°	285.3	283.2	286.4	284.2	284.2
67.5°	238.3	238.3	240.3	239.4	239.4
70°	212.1	212.1	213.2	213.2	213.2
72.5°	188.5	187.6	190.4	190.4	189.6
75°	154.1	154.1	154.1	155.2	155.2
77.5°	120.0	120.2	121.1	120.9	120.0
80°	97.3	98.4	98.4	97.3	97.3
82.5°	74.6	75.6	75.6	75.4	74.6
85°	39.4	41.5	43.7	43.7	43.7
87.5°	11.4	14.8	17.5	17.5	16.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.2	91.2	211.5	61.6	46.4
95°	55.9	221.9	997.3	345.2	212.8
97.5°	102.7	259.9	1535.9	1099.1	753.1
100°	135.4	282.5	1652.8	1674.2	1289.6
102.5°	171.5	306.9	1627.1	2143.0	1807.2
105°	227.8	345.5	1493.8	2638.6	2508.3
107.5°	285.0	390.5	1338.2	2778.3	2894.3
110°	324.6	423.3	1248.8	2724.8	2985.4

TEST NUMBER: P562108

CATALOG NUMBER: SQ4-PR1-150U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	362.4	456.1	1188.6	2598.4	2970.0
115°	423.4	511.7	1132.7	2399.6	2817.8
117.5°	477.2	560.0	1099.6	2182.2	2625.2
120°	520.1	589.5	1096.2	2058.0	2482.5
122.5°	554.5	623.9	1087.6	1949.0	2343.2
125°	597.5	662.7	1081.1	1794.1	2145.0
127.5°	644.4	705.3	1077.7	1701.5	1990.7
130°	668.4	729.4	1072.5	1637.1	1889.3
132.5°	694.2	753.5	1072.5	1586.8	1818.8
135°	730.8	791.7	1068.2	1515.5	1713.0
137.5°	765.2	824.4	1067.8	1455.1	1625.8
140°	791.0	851.9	1066.1	1405.1	1569.0
142.5°	820.2	871.0	1071.2	1365.2	1512.3
145°	861.9	906.0	1076.8	1311.6	1429.3
147.5°	897.6	940.4	1086.3	1257.5	1359.2
150°	928.5	957.9	1089.7	1239.6	1311.1
152.5°	952.6	983.7	1093.2	1215.5	1281.9
155°	984.4	1007.5	1102.6	1185.4	1233.7
157.5°	1023.9	1037.8	1104.8	1171.7	1206.2
160°	1044.6	1055.1	1113.4	1161.3	1190.7
162.5°	1056.6	1068.8	1115.1	1152.6	1175.3
165°	1087.6	1091.8	1115.5	1139.5	1156.3
167.5°	1108.6	1104.8	1125.4	1136.3	1143.0
170°	1115.5	1113.4	1122.0	1124.3	1132.7
172.5°	1131.0	1123.8	1127.1	1120.8	1127.5
175°	1139.2	1132.8	1128.4	1121.8	1113.4
177.5°	1142.6	1132.5	1127.1	1120.3	1122.0
180°	1130.6	1130.6	1130.6	1130.6	1130.6

(END OF REPORT)