

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562115

Luminaire Tested: **SQ4-PR1-150U-100D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562115  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-150U-100D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10092.9 lumens  
Efficiency: N/A  
Efficacy: 108.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 93.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562115  
CATALOG NUMBER: SQ4-PR1-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P562115

CATALOG NUMBER: SQ4-PR1-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	73	62	55	49	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	67	55	48	42	60	51	44	39	42	36	33	33	30	27	25	23	21	17
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	23	20	18	15
7	57	45	37	32	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	52	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13880	13880	13880
5°	14004	13897	13825
10°	13960	13864	13790
15°	13899	13813	13738
20°	13829	13740	13639
25°	13732	13639	13481
30°	13583	13487	13293
35°	13383	13266	13076
40°	13077	12938	12703
45°	12545	12325	12072
50°	11606	11326	11104
55°	10129	9901	9691
60°	8536	8464	8296
65°	7383	7412	7355
70°	6782	6817	6817
75°	6513	6513	6559
80°	6126	6195	6126
85°	4933	5483	5483



TEST NUMBER: P562115

CATALOG NUMBER: SQ4-PR1-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.3	1.4
10°-20°	407.0	4.0
20°-30°	613.9	6.1
30°-40°	731.5	7.2
40°-50°	721.2	7.1
50°-60°	551.2	5.5
60°-70°	341.1	3.4
70°-80°	193.7	1.9
80°-90°	58.9	0.6
90°-100°	464.5	4.6
100°-110°	1321.7	13.1
110°-120°	1266.3	12.5
120°-130°	1002.2	9.9
130°-140°	804.5	8.0
140°-150°	629.8	6.2
150°-160°	460.8	4.6
160°-170°	285.4	2.8
170°-180°	96.9	1.0
0°-30°	1163.2	11.5
0°-40°	1894.7	18.8
0°-60°	3167.0	31.4
0°-90°	3760.8	37.3
90°-120°	3052.5	30.2
90°-150°	5489.0	54.4
90°-180°	6332.0	62.7
0°-180°	10092.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1504	1504	1504	1504	1504	
5°	1512	1496	1500	1495	1493	143
15°	1455	1440	1446	1441	1438	411
25°	1349	1332	1340	1326	1324	621
35°	1188	1174	1178	1162	1161	742
45°	962	949	945	928	925	737
55°	630	620	616	605	602	564
65°	338	336	340	337	337	343
75°	183	183	183	184	184	193
85°	47	49	52	52	52	54
90°	0	0	0	0	0	4
95°	50	200	899	311	192	58
105°	205	312	1347	2379	2262	217
115°	382	461	1021	2164	2541	376
125°	539	598	975	1618	1934	482
135°	659	714	963	1366	1545	508
145°	777	817	971	1183	1289	485
155°	888	908	994	1069	1112	410
165°	981	984	1006	1028	1043	276
175°	1027	1022	1018	1012	1004	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P562115

CATALOG NUMBER: SQ4-PR1-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1504.4	1504.4	1504.4	1504.4	1504.4
2.5°	1513.7	1500.5	1504.4	1501.1	1494.0
5°	1512.1	1495.7	1500.5	1495.2	1492.7
7.5°	1500.5	1484.3	1489.1	1483.9	1482.3
10°	1490.1	1474.9	1479.8	1474.5	1472.0
12.5°	1478.7	1462.5	1468.4	1462.1	1459.5
15°	1455.1	1439.9	1446.1	1440.8	1438.3
17.5°	1429.2	1413.0	1419.1	1413.1	1409.8
20°	1408.5	1393.3	1399.4	1390.3	1389.1
22.5°	1385.7	1370.5	1376.6	1364.4	1364.2
25°	1348.9	1332.4	1339.8	1325.5	1324.3
27.5°	1305.1	1289.9	1296.0	1281.5	1279.9
30°	1275.0	1259.8	1266.0	1250.3	1247.8
32.5°	1240.8	1226.6	1231.7	1216.2	1214.6
35°	1188.2	1174.3	1177.8	1162.3	1161.0
37.5°	1128.3	1115.7	1117.7	1100.6	1099.3
40°	1085.8	1073.2	1074.2	1056.0	1054.7
42.5°	1039.2	1026.5	1025.5	1007.3	1006.0
45°	961.5	948.8	944.6	927.7	925.2
47.5°	872.8	860.2	852.3	838.6	836.8
50°	808.6	795.9	789.1	777.4	773.6
52.5°	739.1	726.4	720.7	710.0	706.2
55°	629.7	619.6	615.5	605.1	602.5
57.5°	525.8	519.0	517.8	507.7	506.6
60°	462.6	458.8	458.7	449.6	449.6
62.5°	408.7	405.9	407.9	401.9	400.9
65°	338.2	335.7	339.5	336.9	336.9
67.5°	282.5	282.5	284.8	283.8	283.8
70°	251.4	251.4	252.7	252.7	252.7
72.5°	223.4	222.4	225.7	225.7	224.7
75°	182.7	182.7	182.7	184.0	184.0
77.5°	142.3	142.5	143.6	143.3	142.3
80°	115.3	116.6	116.6	115.3	115.3
82.5°	88.4	89.6	89.7	89.4	88.4
85°	46.6	49.2	51.8	51.8	51.8
87.5°	13.5	17.5	20.7	20.7	19.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.5	82.2	190.7	55.5	41.9
95°	50.4	200.1	899.2	311.2	191.9
97.5°	92.6	234.4	1384.9	991.0	679.1
100°	122.1	254.7	1490.3	1509.6	1162.8
102.5°	154.7	276.7	1467.1	1932.3	1629.5
105°	205.4	311.5	1346.9	2379.1	2261.7
107.5°	257.0	352.1	1206.6	2505.1	2609.7
110°	292.6	381.7	1126.0	2456.9	2691.9



TEST NUMBER: P562115

CATALOG NUMBER: SQ4-PR1-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	326.7	411.3	1071.7	2342.9	2677.9
115°	381.8	461.4	1021.3	2163.6	2540.7
117.5°	430.2	504.9	991.5	1967.6	2367.1
120°	469.0	531.5	988.4	1855.6	2238.4
122.5°	500.0	562.5	980.6	1757.3	2112.8
125°	538.8	597.5	974.8	1617.7	1934.1
127.5°	581.0	636.0	971.7	1534.2	1795.0
130°	602.7	657.7	967.1	1476.1	1703.5
132.5°	626.0	679.4	967.1	1430.7	1639.9
135°	658.9	713.9	963.2	1366.5	1544.6
137.5°	689.9	743.4	962.8	1312.0	1465.9
140°	713.2	768.1	961.3	1266.9	1414.7
142.5°	739.5	785.4	965.9	1230.9	1363.6
145°	777.1	816.9	970.9	1182.7	1288.8
147.5°	809.3	848.0	979.5	1133.9	1225.6
150°	837.2	863.7	982.6	1117.8	1182.2
152.5°	858.9	887.0	985.7	1095.9	1155.8
155°	887.6	908.5	994.2	1068.8	1112.4
157.5°	923.3	935.8	996.1	1056.5	1087.6
160°	941.9	951.3	1003.9	1047.1	1073.7
162.5°	952.7	963.7	1005.4	1039.2	1059.7
165°	980.6	984.4	1005.8	1027.5	1042.6
167.5°	999.6	996.2	1014.7	1024.6	1030.6
170°	1005.8	1003.9	1011.6	1013.7	1021.3
172.5°	1019.8	1013.3	1016.3	1010.6	1016.7
175°	1027.1	1021.5	1017.5	1011.5	1003.9
177.5°	1030.2	1021.1	1016.3	1010.1	1011.6
180°	1019.4	1019.4	1019.4	1019.4	1019.4

(END OF REPORT)